

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P592726

Luminaire Tested: **HCC4W25D010SL-HM40525950-41WWW**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P592726
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4W25D010SL-HM40525950-41WWW
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WALLWASH DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2328.3 lumens
Efficiency: N/A
Efficacy: 86.9 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.03 / 1.1
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 26.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P592726
CATALOG NUMBER: HCC4W25D010SL-HM40525950-41WWW

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P592726

CATALOG NUMBER: HCC4W25D010SL-HM40525950-41WWW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	106	103	100	108	104	101	98	100	97	95	96	94	92	93	91	89	87								
2	102	95	89	84	100	93	88	83	90	85	81	87	83	80	84	81	78	76								
3	94	85	78	72	92	84	77	72	81	75	71	78	73	69	76	72	68	66								
4	87	77	69	63	85	76	68	63	73	67	62	71	66	61	69	64	60	58								
5	81	70	62	56	79	69	61	56	67	60	55	65	59	54	63	58	54	52								
6	76	64	56	50	74	63	55	50	61	54	49	59	53	49	58	53	48	47								
7	71	58	50	45	69	58	50	45	56	49	44	55	49	44	53	48	44	42								
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38								
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35								
10	59	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	160818	160818	160818
5°	167883	160095	152691
10°	172129	156761	143134
15°	175698	152572	132792
20°	174762	145162	121614
25°	167426	134232	110647
30°	154676	122559	100269
35°	135580	109018	90768
40°	118057	96336	81748
45°	102743	84009	73037
50°	91532	72401	64456
55°	81804	63654	55740
60°	73021	55629	48055
65°	64910	48799	45676
70°	56945	42050	42591
75°	48277	35838	39508
80°	37079	30473	35942
85°	21795	23776	30427



TEST NUMBER: P592726
 CATALOG NUMBER: HCC4W25D010SL-HM40525950-41WWW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	122.2	5.2
10°-20°	337.1	14.5
20°-30°	460.6	19.8
30°-40°	462.5	19.9
40°-50°	382.6	16.4
50°-60°	277.2	11.9
60°-70°	175.6	7.5
70°-80°	88.8	3.8
80°-90°	21.7	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	919.9	39.5
0°-40°	1382.3	59.4
0°-60°	2042.1	87.7
0°-90°	2328.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2328.3	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1304	1304	1304	1304	1304	
5°	1356	1336	1293	1250	1233	130
15°	1376	1322	1195	1084	1040	387
25°	1230	1149	986	862	813	562
35°	900	847	724	635	603	564
45°	589	555	482	434	419	458
55°	380	347	296	270	259	342
65°	222	198	167	150	156	221
75°	101	87	75	78	83	108
85°	15	15	17	20	22	21
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P592726

CATALOG NUMBER: HCC4W25D010SL-HM40525950-41WWW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	1303.8	1303.8	1303.8	1303.8	1303.8	1303.8	1303.8	1303.8	1303.8
2.5°	1328.3	1323.8	1316.1	1306.8	1296.1	1283.8	1273.1	1267.0	1263.9
5°	1355.9	1349.8	1335.9	1316.1	1293.0	1270.0	1250.1	1237.8	1233.2
7.5°	1372.8	1363.6	1343.6	1313.0	1277.7	1243.9	1214.8	1198.0	1193.4
10°	1374.3	1363.6	1337.5	1296.1	1251.6	1207.1	1171.9	1147.3	1142.8
12.5°	1375.9	1362.0	1329.8	1280.7	1225.5	1170.3	1127.4	1098.3	1090.6
15°	1375.9	1362.0	1322.2	1263.9	1194.8	1131.9	1084.4	1050.6	1039.9
17.5°	1363.6	1348.3	1300.7	1233.2	1158.0	1087.5	1032.2	997.0	986.3
20°	1331.4	1314.5	1260.9	1187.3	1105.9	1032.2	977.0	940.2	926.5
22.5°	1285.4	1265.4	1208.7	1128.9	1047.6	972.4	918.8	880.4	868.2
25°	1230.2	1210.2	1148.9	1070.6	986.3	915.7	862.0	826.8	813.0
27.5°	1162.6	1141.2	1081.4	1003.1	924.9	854.3	805.3	773.0	759.3
30°	1086.0	1063.0	1006.2	931.1	860.5	793.0	745.5	719.4	704.0
32.5°	997.0	977.0	926.5	858.9	793.0	728.5	688.7	665.7	653.5
35°	900.4	889.7	846.6	788.4	724.0	670.3	635.1	613.5	602.8
37.5°	814.5	803.7	766.9	717.8	661.1	612.0	582.9	564.5	555.2
40°	733.2	724.0	688.7	647.3	598.3	555.2	530.7	516.9	507.7
42.5°	653.5	648.8	619.7	581.3	538.4	501.6	481.6	470.9	463.2
45°	589.0	582.9	555.2	518.4	481.6	450.9	434.1	426.4	418.7
47.5°	532.2	524.5	495.4	463.2	429.5	401.9	386.6	378.9	375.8
50°	477.0	469.3	443.2	411.1	377.3	357.4	345.1	337.5	335.9
52.5°	427.9	420.3	391.1	360.5	334.4	317.5	306.7	299.1	296.0
55°	380.4	371.2	346.6	317.5	296.0	280.7	269.9	262.3	259.2
57.5°	337.5	328.2	306.7	279.2	259.2	245.4	236.2	228.5	225.5
60°	296.0	288.3	268.5	242.4	225.5	213.2	204.0	197.9	194.8
62.5°	257.6	251.5	231.6	208.6	194.8	184.0	176.3	170.3	173.3
65°	222.4	216.3	197.9	177.9	167.2	156.5	150.3	150.3	156.5
67.5°	188.7	182.6	167.2	150.3	141.1	133.4	128.8	133.4	138.1
70°	157.9	151.9	138.1	124.2	116.6	110.4	110.4	115.0	118.1
72.5°	128.8	122.7	112.0	101.3	95.1	90.5	95.1	98.1	101.3
75°	101.3	96.6	87.4	79.7	75.2	73.6	78.2	81.3	82.9
77.5°	75.2	72.1	65.9	59.8	56.8	58.3	62.9	64.5	65.9
80°	52.2	50.6	46.1	42.9	42.9	44.5	47.5	49.1	50.6
82.5°	32.2	32.2	29.1	27.7	29.1	32.2	33.8	35.2	35.2
85°	15.4	16.8	15.4	15.4	16.8	20.0	20.0	21.5	21.5
87.5°	4.6	4.6	6.1	6.1	7.7	7.7	7.7	7.7	9.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)