

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580609

Luminaire Tested: **HCC4S40D010SL-HM43040840-41WDW**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580609
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-9)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4S40D010SL-HM43040840-41WDW
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WIDE DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 4000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4249.8 lumens
Efficiency: N/A
Efficacy: 103.7 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.07 / 1.04
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 41
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580609
CATALOG NUMBER: HCC4S40D010SL-HM43040840-41WDW

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P580609

CATALOG NUMBER: HCC4S40D010SL-HM43040840-41WDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	89																			
2	103	97	91	87	101	95	90	86	91	87	84	88	85	82	85	83	80	78																			
3	96	87	81	76	94	86	80	75	83	78	74	81	76	72	78	74	71	69																			
4	90	80	72	67	87	78	72	66	76	70	66	74	69	65	72	68	64	62																			
5	84	73	65	60	82	72	65	59	70	64	59	68	63	58	66	62	58	56																			
6	78	67	59	54	77	66	59	54	64	58	53	63	57	53	61	56	53	51																			
7	73	62	54	49	72	61	54	49	60	53	49	58	53	48	57	52	48	46																			
8	69	57	50	45	68	57	50	45	55	49	45	54	49	44	53	48	44	42																			
9	65	53	46	41	64	53	46	41	52	45	41	51	45	41	50	45	41	39																			
10	61	50	43	38	60	49	43	38	48	42	38	48	42	38	47	42	38	36																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	339743	339743	339743
5°	338936	339283	339283
10°	334989	335340	334989
15°	330977	330977	330977
20°	317391	318139	318506
25°	296882	297263	298038
30°	266011	266809	266809
35°	215958	217674	218126
40°	162997	163915	164365
45°	124827	124339	124339
50°	102873	102336	102336
55°	88298	87674	87674
60°	78793	78078	78078
65°	74074	74074	74074
70°	68882	68882	68882
75°	62526	63861	62526
80°	58743	56683	58743
85°	48401	48401	48401



TEST NUMBER: P580609

CATALOG NUMBER: HCC4S40D010SL-HM43040840-41WDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	259.5	6.1
10°-20°	726.2	17.1
20°-30°	998.0	23.5
30°-40°	897.3	21.1
40°-50°	567.0	13.3
50°-60°	370.2	8.7
60°-70°	250.8	5.9
70°-80°	141.1	3.3
80°-90°	39.6	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1983.7	46.7
0°-40°	2881.0	67.8
0°-60°	3818.2	89.8
0°-90°	4249.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4249.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2754	2754	2754	2754	2754	
5°	2737	2737	2740	2740	2740	259
15°	2592	2592	2592	2592	2592	726
25°	2181	2184	2184	2190	2190	996
35°	1434	1440	1446	1451	1449	893
45°	716	713	713	713	713	568
55°	411	411	408	411	408	372
65°	254	254	254	254	254	251
75°	131	134	134	134	131	141
85°	34	34	34	34	34	40
90°	0	0	0	0	0	



TEST NUMBER: P580609

CATALOG NUMBER: HCC4S40D010SL-HM43040840-41WDW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2754.4	2754.4	2754.4	2754.4	2754.4
2.5°	2740.2	2740.2	2740.2	2740.2	2740.2
5°	2737.4	2737.4	2740.2	2740.2	2740.2
7.5°	2717.4	2720.2	2720.2	2720.2	2720.2
10°	2674.6	2674.6	2677.4	2677.4	2674.6
12.5°	2634.7	2634.7	2634.7	2637.5	2634.7
15°	2591.9	2591.9	2591.9	2591.9	2591.9
17.5°	2517.8	2520.6	2520.6	2520.6	2520.6
20°	2418.0	2423.7	2423.7	2426.5	2426.5
22.5°	2303.9	2306.8	2309.6	2312.5	2309.6
25°	2181.4	2184.2	2184.2	2189.9	2189.9
27.5°	2038.8	2041.6	2047.3	2047.3	2047.3
30°	1867.7	1870.5	1873.3	1873.3	1873.3
32.5°	1665.2	1665.2	1671.0	1673.8	1671.0
35°	1434.2	1439.9	1445.6	1451.4	1448.6
37.5°	1214.7	1220.4	1223.2	1223.2	1226.0
40°	1012.3	1018.0	1018.0	1023.7	1020.8
42.5°	852.5	849.7	849.7	855.4	852.5
45°	715.6	712.8	712.8	712.8	712.8
47.5°	615.9	613.1	613.1	613.1	613.1
50°	536.1	533.3	533.3	533.3	533.3
52.5°	470.5	467.7	467.7	467.7	464.8
55°	410.6	410.6	407.7	410.6	407.7
57.5°	356.5	356.5	356.5	356.5	356.5
60°	319.4	316.5	316.5	316.5	316.5
62.5°	285.2	285.2	285.2	285.2	285.2
65°	253.8	253.8	253.8	253.8	253.8
67.5°	222.4	219.6	222.4	222.4	219.6
70°	191.0	188.2	191.0	191.0	191.0
72.5°	159.6	159.6	159.6	162.5	159.6
75°	131.2	134.0	134.0	134.0	131.2
77.5°	105.5	108.4	105.5	105.5	105.5
80°	82.7	79.8	79.8	79.8	82.7
82.5°	57.1	57.1	57.1	57.1	57.1
85°	34.2	34.2	34.2	34.2	34.2
87.5°	14.2	14.2	14.2	14.2	14.2
90°	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)