

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580630

Luminaire Tested: **HCC4W40D010BZ-HM43040927-41WWBB**

Issue Date: 9/9/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P580630  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-17)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC4W40D010BZ-HM43040927-41WWBB  
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WALLWASH DISTRIBUTION, WHITE BAFFLE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2635.7 lumens  
Efficiency: N/A  
Efficacy: 64.3 lumens/watt  
Spacing Criteria (0/90/45): 1.11 / 1.04 / 1.12  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 41  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P580630  
CATALOG NUMBER: HCC4W40D010BZ-HM43040927-41WWBB

### Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P580630

CATALOG NUMBER: HCC4W40D010BZ-HM43040927-41WWBB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				
1	111	108	104	101	109	105	102	100	101	99	97	97	95	94	94	92	91	89				
2	103	97	91	87	101	95	90	86	92	87	84	88	85	82	85	83	80	78				
3	96	87	80	75	94	86	79	74	83	78	73	80	76	72	78	74	71	69				
4	89	79	72	66	87	78	71	65	75	69	65	73	68	64	71	67	63	61				
5	83	72	64	58	81	71	64	58	69	62	58	67	61	57	65	60	56	55				
6	77	66	58	52	75	65	57	52	63	57	52	61	56	51	60	55	51	49				
7	72	60	53	47	71	59	52	47	58	51	47	57	51	46	55	50	46	44				
8	68	56	48	43	66	55	48	43	54	47	42	53	47	42	51	46	42	40				
9	64	52	44	39	62	51	44	39	50	43	39	49	43	39	48	43	39	37				
10	60	48	41	36	59	47	41	36	46	40	36	46	40	36	45	39	36	34				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	188213	188213	188213
5°	199407	187582	178185
10°	207699	184591	167745
15°	215642	180167	157718
20°	217671	171520	145884
25°	210637	158634	133525
30°	196920	143752	121505
35°	175513	127795	109168
40°	153416	111133	97157
45°	133654	94266	84061
50°	116632	79980	72055
55°	102212	66299	58342
60°	89426	53532	42826
65°	77927	39927	24079
70°	68125	25822	7826
75°	55902	13439	2097
80°	41625	6109	1492
85°	24625	2972	2972



TEST NUMBER: P580630  
 CATALOG NUMBER: HCC4W40D010BZ-HM43040927-41WWBB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	144.0	5.5
10°-20°	403.1	15.3
20°-30°	557.3	21.1
30°-40°	560.4	21.3
40°-50°	452.2	17.2
50°-60°	305.8	11.6
60°-70°	155.6	5.9
70°-80°	49.8	1.9
80°-90°	7.6	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1104.4	41.9
0°-40°	1664.7	63.2
0°-60°	2422.7	91.9
0°-90°	2635.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2635.7	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	1526	1526	1526	1526	1526	
5°	1610	1580	1515	1461	1439	155
15°	1689	1598	1411	1276	1235	476
25°	1548	1413	1166	1022	981	708
35°	1166	1053	849	742	725	728
45°	766	686	540	482	482	594
55°	475	410	308	269	271	427
65°	267	217	137	89	82	268
75°	117	82	28	6	4	126
85°	17	9	2	2	2	23
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P580630

CATALOG NUMBER: HCC4W40D010BZ-HM43040927-41WWBB

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	1525.9	1525.9	1525.9	1525.9	1525.9	1525.9	1525.9	1525.9	1525.9
2.5°	1567.2	1558.5	1549.8	1534.6	1517.3	1499.9	1489.0	1480.4	1476.0
5°	1610.5	1599.8	1580.2	1547.7	1515.0	1484.7	1460.8	1445.6	1439.1
7.5°	1645.3	1630.2	1597.5	1552.0	1502.0	1454.3	1423.9	1402.3	1393.5
10°	1658.3	1640.9	1597.5	1536.8	1473.8	1415.3	1371.8	1350.1	1339.3
12.5°	1673.5	1654.0	1599.8	1523.8	1445.6	1376.1	1326.3	1298.0	1287.1
15°	1688.7	1662.7	1597.5	1504.3	1410.9	1330.6	1276.3	1248.1	1235.1
17.5°	1688.7	1658.3	1580.2	1471.6	1365.3	1280.6	1219.9	1187.4	1176.5
20°	1658.3	1623.7	1538.9	1419.5	1306.7	1215.5	1156.9	1124.4	1111.4
22.5°	1610.5	1571.5	1480.4	1356.6	1237.2	1148.2	1089.6	1059.2	1046.2
25°	1547.7	1508.5	1413.0	1285.0	1165.6	1076.6	1022.4	994.1	981.1
27.5°	1473.8	1430.4	1334.9	1206.9	1089.6	1005.0	955.1	929.0	918.2
30°	1382.6	1341.4	1248.1	1122.2	1009.3	931.2	885.6	861.7	853.1
32.5°	1276.3	1241.6	1150.4	1033.2	926.8	855.2	814.0	794.5	785.7
35°	1165.6	1133.0	1052.7	944.2	848.7	781.4	742.3	729.3	725.0
37.5°	1061.5	1033.2	955.1	855.2	768.4	709.8	675.1	666.3	662.1
40°	952.8	933.3	861.7	770.6	690.2	638.2	609.9	603.4	603.4
42.5°	855.2	833.5	770.6	688.1	616.4	564.3	544.8	538.3	540.4
45°	766.2	744.6	685.9	609.9	540.4	497.1	481.9	481.9	481.9
47.5°	683.7	664.2	609.9	531.8	475.3	440.7	425.4	425.4	427.7
50°	607.8	594.7	533.9	466.7	416.8	384.2	373.3	371.2	375.5
52.5°	536.2	520.9	466.7	405.9	358.2	332.2	321.3	319.0	321.3
55°	475.3	458.0	410.3	351.7	308.3	282.2	269.2	267.0	271.3
57.5°	416.8	403.8	353.8	301.7	260.5	234.4	223.5	219.3	221.4
60°	362.5	349.4	303.9	253.9	217.0	191.0	175.8	171.5	173.6
62.5°	312.5	301.7	258.3	210.5	173.6	149.8	134.6	123.8	128.0
65°	267.0	256.1	217.0	169.3	136.8	110.8	89.0	80.3	82.5
67.5°	227.9	214.9	178.0	134.6	102.0	73.8	49.9	45.6	45.6
70°	188.9	175.8	143.3	104.1	71.6	39.1	21.7	21.7	21.7
72.5°	151.9	141.1	110.8	78.1	45.6	17.4	8.6	8.6	8.6
75°	117.3	108.5	82.5	54.3	28.2	8.6	6.5	4.4	4.4
77.5°	86.9	78.1	58.6	36.9	17.4	4.4	4.4	4.4	4.4
80°	58.6	52.1	39.1	21.7	8.6	2.1	2.1	2.1	2.1
82.5°	34.8	30.4	21.7	10.9	4.4	2.1	2.1	2.1	2.1
85°	17.4	13.0	8.6	4.4	2.1	2.1	2.1	2.1	2.1
87.5°	4.4	2.1	2.1	2.1	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°    - - 45°-225°    - - - - 90°-270°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)