

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580990

Luminaire Tested: **HCC4W05D010MB-HM40525827-41WWBB**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580990
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-17)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4W05D010MB-HM40525827-41WWBB
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WALLWASH DISTRIBUTION, WHITE BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 484.7 lumens
Efficiency: N/A
Efficacy: 80.8 lumens/watt
Spacing Criteria (0/90/45): 1.11 / 1.04 / 1.12
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580990
CATALOG NUMBER: HCC4W05D010MB-HM40525827-41WWBB

Luminous Intensity Polar Plot





TEST NUMBER: P580990

CATALOG NUMBER: HCC4W05D010MB-HM40525827-41WWBB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	108	104	101	109	105	102	100	101	99	97	97	95	94	94	92	91	89								
2	103	97	91	87	101	95	90	86	92	87	84	88	85	82	85	83	80	78								
3	96	87	80	75	94	86	79	74	83	78	73	80	76	72	78	74	71	69								
4	89	79	72	66	87	78	71	65	75	69	65	73	68	64	71	67	63	61								
5	83	72	64	58	81	71	64	58	69	62	58	67	61	57	65	60	56	55								
6	77	66	58	52	75	65	57	52	63	57	52	61	56	51	60	55	51	49								
7	72	60	53	47	71	59	52	47	58	51	47	57	51	46	55	50	46	44								
8	68	56	48	43	66	55	48	43	54	47	42	53	47	42	51	46	42	40								
9	64	52	44	39	62	51	44	39	50	43	39	49	43	39	48	43	39	37								
10	60	48	41	36	59	47	41	36	46	40	36	46	40	36	45	39	36	34								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	34611	34611	34611
5°	36662	34495	32762
10°	38201	33942	30849
15°	39650	33137	29000
20°	40035	31542	26817
25°	38720	29166	24552
30°	36205	26434	22347
35°	32269	23505	20087
40°	28210	20433	17873
45°	24578	17339	15455
50°	21453	14699	13241
55°	18795	12172	10731
60°	16430	9868	7869
65°	14330	7355	4436
70°	12514	4760	1443
75°	10294	2478	381
80°	7671	1137	355
85°	4529	708	708



TEST NUMBER: P580990
 CATALOG NUMBER: HCC4W05D010MB-HM40525827-41WWBB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	26.5	5.5
10°-20°	74.1	15.3
20°-30°	102.5	21.1
30°-40°	103.1	21.3
40°-50°	83.1	17.2
50°-60°	56.2	11.6
60°-70°	28.6	5.9
70°-80°	9.2	1.9
80°-90°	1.4	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	203.1	41.9
0°-40°	306.1	63.2
0°-60°	445.5	91.9
0°-90°	484.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	484.7	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	281	281	281	281	281	
5°	296	291	279	269	265	29
15°	310	294	260	235	227	87
25°	284	260	214	188	180	130
35°	214	194	156	136	133	134
45°	141	126	99	89	89	109
55°	87	76	57	50	50	79
65°	49	40	25	16	15	49
75°	22	15	5	1	1	23
85°	3	2	0	0	0	4
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P580990

CATALOG NUMBER: HCC4W05D010MB-HM40525827-41WWBB

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	280.6	280.6	280.6	280.6	280.6	280.6	280.6	280.6	280.6
2.5°	288.2	286.6	285.0	282.2	279.0	275.8	273.8	272.2	271.4
5°	296.1	294.2	290.6	284.5	278.6	273.0	268.7	265.8	264.6
7.5°	302.6	299.8	293.7	285.3	276.1	267.4	261.8	257.9	256.3
10°	305.0	301.7	293.7	282.6	271.0	260.3	252.2	248.2	246.3
12.5°	307.7	304.2	294.2	280.2	265.8	253.0	243.9	238.7	236.6
15°	310.5	305.8	293.7	276.6	259.5	244.7	234.7	229.5	227.1
17.5°	310.5	305.0	290.6	270.6	251.1	235.5	224.3	218.4	216.3
20°	305.0	298.5	283.0	261.0	240.3	223.5	212.7	206.8	204.3
22.5°	296.1	289.0	272.2	249.5	227.5	211.1	200.3	194.8	192.4
25°	284.5	277.4	259.8	236.3	214.3	197.9	188.0	182.8	180.4
27.5°	271.0	263.0	245.5	221.9	200.3	184.8	175.6	170.8	168.8
30°	254.2	246.6	229.5	206.3	185.6	171.3	162.9	158.4	156.9
32.5°	234.7	228.2	211.6	190.0	170.5	157.3	149.7	146.1	144.5
35°	214.3	208.4	193.6	173.7	156.1	143.7	136.5	134.2	133.4
37.5°	195.2	190.0	175.6	157.3	141.3	130.5	124.2	122.6	121.8
40°	175.2	171.6	158.4	141.6	126.9	117.4	112.1	111.0	111.0
42.5°	157.3	153.2	141.6	126.6	113.4	103.7	100.2	99.0	99.4
45°	140.9	136.9	126.1	112.1	99.4	91.4	88.6	88.6	88.6
47.5°	125.8	122.1	112.1	97.8	87.4	81.0	78.2	78.2	78.7
50°	111.8	109.4	98.2	85.8	76.6	70.6	68.7	68.2	69.0
52.5°	98.6	95.8	85.8	74.7	65.8	61.1	59.0	58.7	59.0
55°	87.4	84.2	75.5	64.7	56.6	51.9	49.5	49.1	49.9
57.5°	76.6	74.2	65.0	55.5	47.9	43.1	41.1	40.3	40.7
60°	66.6	64.2	55.8	46.6	40.0	35.1	32.3	31.6	31.9
62.5°	57.4	55.5	47.4	38.7	31.9	27.6	24.7	22.7	23.5
65°	49.1	47.1	40.0	31.1	25.2	20.3	16.3	14.8	15.2
67.5°	41.9	39.5	32.7	24.7	18.7	13.6	9.2	8.4	8.4
70°	34.7	32.3	26.3	19.2	13.2	7.2	4.0	4.0	4.0
72.5°	27.9	26.0	20.3	14.4	8.4	3.2	1.6	1.6	1.6
75°	21.6	20.0	15.2	10.0	5.2	1.6	1.2	0.8	0.8
77.5°	16.0	14.4	10.8	6.8	3.2	0.8	0.8	0.8	0.8
80°	10.8	9.5	7.2	4.0	1.6	0.5	0.5	0.5	0.5
82.5°	6.4	5.6	4.0	2.0	0.8	0.5	0.5	0.5	0.5
85°	3.2	2.4	1.6	0.8	0.5	0.5	0.5	0.5	0.5
87.5°	0.8	0.5	0.5	0.5	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)