

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581006

Luminaire Tested: **HCC4S05D010MB-HM40525830-41RWWC**

Issue Date: 9/9/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P581006  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-14)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC4S05D010MB-HM40525830-41RWWC  
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WALLWASH DISTRIBUTION, SPECULAR TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 666.8 lumens  
Efficiency: N/A  
Efficacy: 111.1 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.15 / 1.21  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 6  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P581006  
CATALOG NUMBER: HCC4S05D010MB-HM40525830-41RWWC

### Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P581006

CATALOG NUMBER: HCC4S05D010MB-HM40525830-41RWWC

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	111	107	103	100	108	105	102	99	101	98	96	97	95	93	93	92	90	88					88			
2	102	95	90	85	100	94	88	84	90	86	82	87	83	80	84	81	78	76					76			
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67					67			
4	87	77	69	63	85	76	68	63	73	67	62	71	66	61	69	64	60	58					58			
5	81	70	61	56	79	68	61	55	66	60	55	65	59	54	63	58	54	52					52			
6	75	63	55	49	74	62	55	49	61	54	49	59	53	48	58	52	48	46					46			
7	70	58	50	44	69	57	49	44	56	49	44	54	48	44	53	47	43	41					41			
8	66	53	45	40	64	53	45	40	51	44	40	50	44	39	49	43	39	37					37			
9	62	49	42	36	60	49	41	36	47	41	36	46	40	36	45	40	36	34					34			
10	58	46	38	33	57	45	38	33	44	38	33	43	37	33	42	37	33	31					31			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	39471	39471	39471
5°	41058	39832	39411
10°	42409	40192	39315
15°	43902	40301	39305
20°	44038	39326	38827
25°	42489	37372	37658
30°	39538	34795	35778
35°	35612	31847	33007
40°	31398	28967	30287
45°	27456	26096	27387
50°	24313	23488	24716
55°	21376	20752	21569
60°	19094	17688	18230
65°	16782	14389	14155
70°	14642	10603	9665
75°	12153	6386	5147
80°	9163	2415	1563
85°	4387	708	708



TEST NUMBER: P581006  
 CATALOG NUMBER: HCC4S05D010MB-HM40525830-41RWWC

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	30.9	4.6
10°-20°	90.1	13.5
20°-30°	130.4	19.6
30°-40°	137.6	20.6
40°-50°	119.1	17.9
50°-60°	88.2	13.2
60°-70°	50.9	7.6
70°-80°	17.8	2.7
80°-90°	1.9	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	251.4	37.7
0°-40°	389.0	58.3
0°-60°	596.3	89.4
0°-90°	666.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	666.8	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	320	320	320	320	320	
5°	332	327	322	319	318	32
15°	344	333	316	308	308	97
25°	312	297	275	273	277	143
35°	236	226	212	216	219	148
45°	157	153	150	155	157	122
55°	99	97	96	100	100	90
65°	58	54	49	47	48	57
75°	26	22	13	11	11	27
85°	3	2	0	0	0	5
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P581006

CATALOG NUMBER: HCC4S05D010MB-HM40525830-41RWWC

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	320.0	320.0	320.0	320.0	320.0	320.0	320.0	320.0	320.0
2.5°	324.7	323.8	322.6	320.9	319.0	317.8	317.3	316.9	316.9
5°	331.6	329.9	327.3	323.8	321.7	320.4	319.0	318.3	318.3
7.5°	336.4	334.7	330.7	326.0	323.0	320.4	318.7	317.3	317.3
10°	338.6	336.4	331.6	325.6	320.9	317.3	314.7	313.9	313.9
12.5°	341.2	338.6	332.1	324.3	318.3	313.9	311.3	310.4	310.4
15°	343.8	340.7	332.6	323.5	315.6	310.4	308.3	307.8	307.8
17.5°	342.4	338.6	329.0	318.3	309.6	304.4	302.3	302.3	302.7
20°	335.5	331.6	320.9	308.7	299.6	295.8	294.1	294.9	295.8
22.5°	325.2	320.4	308.7	297.0	287.5	284.1	284.1	285.3	286.7
25°	312.2	307.8	296.6	283.6	274.6	271.9	272.9	275.0	276.7
27.5°	297.5	292.7	281.0	269.0	259.9	258.6	260.7	263.8	264.6
30°	277.6	273.6	263.8	252.1	244.3	243.9	246.9	249.0	251.2
32.5°	258.6	254.2	244.7	233.5	227.9	228.2	231.8	234.4	235.6
35°	236.5	232.7	225.8	216.7	211.5	212.4	216.2	218.8	219.2
37.5°	215.8	213.2	206.2	199.3	195.4	197.1	200.7	203.6	203.6
40°	195.0	192.8	187.6	182.1	179.9	182.1	185.5	188.1	188.1
42.5°	175.1	173.8	169.5	165.6	164.3	167.3	170.4	172.5	172.1
45°	157.4	156.1	153.1	150.0	149.6	152.7	155.3	156.5	157.0
47.5°	141.4	140.5	137.9	135.7	135.7	138.8	141.0	142.2	142.7
50°	126.7	125.9	123.7	121.9	122.4	125.4	127.1	128.4	128.8
52.5°	112.0	111.6	109.9	107.7	109.0	111.1	113.3	114.2	114.6
55°	99.4	99.4	97.3	95.6	96.5	98.6	99.9	100.3	100.3
57.5°	88.2	87.7	85.1	83.4	83.9	86.0	86.9	87.4	87.4
60°	77.4	77.0	74.3	71.7	71.7	73.1	73.5	73.9	73.9
62.5°	67.0	66.6	63.6	61.4	60.5	60.2	60.2	60.9	62.7
65°	57.5	57.1	54.0	50.6	49.3	48.0	46.6	47.6	48.5
67.5°	48.8	48.0	44.9	42.0	38.9	36.8	34.6	35.9	37.6
70°	40.6	39.7	36.3	32.9	29.4	26.0	24.2	26.0	26.8
72.5°	32.9	32.0	28.5	25.1	20.8	17.3	16.9	17.3	17.7
75°	25.5	25.1	21.6	17.7	13.4	10.8	10.8	10.8	10.8
77.5°	19.1	18.2	14.8	11.2	7.8	6.0	5.7	5.7	5.7
80°	12.9	12.1	9.1	6.5	3.4	2.6	2.6	2.2	2.2
82.5°	7.4	6.9	4.8	2.6	1.2	0.9	0.9	0.9	0.9
85°	3.1	2.6	1.7	0.9	0.5	0.5	0.5	0.5	0.5
87.5°	0.5	0.5	0.5	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°    - - 45°-225°    - - - - 90°-270°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)