

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581008

Luminaire Tested: **HCC4W05D010SL-HM40525830-41WWBB**

Issue Date: 9/9/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P581008  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-17)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC4W05D010SL-HM40525830-41WWBB  
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WALLWASH DISTRIBUTION, WHITE BAFFLE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 525.0 lumens  
Efficiency: N/A  
Efficacy: 87.5 lumens/watt  
Spacing Criteria (0/90/45): 1.11 / 1.04 / 1.12  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 6  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P581008  
CATALOG NUMBER: HCC4W05D010SL-HM40525830-41WWBB

### Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P581008

CATALOG NUMBER: HCC4W05D010SL-HM40525830-41WWBB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20										
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	108	104	101	109	105	102	100	101	99	97	97	95	94	94	92	91	89								
2	103	97	91	87	101	95	90	86	92	87	84	88	85	82	85	83	80	78								
3	96	87	80	75	94	86	79	74	83	78	73	80	76	72	78	74	71	69								
4	89	79	72	66	87	78	71	65	75	69	65	73	68	64	71	67	63	61								
5	83	72	64	58	81	71	64	58	69	62	58	67	61	57	65	60	56	55								
6	77	66	58	52	75	65	57	52	63	57	52	61	56	51	60	55	51	49								
7	72	60	53	47	71	59	52	47	58	51	47	57	51	46	55	50	46	44								
8	68	56	48	43	66	55	48	43	54	47	42	53	47	42	51	46	42	40								
9	64	52	44	39	62	51	44	39	50	43	39	49	43	39	48	43	39	37								
10	60	48	41	36	59	47	41	36	46	40	36	46	40	36	45	39	36	34								

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	37497	37497	37497
5°	39720	37368	35486
10°	41370	36760	33404
15°	42944	35883	31413
20°	43356	34167	29048
25°	41959	31588	26593
30°	39224	28628	24198
35°	34949	25448	21743
40°	30561	22124	19354
45°	26602	18769	16746
50°	23219	15927	14354
55°	20365	13204	11613
60°	17811	10657	8536
65°	15498	7939	4816
70°	13560	5157	1551
75°	11152	2716	429
80°	8311	1208	355
85°	4812	708	708



TEST NUMBER: P581008  
 CATALOG NUMBER: HCC4W05D010SL-HM40525830-41WWBB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	28.7	5.5
10°-20°	80.3	15.3
20°-30°	111.0	21.1
30°-40°	111.6	21.3
40°-50°	90.1	17.2
50°-60°	60.9	11.6
60°-70°	31.0	5.9
70°-80°	9.9	1.9
80°-90°	1.5	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	219.9	41.9
0°-40°	331.6	63.2
0°-60°	482.5	91.9
0°-90°	525.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	525.0	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	304	304	304	304	304	
5°	321	315	302	291	287	31
15°	336	318	281	254	246	95
25°	308	282	232	204	195	141
35°	232	210	169	148	144	145
45°	152	137	108	96	96	118
55°	95	82	61	54	54	85
65°	53	43	27	18	16	53
75°	23	16	6	1	1	25
85°	3	2	0	0	0	5
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P581008

CATALOG NUMBER: HCC4W05D010SL-HM40525830-41WWBB

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	304.0	304.0	304.0	304.0	304.0	304.0	304.0	304.0	304.0
2.5°	312.1	310.4	308.6	305.7	302.1	298.7	296.6	294.9	294.0
5°	320.8	318.6	314.7	308.3	301.8	295.7	290.9	287.9	286.6
7.5°	327.7	324.6	318.1	309.1	299.2	289.7	283.6	279.2	277.5
10°	330.3	326.8	318.1	306.1	293.5	281.8	273.2	268.9	266.7
12.5°	333.3	329.4	318.6	303.5	287.9	274.1	264.1	258.6	256.4
15°	336.3	331.2	318.1	299.5	281.0	265.0	254.2	248.6	246.0
17.5°	336.3	330.3	314.7	293.1	271.9	255.0	243.0	236.4	234.3
20°	330.3	323.4	306.4	282.7	260.3	242.1	230.4	223.9	221.3
22.5°	320.8	313.0	294.9	270.1	246.4	228.7	217.0	211.0	208.4
25°	308.3	300.4	281.5	255.9	232.1	214.4	203.6	197.9	195.4
27.5°	293.5	284.9	265.8	240.4	217.0	200.1	190.2	185.0	182.8
30°	275.4	267.2	248.6	223.5	201.0	185.5	176.4	171.6	169.9
32.5°	254.2	247.3	229.2	205.8	184.6	170.4	162.1	158.2	156.5
35°	232.1	225.6	209.6	188.1	169.0	155.6	147.9	145.3	144.4
37.5°	211.3	205.8	190.2	170.4	153.0	141.3	134.5	132.7	131.9
40°	189.8	185.9	171.6	153.5	137.4	127.1	121.4	120.2	120.2
42.5°	170.4	166.1	153.5	137.0	122.8	112.4	108.5	107.3	107.6
45°	152.5	148.2	136.7	121.4	107.6	99.0	96.0	96.0	96.0
47.5°	136.2	132.2	121.4	105.9	94.7	87.7	84.8	84.8	85.1
50°	121.0	118.5	106.3	93.0	83.0	76.5	74.3	73.9	74.8
52.5°	106.8	103.7	93.0	80.8	71.3	66.2	64.0	63.6	64.0
55°	94.7	91.3	81.7	70.0	61.4	56.2	53.6	53.1	54.0
57.5°	83.0	80.4	70.5	60.0	51.9	46.6	44.5	43.7	44.0
60°	72.2	69.6	60.5	50.6	43.2	38.0	35.1	34.2	34.6
62.5°	62.2	60.0	51.4	41.9	34.6	29.9	26.8	24.6	25.5
65°	53.1	51.0	43.2	33.7	27.2	22.0	17.7	16.0	16.5
67.5°	45.4	42.8	35.4	26.8	20.3	14.6	10.0	9.1	9.1
70°	37.6	35.1	28.5	20.8	14.3	7.8	4.3	4.3	4.3
72.5°	30.3	28.1	22.0	15.5	9.1	3.4	1.7	1.7	1.7
75°	23.4	21.6	16.5	10.8	5.7	1.7	1.2	0.9	0.9
77.5°	17.3	15.5	11.7	7.4	3.4	0.9	0.9	0.9	0.9
80°	11.7	10.3	7.8	4.3	1.7	0.5	0.5	0.5	0.5
82.5°	6.9	6.0	4.3	2.2	0.9	0.5	0.5	0.5	0.5
85°	3.4	2.6	1.7	0.9	0.5	0.5	0.5	0.5	0.5
87.5°	0.9	0.5	0.5	0.5	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°    - - 45°-225°    - - - - 90°-270°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)