

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581080

Luminaire Tested: **HCC4W05D010MW-HM40525930-41WWBB**

Issue Date: 9/9/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P581080  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-17)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC4W05D010MW-HM40525930-41WWBB  
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WALLWASH DISTRIBUTION, WHITE BAFFLE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 461.3 lumens  
Efficiency: N/A  
Efficacy: 76.9 lumens/watt  
Spacing Criteria (0/90/45): 1.11 / 1.04 / 1.12  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 6  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P581080  
CATALOG NUMBER: HCC4W05D010MW-HM40525930-41WWBB

### Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P581080

CATALOG NUMBER: HCC4W05D010MW-HM40525930-41WWBB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20				
RC	80					70					50					30				
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	111	108	104	101	109	105	102	100	101	99	97	97	95	94	94	92	91	89		
2	103	97	91	87	101	95	90	86	92	87	84	88	85	82	86	83	80	78		
3	96	87	80	75	94	86	79	74	83	78	73	80	76	72	78	74	71	69		
4	89	79	72	66	87	78	71	65	75	69	65	73	68	64	71	67	63	61		
5	83	72	64	58	81	71	64	58	69	62	58	67	61	57	65	60	56	55		
6	77	66	58	52	75	65	57	52	63	57	52	61	56	51	60	55	51	49		
7	72	60	53	47	71	60	52	47	58	51	47	57	51	46	55	50	46	44		
8	68	56	48	43	66	55	48	43	54	47	43	53	47	42	51	46	42	40		
9	64	52	44	39	62	51	44	39	50	43	39	49	43	39	48	43	39	37		
10	60	48	41	36	59	47	41	36	47	40	36	46	40	36	45	39	36	34		

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	32946	32946	32946
5°	34904	32824	31189
10°	36347	32314	29358
15°	37747	31541	27608
20°	38092	30020	25530
25°	36869	27764	23368
30°	34467	25153	21264
35°	30718	22376	19108
40°	26841	19451	17019
45°	23409	16484	14705
50°	20398	14008	12607
55°	17892	11591	10193
60°	15640	9374	7499
65°	13659	6975	4203
70°	11901	4508	1334
75°	9770	2383	381
80°	7245	1065	213
85°	4387	425	425



TEST NUMBER: P581080

CATALOG NUMBER: HCC4W05D010MW-HM40525930-41WWBB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	25.2	5.5
10°-20°	70.5	15.3
20°-30°	97.5	21.1
30°-40°	98.1	21.3
40°-50°	79.1	17.2
50°-60°	53.5	11.6
60°-70°	27.2	5.9
70°-80°	8.7	1.9
80°-90°	1.3	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	193.3	41.9
0°-40°	291.4	63.2
0°-60°	424.0	91.9
0°-90°	461.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	461.3	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	267	267	267	267	267	
5°	282	277	265	256	252	27
15°	296	280	247	223	216	83
25°	271	247	204	179	172	124
35°	204	184	149	130	127	127
45°	134	120	94	84	84	104
55°	83	72	54	47	47	75
65°	47	38	24	16	14	47
75°	20	14	5	1	1	22
85°	3	2	0	0	0	4
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P581080

CATALOG NUMBER: HCC4W05D010MW-HM40525930-41WWBB

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	267.1	267.1	267.1	267.1	267.1	267.1	267.1	267.1	267.1
2.5°	274.3	272.7	271.3	268.5	265.6	262.5	260.6	259.1	258.3
5°	281.9	280.0	276.6	270.9	265.1	259.8	255.7	253.0	251.9
7.5°	287.9	285.3	279.7	271.6	262.9	254.6	249.2	245.4	243.9
10°	290.2	287.2	279.7	269.0	258.0	247.7	240.1	236.3	234.4
12.5°	292.9	289.5	280.0	266.7	253.0	240.8	232.1	227.2	225.3
15°	295.6	291.0	279.7	263.3	247.0	232.9	223.4	218.5	216.2
17.5°	295.6	290.2	276.6	257.5	238.9	224.2	213.5	207.8	205.9
20°	290.2	284.2	269.3	248.5	228.7	212.7	202.5	196.8	194.5
22.5°	281.9	275.0	259.1	237.4	216.6	201.0	190.7	185.3	183.1
25°	270.9	264.0	247.3	225.0	204.0	188.4	179.0	174.0	171.7
27.5°	258.0	250.4	233.7	211.2	190.7	175.9	167.2	162.6	160.7
30°	242.0	234.8	218.5	196.4	176.6	163.0	155.0	150.8	149.3
32.5°	223.4	217.4	201.3	180.8	162.2	149.7	142.4	139.0	137.6
35°	204.0	198.3	184.2	165.3	148.6	136.8	130.0	127.7	126.9
37.5°	185.8	180.8	167.2	149.7	134.5	124.3	118.2	116.7	115.9
40°	166.7	163.3	150.8	134.8	120.8	111.7	106.8	105.7	105.7
42.5°	149.7	145.8	134.8	120.4	107.9	98.7	95.3	94.2	94.5
45°	134.2	130.3	120.1	106.8	94.5	87.1	84.3	84.3	84.3
47.5°	119.6	116.2	106.8	93.1	83.2	77.1	74.5	74.5	74.8
50°	106.3	104.1	93.4	81.7	73.0	67.2	65.4	64.9	65.7
52.5°	93.9	91.1	81.7	71.1	62.7	58.1	56.2	55.8	56.2
55°	83.2	80.1	71.8	61.5	53.9	49.4	47.1	46.8	47.4
57.5°	73.0	70.7	62.0	52.8	45.6	41.0	39.2	38.4	38.7
60°	63.4	61.2	53.2	44.5	38.0	33.5	30.8	30.0	30.4
62.5°	54.7	52.8	45.2	36.9	30.4	26.2	23.6	21.7	22.4
65°	46.8	44.8	38.0	29.6	23.9	19.4	15.5	14.1	14.4
67.5°	39.8	37.6	31.1	23.6	17.8	12.9	8.7	7.9	7.9
70°	33.0	30.8	25.1	18.3	12.5	6.8	3.7	3.7	3.7
72.5°	26.6	24.7	19.4	13.6	7.9	3.1	1.5	1.5	1.5
75°	20.5	19.0	14.4	9.5	5.0	1.5	1.1	0.8	0.8
77.5°	15.2	13.6	10.2	6.5	3.1	0.8	0.8	0.8	0.8
80°	10.2	9.1	6.8	3.7	1.5	0.3	0.3	0.3	0.3
82.5°	6.1	5.3	3.7	1.9	0.8	0.3	0.3	0.3	0.3
85°	3.1	2.3	1.5	0.8	0.3	0.3	0.3	0.3	0.3
87.5°	0.8	0.3	0.3	0.3	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°    - - 45°-225°    - - - - 90°-270°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)