

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581099

Luminaire Tested: **HCC4S05D010MB-HM40525935-41WWW**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P581099
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4S05D010MB-HM40525935-41WWW
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WALLWASH DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 607.6 lumens
Efficiency: N/A
Efficacy: 101.3 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.03 / 1.1
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P581099
CATALOG NUMBER: HCC4S05D010MB-HM40525935-41WWW

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P581099

CATALOG NUMBER: HCC4S05D010MB-HM40525935-41WWW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	111	106	103	100	108	104	101	98	100	97	95	96	94	92	93	91	89	87					87			
2	102	95	89	84	100	93	88	83	90	85	81	87	83	80	84	81	78	76					76			
3	94	85	78	72	92	84	77	72	81	75	71	78	73	69	76	72	68	66					66			
4	87	77	69	63	85	76	68	63	73	67	62	71	66	61	69	64	60	58					58			
5	81	70	62	56	79	69	61	56	67	60	55	65	59	54	63	58	54	52					52			
6	76	64	56	50	74	63	55	50	61	54	49	59	53	49	58	53	48	47					47			
7	71	58	50	45	69	58	50	45	56	49	44	55	49	44	53	48	44	42					42			
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38					38			
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35					35			
10	59	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32					32			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	41975	41975	41975
5°	43819	41776	39857
10°	44927	40919	37349
15°	45856	39816	34657
20°	45600	37882	31739
25°	43701	35031	28866
30°	40364	31989	26178
35°	35371	28459	23686
40°	30819	25135	21335
45°	26811	21909	19066
50°	23891	18901	16810
55°	21354	16623	14537
60°	19069	14505	12532
65°	16928	12725	11937
70°	14858	10963	11144
75°	12581	9341	10294
80°	9660	7956	9376
85°	5661	6227	7925



TEST NUMBER: P581099
 CATALOG NUMBER: HCC4S05D010MB-HM40525935-41WWW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	31.9	5.2
10°-20°	88.0	14.5
20°-30°	120.2	19.8
30°-40°	120.7	19.9
40°-50°	99.8	16.4
50°-60°	72.3	11.9
60°-70°	45.8	7.5
70°-80°	23.2	3.8
80°-90°	5.7	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	240.1	39.5
0°-40°	360.8	59.4
0°-60°	532.9	87.7
0°-90°	607.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	607.6	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	340	340	340	340	340	
5°	354	349	337	326	322	34
15°	359	345	312	283	271	101
25°	321	300	257	225	212	147
35°	235	221	189	166	157	147
45°	154	145	126	113	109	120
55°	99	90	77	70	68	89
65°	58	52	44	39	41	58
75°	26	23	20	20	22	28
85°	4	4	4	5	6	6
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P581099

CATALOG NUMBER: HCC4S05D010MB-HM40525935-41WWW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	340.3	340.3	340.3	340.3	340.3	340.3	340.3	340.3	340.3
2.5°	346.6	345.5	343.5	341.1	338.2	335.1	332.2	330.6	329.8
5°	353.9	352.3	348.7	343.5	337.4	331.4	326.2	323.0	321.9
7.5°	358.3	355.8	350.6	342.7	333.5	324.6	317.0	312.6	311.4
10°	358.7	355.8	349.0	338.2	326.7	315.1	305.8	299.4	298.2
12.5°	359.1	355.5	347.1	334.3	319.8	305.4	294.2	286.6	284.7
15°	359.1	355.5	345.0	329.8	311.8	295.4	283.0	274.2	271.4
17.5°	355.8	351.8	339.5	321.9	302.3	283.9	269.4	260.1	257.4
20°	347.4	343.0	329.0	309.9	288.6	269.4	255.0	245.4	241.8
22.5°	335.4	330.3	315.4	294.6	273.4	253.8	239.8	229.7	226.5
25°	321.1	315.9	299.9	279.4	257.4	239.0	225.0	215.8	212.1
27.5°	303.4	297.8	282.2	261.8	241.4	222.9	210.2	201.8	198.2
30°	283.4	277.4	262.6	243.0	224.6	206.9	194.5	187.7	183.8
32.5°	260.1	255.0	241.8	224.2	206.9	190.1	179.8	173.8	170.5
35°	234.9	232.2	221.0	205.8	189.0	174.9	165.7	160.1	157.3
37.5°	212.6	209.7	200.1	187.4	172.5	159.7	152.1	147.3	144.9
40°	191.4	189.0	179.8	168.9	156.1	144.9	138.5	135.0	132.5
42.5°	170.5	169.3	161.7	151.7	140.5	130.9	125.6	122.9	120.9
45°	153.7	152.1	144.9	135.3	125.6	117.7	113.3	111.2	109.3
47.5°	138.9	136.9	129.3	120.9	112.1	104.9	100.9	98.9	98.1
50°	124.5	122.5	115.7	107.3	98.5	93.3	90.1	88.1	87.6
52.5°	111.7	109.6	102.0	94.1	87.3	82.9	80.0	78.1	77.3
55°	99.3	96.8	90.5	82.9	77.3	73.2	70.5	68.4	67.6
57.5°	88.1	85.7	80.0	72.9	67.6	64.0	61.6	59.6	58.8
60°	77.3	75.3	70.0	63.2	58.8	55.6	53.2	51.6	50.8
62.5°	67.3	65.6	60.5	54.5	50.8	48.0	46.1	44.4	45.3
65°	58.0	56.4	51.6	46.4	43.6	40.9	39.3	39.3	40.9
67.5°	49.3	47.7	43.6	39.3	36.8	34.8	33.6	34.8	36.0
70°	41.2	39.6	36.0	32.5	30.4	28.8	28.8	30.1	30.9
72.5°	33.6	32.0	29.2	26.4	24.9	23.6	24.9	25.7	26.4
75°	26.4	25.2	22.8	20.8	19.6	19.2	20.4	21.2	21.6
77.5°	19.6	18.8	17.3	15.7	14.8	15.2	16.5	16.8	17.3
80°	13.6	13.2	12.0	11.2	11.2	11.6	12.4	12.8	13.2
82.5°	8.4	8.4	7.6	7.2	7.6	8.4	8.9	9.2	9.2
85°	4.0	4.4	4.0	4.0	4.4	5.2	5.2	5.6	5.6
87.5°	1.2	1.2	1.6	1.6	2.0	2.0	2.0	2.0	2.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)