

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581100

Luminaire Tested: **HCC4W05D010BZ-HM40525935-41WWWB**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P581100
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-18)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4W05D010BZ-HM40525935-41WWWB
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WALLWASH DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 604.9 lumens
Efficiency: N/A
Efficacy: 100.8 lumens/watt
Spacing Criteria (0/90/45): 1.13 / 1.07 / 1.15
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P581100
CATALOG NUMBER: HCC4W05D010BZ-HM40525935-41WWWB

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P581100

CATALOG NUMBER: HCC4W05D010BZ-HM40525935-41WWWB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20										
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	92	91	89	87								
2	102	95	89	84	99	93	87	83	89	85	81	86	82	79	83	80	77	75								
3	94	85	77	72	92	83	76	71	80	75	70	78	73	69	75	71	68	66								
4	87	76	68	62	85	75	68	62	72	66	61	70	65	60	68	63	60	58								
5	81	69	61	55	79	68	60	55	66	59	54	64	58	53	62	57	53	51								
6	75	63	55	49	73	62	54	49	60	53	48	59	53	48	57	52	47	46								
7	70	58	50	44	68	57	49	44	55	48	43	54	48	43	53	47	43	41								
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37								
9	61	49	41	36	60	48	41	36	47	41	36	46	40	36	45	40	36	34								
10	58	45	38	33	57	45	38	33	44	38	33	43	37	33	42	37	33	31								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	38472	38472	38472
5°	40451	38420	36972
10°	41871	37950	35295
15°	43149	37262	33801
20°	43185	35743	31857
25°	41564	33398	29860
30°	38598	30736	27887
35°	34603	27676	25809
40°	30352	24684	23847
45°	26532	21857	21997
50°	23430	19132	19822
55°	20666	16967	17827
60°	18477	14999	15591
65°	16373	13221	13221
70°	14281	11252	11252
75°	12248	9531	10723
80°	9660	8524	9660
85°	6227	7359	9057



TEST NUMBER: P581100
 CATALOG NUMBER: HCC4W05D010BZ-HM40525935-41WWWB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	29.5	4.9
10°-20°	83.2	13.8
20°-30°	116.6	19.3
30°-40°	120.1	19.9
40°-50°	102.3	16.9
50°-60°	75.8	12.5
60°-70°	47.6	7.9
70°-80°	23.6	3.9
80°-90°	6.2	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	229.3	37.9
0°-40°	349.4	57.8
0°-60°	527.5	87.2
0°-90°	604.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	604.9	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	312	312	312	312	312	
5°	327	321	310	302	299	31
15°	338	323	292	271	265	95
25°	305	284	245	224	219	140
35°	230	213	184	172	171	143
45°	152	142	125	123	126	118
55°	96	88	79	80	83	87
65°	56	50	45	44	45	56
75°	26	23	20	22	22	27
85°	4	4	5	6	6	6
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P581100

CATALOG NUMBER: HCC4W05D010BZ-HM40525935-41WWWB

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	311.9	311.9	311.9	311.9	311.9	311.9	311.9	311.9	311.9
2.5°	318.7	317.5	315.9	313.0	310.3	307.8	305.4	304.3	303.8
5°	326.7	324.3	321.1	315.9	310.3	305.4	301.5	299.4	298.6
7.5°	332.3	329.8	324.7	316.7	308.7	301.5	295.1	292.3	291.5
10°	334.3	331.5	324.3	313.5	303.0	294.3	287.0	283.4	281.8
12.5°	335.8	332.3	323.0	310.3	297.5	286.7	279.0	274.2	273.1
15°	337.9	333.9	322.7	307.0	291.8	279.0	270.6	266.3	264.7
17.5°	335.8	331.5	318.3	300.7	283.4	269.4	260.3	256.2	254.6
20°	329.0	324.3	309.5	290.7	272.3	257.9	248.6	244.6	242.7
22.5°	318.7	313.5	298.3	278.2	259.5	245.4	236.6	232.6	231.4
25°	305.4	300.2	284.2	263.8	245.4	231.8	224.2	220.6	219.4
27.5°	289.9	284.7	269.0	249.0	231.4	218.6	212.6	209.0	208.2
30°	271.0	265.8	250.6	232.2	215.8	203.7	199.0	196.1	195.8
32.5°	250.3	245.8	231.8	215.0	199.4	189.3	185.8	183.8	183.3
35°	229.8	225.0	212.6	197.4	183.8	174.9	171.7	171.4	171.4
37.5°	209.0	204.2	194.2	180.1	168.5	160.5	159.4	159.7	159.7
40°	188.5	184.2	175.4	163.8	153.3	147.3	146.9	147.8	148.1
42.5°	169.3	165.7	157.8	147.8	138.9	134.2	134.5	136.1	137.3
45°	152.1	148.9	141.8	132.9	125.3	121.7	122.9	124.8	126.1
47.5°	136.5	133.7	126.9	118.9	112.5	110.1	111.7	114.1	115.7
50°	122.1	119.7	113.3	104.9	99.7	98.1	100.1	102.5	103.3
52.5°	109.3	106.9	100.1	92.8	88.9	88.1	90.1	92.0	93.3
55°	96.1	94.1	88.5	82.1	78.9	78.4	80.5	82.1	82.9
57.5°	85.2	83.3	78.1	72.4	69.7	69.2	71.3	72.4	72.9
60°	74.9	72.9	68.1	62.9	60.8	60.8	62.1	62.9	63.2
62.5°	65.3	63.2	58.9	54.5	52.9	52.9	52.9	53.2	54.5
65°	56.1	54.5	50.4	46.4	45.3	44.5	44.5	44.5	45.3
67.5°	47.7	46.1	42.8	39.3	38.0	36.9	36.4	37.2	37.2
70°	39.6	38.5	35.2	32.5	31.2	30.1	29.6	31.2	31.2
72.5°	32.5	31.2	29.2	26.4	25.2	24.9	25.7	26.4	26.8
75°	25.7	24.4	22.8	21.2	20.0	20.4	21.6	22.0	22.5
77.5°	19.2	18.8	17.3	16.0	16.0	16.5	17.3	18.0	18.4
80°	13.6	13.2	12.4	11.6	12.0	12.8	13.2	14.0	13.6
82.5°	8.4	8.4	8.1	8.1	8.4	9.2	9.6	10.0	10.4
85°	4.4	4.4	4.4	4.8	5.2	5.6	6.0	6.4	6.4
87.5°	1.2	1.6	1.6	2.0	2.4	2.4	2.8	2.8	2.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)