

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581097

Luminaire Tested: **HCC4W05D010SL-HM40525935-41RWWH**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P581097
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-15)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4W05D010SL-HM40525935-41RWWH
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WALLWASH DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 614.1 lumens
Efficiency: N/A
Efficacy: 102.3 lumens/watt
Spacing Criteria (0/90/45): 1.14 / 1.08 / 1.16
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P581097
CATALOG NUMBER: HCC4W05D010SL-HM40525935-41RWWH

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P581097

CATALOG NUMBER: HCC4W05D010SL-HM40525935-41RWWH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20				
RC	80					70					50					30				
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	111	107	104	100	108	105	102	99	101	98	96	97	95	93	93	92	90	88		
2	103	96	90	85	100	94	89	84	90	86	82	87	84	80	84	81	79	77		
3	95	86	79	73	92	84	78	73	81	76	71	79	74	70	76	72	69	67		
4	88	77	70	64	86	76	69	63	74	67	62	71	66	62	69	65	61	59		
5	81	70	62	56	79	69	61	56	67	60	55	65	59	55	63	58	54	52		
6	76	64	56	50	74	63	55	50	61	54	49	60	54	49	58	53	49	47		
7	71	58	51	45	69	58	50	45	56	49	45	55	49	44	54	48	44	42		
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38		
9	62	50	42	37	61	49	42	37	48	41	37	47	41	37	46	41	37	35		
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	39730	39730	39730
5°	40785	39745	39002
10°	41708	39391	37838
15°	42868	38845	36841
20°	42752	37344	35349
25°	40952	34977	33657
30°	37686	32203	31861
35°	33142	29227	29468
40°	28677	26149	27244
45°	24927	23235	24648
50°	22106	20494	21895
55°	19634	17978	18774
60°	17466	15591	15591
65°	15527	12959	12171
70°	13416	9809	8691
75°	11247	6481	5338
80°	8524	3125	2841
85°	4529	1132	1132



TEST NUMBER: P581097
 CATALOG NUMBER: HCC4W05D010SL-HM40525935-41RWWH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	30.5	5.0
10°-20°	86.5	14.1
20°-30°	122.0	19.9
30°-40°	126.0	20.5
40°-50°	106.8	17.4
50°-60°	77.7	12.7
60°-70°	45.4	7.4
70°-80°	16.9	2.7
80°-90°	2.2	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	239.0	38.9
0°-40°	365.0	59.4
0°-60°	549.5	89.5
0°-90°	614.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	614.1	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	322	322	322	322	322	
5°	329	326	321	316	315	32
15°	336	325	304	291	288	94
25°	301	284	257	248	247	138
35°	220	210	194	194	196	137
45°	143	139	133	138	141	111
55°	91	87	84	86	87	82
65°	53	49	44	42	42	53
75°	24	20	14	11	11	25
85°	3	2	1	1	1	4
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P581097

CATALOG NUMBER: HCC4W05D010SL-HM40525935-41RWWH

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	322.1	322.1	322.1	322.1	322.1	322.1	322.1	322.1	322.1
2.5°	325.0	324.2	323.4	322.1	320.5	319.4	318.1	317.3	317.3
5°	329.4	328.1	326.5	323.7	321.0	318.6	316.1	315.0	315.0
7.5°	332.6	331.0	327.8	323.7	318.9	315.3	311.8	310.2	309.3
10°	333.0	331.3	327.0	321.0	314.5	308.9	305.0	302.6	302.1
12.5°	333.8	331.8	326.2	317.8	309.3	302.6	298.2	295.8	295.0
15°	335.7	333.0	325.4	314.5	304.2	296.1	291.4	289.3	288.5
17.5°	333.8	329.7	320.5	307.7	296.1	287.4	282.5	280.6	280.6
20°	325.7	321.8	311.0	296.9	284.5	276.1	271.4	270.1	269.3
22.5°	314.5	310.2	298.5	283.8	271.4	263.8	260.5	258.9	258.6
25°	300.9	296.6	284.1	268.9	257.0	250.5	247.8	247.8	247.3
27.5°	285.7	280.1	267.3	254.1	242.5	237.7	236.5	236.5	236.9
30°	264.6	260.5	249.7	236.9	226.1	222.9	222.9	223.7	223.7
32.5°	241.8	238.9	229.3	218.1	209.7	207.7	208.5	210.1	210.5
35°	220.1	216.9	210.5	200.4	194.1	193.3	194.5	195.7	195.7
37.5°	198.9	195.7	191.2	183.3	178.5	178.9	180.5	182.1	183.3
40°	178.1	175.7	172.5	166.1	162.4	164.1	166.1	167.6	169.2
42.5°	159.7	157.3	154.9	150.0	147.7	149.7	152.1	153.7	155.3
45°	142.9	141.3	138.8	134.8	133.2	135.3	138.0	139.7	141.3
47.5°	128.5	127.7	124.5	120.9	120.1	122.0	124.5	126.4	127.7
50°	115.2	114.1	111.2	107.6	106.8	110.1	111.7	112.8	114.1
52.5°	102.5	101.2	98.1	94.9	94.9	97.3	98.4	98.9	100.0
55°	91.3	90.0	86.8	84.4	83.6	85.7	86.5	86.5	87.3
57.5°	80.8	79.7	76.4	73.7	73.2	74.5	74.5	74.5	74.8
60°	70.8	69.6	66.4	64.0	63.2	63.7	63.2	62.9	63.2
62.5°	61.6	60.4	57.2	54.5	53.6	53.6	52.4	52.0	52.4
65°	53.2	51.2	48.8	46.0	44.4	43.2	41.7	41.7	41.7
67.5°	44.8	43.2	40.4	37.6	35.6	33.6	31.2	32.0	32.5
70°	37.2	36.0	32.8	30.0	27.2	24.9	22.8	23.6	24.1
72.5°	30.4	28.8	26.0	22.8	20.4	17.3	16.0	16.8	16.8
75°	23.6	22.0	19.6	16.5	13.6	10.8	10.8	11.2	11.2
77.5°	17.6	16.0	13.6	10.8	8.4	6.4	6.8	6.8	6.8
80°	12.0	10.8	8.9	6.4	4.4	3.6	3.6	3.6	4.0
82.5°	6.8	6.0	4.8	3.2	2.0	2.0	2.0	2.0	2.0
85°	3.2	2.4	2.0	1.2	0.8	0.8	0.8	0.8	0.8
87.5°	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)