

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581098

Luminaire Tested: **HCC4W05D010SL-HM40525935-41WWBB**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P581098
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-17)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4W05D010SL-HM40525935-41WWBB
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WALLWASH DISTRIBUTION, WHITE BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 486.0 lumens
Efficiency: N/A
Efficacy: 81.0 lumens/watt
Spacing Criteria (0/90/45): 1.11 / 1.04 / 1.12
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P581098
CATALOG NUMBER: HCC4W05D010SL-HM40525935-41WWBB

Luminous Intensity Polar Plot





TEST NUMBER: P581098

CATALOG NUMBER: HCC4W05D010SL-HM40525935-41WWBB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20										
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	108	104	101	109	105	102	100	101	99	97	97	95	94	94	92	91	89								
2	103	97	91	87	101	95	90	86	92	87	84	88	85	82	85	83	80	78								
3	96	87	80	75	94	86	79	74	83	78	73	80	76	72	78	74	71	69								
4	89	79	72	66	87	78	71	65	75	69	65	73	68	64	71	67	63	61								
5	83	72	64	58	81	71	64	58	69	62	58	67	61	57	65	60	56	55								
6	77	66	58	52	75	65	57	52	63	57	52	61	56	51	60	55	51	49								
7	72	60	53	47	71	59	52	47	58	51	47	57	51	46	55	50	46	44								
8	68	56	48	43	66	55	48	43	54	47	42	53	47	42	51	46	42	40								
9	64	52	44	39	62	51	44	39	50	43	39	49	43	39	48	43	39	37								
10	60	48	41	36	59	47	41	36	46	40	36	46	40	36	45	39	36	34								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	34709	34709	34709
5°	36761	34582	32861
10°	38301	34030	30924
15°	39752	33214	29077
20°	40140	31634	26896
25°	38828	29247	24620
30°	36305	26491	22404
35°	32359	23565	20132
40°	28291	20481	17905
45°	24648	17391	15507
50°	21492	14737	13279
55°	18838	12236	10774
60°	16504	9892	7894
65°	14389	7355	4436
70°	12550	4760	1443
75°	10294	2478	381
80°	7671	1137	355
85°	4529	708	708



TEST NUMBER: P581098
 CATALOG NUMBER: HCC4W05D010SL-HM40525935-41WWBB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	26.6	5.5
10°-20°	74.3	15.3
20°-30°	102.7	21.1
30°-40°	103.3	21.3
40°-50°	83.4	17.2
50°-60°	56.4	11.6
60°-70°	28.7	5.9
70°-80°	9.2	1.9
80°-90°	1.4	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	203.6	41.9
0°-40°	306.9	63.2
0°-60°	446.7	91.9
0°-90°	486.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	486.0	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	281	281	281	281	281	
5°	297	291	279	269	265	29
15°	311	294	260	235	228	88
25°	285	260	215	188	181	131
35°	215	194	156	137	134	134
45°	141	126	100	89	89	109
55°	88	76	57	50	50	79
65°	49	40	25	16	15	49
75°	22	15	5	1	1	23
85°	3	2	0	0	0	4
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P581098

CATALOG NUMBER: HCC4W05D010SL-HM40525935-41WWBB

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	281.4	281.4	281.4	281.4	281.4	281.4	281.4	281.4	281.4
2.5°	289.0	287.4	285.7	283.0	279.8	276.5	274.6	273.0	272.2
5°	296.9	295.0	291.4	285.3	279.3	273.8	269.3	266.5	265.4
7.5°	303.4	300.5	294.5	286.1	276.9	268.1	262.5	258.6	257.0
10°	305.8	302.5	294.5	283.3	271.7	260.9	252.9	248.9	246.9
12.5°	308.5	305.0	295.0	280.9	266.5	253.7	244.5	239.3	237.3
15°	311.3	306.6	294.5	277.3	260.1	245.3	235.3	230.1	227.7
17.5°	311.3	305.8	291.4	271.3	251.7	236.1	224.8	218.9	216.9
20°	305.8	299.3	283.8	261.7	241.0	224.0	213.3	207.3	204.9
22.5°	296.9	289.8	273.0	250.2	228.1	211.7	200.9	195.3	192.8
25°	285.3	278.1	260.5	236.9	214.9	198.5	188.5	183.3	180.9
27.5°	271.7	263.7	246.1	222.5	200.9	185.2	176.0	171.3	169.2
30°	254.9	247.3	230.1	206.9	186.0	171.7	163.3	158.9	157.3
32.5°	235.3	228.9	212.1	190.5	170.9	157.7	150.0	146.4	144.8
35°	214.9	208.8	194.1	174.1	156.5	144.0	136.9	134.5	133.7
37.5°	195.7	190.5	176.0	157.7	141.6	130.9	124.5	122.8	122.0
40°	175.7	172.1	158.9	142.1	127.2	117.7	112.5	111.2	111.2
42.5°	157.7	153.7	142.1	126.9	113.6	104.1	100.4	99.2	99.7
45°	141.3	137.2	126.4	112.5	99.7	91.6	88.9	88.9	88.9
47.5°	126.1	122.5	112.5	98.1	87.6	81.3	78.4	78.4	78.9
50°	112.0	109.6	98.4	86.0	76.8	70.8	68.8	68.4	69.2
52.5°	98.9	96.0	86.0	74.8	66.1	61.2	59.2	58.8	59.2
55°	87.6	84.4	75.6	64.8	56.9	52.0	49.6	49.3	50.1
57.5°	76.8	74.5	65.3	55.6	48.0	43.2	41.2	40.4	40.9
60°	66.9	64.5	56.1	46.9	40.1	35.2	32.5	31.7	32.0
62.5°	57.7	55.6	47.7	38.8	32.0	27.6	24.9	22.8	23.6
65°	49.3	47.2	40.1	31.2	25.2	20.4	16.5	14.8	15.2
67.5°	42.0	39.6	32.8	24.9	18.8	13.6	9.2	8.4	8.4
70°	34.8	32.5	26.4	19.2	13.2	7.2	4.0	4.0	4.0
72.5°	28.0	26.0	20.4	14.4	8.4	3.2	1.6	1.6	1.6
75°	21.6	20.0	15.2	10.0	5.2	1.6	1.2	0.8	0.8
77.5°	16.0	14.4	10.8	6.8	3.2	0.8	0.8	0.8	0.8
80°	10.8	9.6	7.2	4.0	1.6	0.5	0.5	0.5	0.5
82.5°	6.4	5.6	4.0	2.0	0.8	0.5	0.5	0.5	0.5
85°	3.2	2.4	1.6	0.8	0.5	0.5	0.5	0.5	0.5
87.5°	0.8	0.5	0.5	0.5	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)