

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581424

Luminaire Tested: **HCC4S07D010BZ-HM40525827-41WWWB**

Issue Date: 9/9/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P581424  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-18)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC4S07D010BZ-HM40525827-41WWWB  
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WALLWASH DISTRIBUTION, BLACK BAFFLE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 797.7 lumens  
Efficiency: N/A  
Efficacy: 99.7 lumens/watt  
Spacing Criteria (0/90/45): 1.13 / 1.07 / 1.15  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P581424  
CATALOG NUMBER: HCC4S07D010BZ-HM40525827-41WWWB

### Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P581424

CATALOG NUMBER: HCC4S07D010BZ-HM40525827-41WWWB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	92	91	89	87								
2	102	95	89	84	99	93	87	83	89	85	81	86	82	79	83	80	77	75								
3	94	85	77	72	92	83	76	71	80	75	70	78	73	69	75	71	68	66								
4	87	76	68	62	85	75	68	62	72	66	61	70	65	60	68	63	60	58								
5	81	69	61	55	79	68	60	55	66	59	54	64	58	53	62	57	53	51								
6	75	63	55	49	73	62	54	49	60	53	48	59	53	48	57	52	47	46								
7	70	58	50	44	68	57	49	44	55	48	43	54	48	43	53	47	43	41								
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37								
9	61	49	41	36	60	48	41	36	47	41	36	46	40	36	45	40	36	34								
10	58	46	38	33	57	45	38	33	44	38	33	43	37	33	42	37	33	31								

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	50744	50744	50744
5°	53340	50666	48784
10°	55235	50074	46567
15°	56902	49163	44566
20°	56968	47123	42004
25°	54833	44041	39386
30°	50904	40535	36775
35°	45625	36500	34030
40°	40061	32557	31463
45°	34992	28817	29026
50°	30895	25215	26136
55°	27268	22365	23526
60°	24373	19785	20574
65°	21598	17395	17395
70°	18825	14858	14858
75°	16108	12581	14106
80°	12786	11223	12786
85°	8208	9624	11888



TEST NUMBER: P581424  
 CATALOG NUMBER: HCC4S07D010BZ-HM40525827-41WWWB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	39.0	4.9
10°-20°	109.8	13.8
20°-30°	153.8	19.3
30°-40°	158.4	19.9
40°-50°	134.9	16.9
50°-60°	99.9	12.5
60°-70°	62.7	7.9
70°-80°	31.2	3.9
80°-90°	8.2	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	302.5	37.9
0°-40°	460.9	57.8
0°-60°	695.7	87.2
0°-90°	797.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	797.7	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	411	411	411	411	411	
5°	431	423	409	398	394	41
15°	446	426	385	357	349	125
25°	403	375	324	296	289	184
35°	303	280	242	227	226	189
45°	201	187	165	162	166	156
55°	127	117	104	106	109	115
65°	74	67	60	59	60	74
75°	34	30	26	29	30	36
85°	6	6	7	8	8	7
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P581424

CATALOG NUMBER: HCC4S07D010BZ-HM40525827-41WWWB

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	411.4	411.4	411.4	411.4	411.4	411.4	411.4	411.4	411.4
2.5°	420.4	418.8	416.6	413.0	409.2	406.0	402.9	401.4	400.8
5°	430.8	427.8	423.4	416.6	409.2	402.9	397.6	395.0	394.0
7.5°	438.2	435.1	428.2	417.6	407.2	397.6	389.2	385.4	384.4
10°	441.0	437.2	427.8	413.4	399.8	388.1	378.6	373.8	371.8
12.5°	443.0	438.2	426.2	409.2	392.4	378.0	368.0	361.7	360.2
15°	445.6	440.4	425.6	405.0	385.0	368.0	357.0	351.2	349.0
17.5°	443.0	437.2	419.8	396.6	373.8	355.4	343.2	338.0	335.8
20°	434.0	427.8	408.2	383.4	359.0	340.0	328.0	322.6	320.0
22.5°	420.4	413.4	393.4	367.0	342.2	323.6	312.0	306.8	305.2
25°	402.9	396.0	374.9	348.0	323.6	305.8	295.7	291.0	289.4
27.5°	382.3	375.4	354.8	328.4	305.2	288.4	280.4	275.6	274.6
30°	357.4	350.6	330.6	306.2	284.6	268.8	262.4	258.8	258.2
32.5°	330.0	324.2	305.8	283.6	263.0	249.8	245.0	242.4	241.8
35°	303.0	296.8	280.4	260.4	242.4	230.8	226.6	226.0	226.0
37.5°	275.6	269.3	256.0	237.6	222.3	211.8	210.2	210.6	210.6
40°	248.8	242.8	231.2	216.0	202.2	194.4	193.8	194.8	195.4
42.5°	223.4	218.6	208.0	194.8	183.2	176.8	177.4	179.6	181.2
45°	200.6	196.4	187.0	175.4	165.2	160.6	162.2	164.8	166.4
47.5°	180.0	176.4	167.4	156.8	148.4	145.2	147.4	150.4	152.6
50°	161.0	157.8	149.4	138.4	131.4	129.4	132.0	135.2	136.2
52.5°	144.2	141.0	132.0	122.6	117.2	116.2	118.8	121.4	123.0
55°	126.8	124.0	116.6	108.2	104.0	103.4	106.2	108.2	109.4
57.5°	112.4	109.8	103.0	95.6	91.8	91.4	94.0	95.6	96.2
60°	98.8	96.2	89.8	83.0	80.2	80.2	81.8	83.0	83.4
62.5°	86.0	83.4	77.6	71.8	69.6	69.6	69.6	70.2	71.8
65°	74.0	71.8	66.6	61.2	59.6	58.6	58.6	58.6	59.6
67.5°	62.8	60.8	56.4	51.8	50.2	48.6	48.0	49.2	49.2
70°	52.2	50.6	46.4	42.8	41.2	39.6	39.0	41.2	41.2
72.5°	42.8	41.2	38.6	34.8	33.2	32.8	33.8	34.8	35.4
75°	33.8	32.2	30.0	28.0	26.4	27.0	28.6	29.0	29.6
77.5°	25.4	24.8	22.8	21.2	21.2	21.6	22.8	23.8	24.2
80°	18.0	17.4	16.4	15.4	15.8	16.8	17.4	18.4	18.0
82.5°	11.0	11.0	10.6	10.6	11.0	12.2	12.6	13.2	13.8
85°	5.8	5.8	5.8	6.4	6.8	7.4	8.0	8.4	8.4
87.5°	1.6	2.2	2.2	2.6	3.2	3.2	3.6	3.6	3.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°    - - 45°-225°    - - - - 90°-270°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)