

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581439

Luminaire Tested: **HCC4S07D010BZ-HM40525830-41RWWH**

Issue Date: 9/9/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P581439  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-15)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC4S07D010BZ-HM40525830-41RWWH  
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WALLWASH DISTRIBUTION, HAZE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 877.2 lumens  
Efficiency: N/A  
Efficacy: 109.6 lumens/watt  
Spacing Criteria (0/90/45): 1.14 / 1.08 / 1.16  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P581439  
CATALOG NUMBER: HCC4S07D010BZ-HM40525830-41RWWH

### Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P581439

CATALOG NUMBER: HCC4S07D010BZ-HM40525830-41RWWH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	104	100	108	105	102	99	101	98	96	97	95	93	93	92	90	88								
2	103	96	90	85	100	94	89	84	90	86	82	87	84	80	84	81	79	77								
3	95	86	79	73	92	84	78	73	81	76	71	79	74	70	76	72	69	67								
4	88	77	70	64	86	76	69	63	74	67	62	71	66	62	69	65	61	59								
5	81	70	62	56	79	69	61	56	67	60	55	65	59	55	63	58	54	52								
6	76	64	56	50	74	63	55	50	61	54	49	60	54	49	58	53	49	47								
7	71	58	51	45	69	58	50	45	56	49	45	55	49	44	54	48	44	42								
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38								
9	62	50	42	37	61	49	42	37	48	41	37	47	41	37	46	41	37	35								
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32								

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	56764	56764	56764
5°	58268	56770	55718
10°	59581	56287	54057
15°	61256	55484	52637
20°	61076	53358	50509
25°	58508	49948	48083
30°	53823	46004	45520
35°	47341	41755	42101
40°	40979	37388	38934
45°	35620	33213	35201
50°	31605	29283	31278
55°	28021	25698	26795
60°	24965	22301	22301
65°	22181	18533	17337
70°	19150	14029	12370
75°	16060	9293	7625
80°	12217	4475	4049
85°	6510	1557	1557



TEST NUMBER: P581439  
 CATALOG NUMBER: HCC4S07D010BZ-HM40525830-41RWWH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	43.6	5.0
10°-20°	123.6	14.1
20°-30°	174.3	19.9
30°-40°	180.0	20.5
40°-50°	152.6	17.4
50°-60°	111.0	12.7
60°-70°	64.9	7.4
70°-80°	24.1	2.7
80°-90°	3.1	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	341.4	38.9
0°-40°	521.4	59.4
0°-60°	785.1	89.5
0°-90°	877.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	877.2	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	460	460	460	460	460	
5°	471	466	458	452	450	45
15°	480	465	434	416	412	135
25°	430	406	367	354	353	197
35°	314	301	277	278	280	196
45°	204	198	190	197	202	159
55°	130	124	120	124	125	117
65°	76	70	64	59	59	75
75°	34	28	20	16	16	36
85°	5	3	1	1	1	6
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P581439

CATALOG NUMBER: HCC4S07D010BZ-HM40525830-41RWWH

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	460.2	460.2	460.2	460.2	460.2	460.2	460.2	460.2	460.2
2.5°	464.2	463.1	461.9	460.2	457.9	456.2	454.5	453.4	453.4
5°	470.6	468.9	466.5	462.5	458.5	455.1	451.7	450.0	450.0
7.5°	475.1	472.8	468.3	462.5	455.7	450.5	445.4	443.0	441.9
10°	475.7	473.4	467.0	458.5	449.4	441.3	435.6	432.2	431.6
12.5°	476.8	474.0	465.9	453.9	441.9	432.2	426.0	422.5	421.4
15°	479.7	475.7	464.8	449.4	434.5	423.1	416.2	413.3	412.2
17.5°	476.8	471.1	457.9	439.6	423.1	410.5	403.6	400.8	400.8
20°	465.3	459.6	444.3	424.2	406.5	394.4	387.6	385.9	384.8
22.5°	449.4	443.0	426.5	405.4	387.6	376.8	372.2	369.8	369.3
25°	429.9	423.7	405.9	384.2	367.0	357.9	353.9	353.9	353.3
27.5°	408.2	400.2	381.9	363.0	346.4	339.6	337.9	337.9	338.4
30°	377.9	372.2	356.8	338.4	323.0	318.4	318.4	319.6	319.6
32.5°	345.3	341.3	327.6	311.6	299.5	296.7	297.8	300.2	300.8
35°	314.4	309.9	300.8	286.4	277.3	276.2	277.9	279.6	279.6
37.5°	284.2	279.6	273.2	261.9	255.0	255.6	257.9	260.1	261.9
40°	254.5	250.9	246.4	237.3	232.2	234.4	237.3	239.5	241.8
42.5°	228.2	224.6	221.2	214.4	211.0	213.8	217.2	219.5	221.8
45°	204.2	201.8	198.4	192.7	190.4	193.2	197.2	199.5	201.8
47.5°	183.6	182.4	177.8	172.6	171.5	174.3	177.8	180.7	182.4
50°	164.7	163.0	159.0	153.7	152.6	157.3	159.5	161.3	163.0
52.5°	146.3	144.6	140.1	135.5	135.5	138.9	140.7	141.2	142.9
55°	130.3	128.6	124.0	120.6	119.5	122.3	123.5	123.5	124.6
57.5°	115.5	113.8	109.2	105.2	104.6	106.3	106.3	106.3	106.9
60°	101.2	99.5	94.9	91.5	90.4	90.9	90.4	89.8	90.4
62.5°	88.1	86.4	81.7	77.7	76.6	76.6	74.9	74.3	74.9
65°	76.0	73.2	69.8	65.8	63.5	61.8	59.4	59.4	59.4
67.5°	64.1	61.8	57.7	53.7	50.9	48.0	44.6	45.7	46.3
70°	53.1	51.4	46.9	42.9	38.9	35.4	32.5	33.7	34.3
72.5°	43.5	41.2	37.2	32.5	29.1	24.6	22.9	24.0	24.0
75°	33.7	31.4	28.0	23.4	19.5	15.5	15.5	16.0	16.0
77.5°	25.1	22.9	19.5	15.5	12.1	9.1	9.7	9.7	9.7
80°	17.2	15.5	12.6	9.1	6.3	5.1	5.1	5.1	5.7
82.5°	9.7	8.5	6.8	4.6	2.8	2.8	2.8	2.8	2.8
85°	4.6	3.4	2.8	1.7	1.1	1.1	1.1	1.1	1.1
87.5°	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°    - - 45°-225°    - - - - 90°-270°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)