

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581442

Luminaire Tested: **HCC4W07D010BZ-HM40525830-41WWWB**

Issue Date: 9/9/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P581442  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-18)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC4W07D010BZ-HM40525830-41WWWB  
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WALLWASH DISTRIBUTION, BLACK BAFFLE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 864.0 lumens  
Efficiency: N/A  
Efficacy: 108.0 lumens/watt  
Spacing Criteria (0/90/45): 1.13 / 1.07 / 1.15  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P581442  
CATALOG NUMBER: HCC4W07D010BZ-HM40525830-41WWWB

### Luminous Intensity Polar Plot





TEST NUMBER: P581442

CATALOG NUMBER: HCC4W07D010BZ-HM40525830-41WWWB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20										
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	92	91	89	87								
2	102	95	89	84	99	93	87	83	89	85	81	86	82	79	83	80	77	75								
3	94	85	77	72	92	83	76	71	80	75	70	78	73	69	75	71	68	66								
4	87	76	68	62	85	75	68	62	72	66	61	70	65	60	68	63	60	58								
5	81	69	61	55	79	68	60	55	66	59	54	64	58	53	62	57	53	51								
6	75	63	55	49	73	62	54	49	60	53	48	59	53	48	57	52	47	46								
7	70	58	50	44	68	57	49	44	55	48	43	54	48	43	53	47	43	41								
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37								
9	61	49	41	36	60	48	41	36	47	41	36	46	40	36	45	40	36	34								
10	58	45	38	33	57	45	38	33	44	38	33	43	37	33	42	37	33	31								

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	54950	54950	54950
5°	57785	54888	52820
10°	59819	54233	50425
15°	61639	53250	48269
20°	61706	51061	45495
25°	59393	47716	42653
30°	55134	43910	39837
35°	49434	39527	36861
40°	43378	35279	34087
45°	37923	31224	31416
50°	33485	27325	28323
55°	29504	24236	25462
60°	26396	21437	22301
65°	23378	18854	18854
70°	20448	16084	16084
75°	17442	13630	15250
80°	13851	12217	13851
85°	8916	10473	12879



TEST NUMBER: P581442  
 CATALOG NUMBER: HCC4W07D010BZ-HM40525830-41WWWB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	42.2	4.9
10°-20°	118.9	13.8
20°-30°	166.5	19.3
30°-40°	171.6	19.9
40°-50°	146.1	16.9
50°-60°	108.2	12.5
60°-70°	67.9	7.9
70°-80°	33.7	3.9
80°-90°	8.9	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	327.6	37.9
0°-40°	499.2	57.8
0°-60°	753.5	87.2
0°-90°	864.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	864.0	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	446	446	446	446	446	
5°	467	459	443	431	427	45
15°	483	461	417	387	378	136
25°	436	406	351	320	313	200
35°	328	304	262	245	245	205
45°	217	202	179	176	180	169
55°	137	126	113	115	118	124
65°	80	72	65	64	65	80
75°	37	32	29	31	32	39
85°	6	6	7	8	9	8
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P581442

CATALOG NUMBER: HCC4W07D010BZ-HM40525830-41WWWB

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	445.5	445.5	445.5	445.5	445.5	445.5	445.5	445.5	445.5
2.5°	455.3	453.5	451.2	447.2	443.3	439.8	436.4	434.7	434.1
5°	466.7	463.3	458.7	451.2	443.3	436.4	430.6	427.8	426.6
7.5°	474.7	471.2	463.8	452.4	441.0	430.6	421.5	417.5	416.4
10°	477.6	473.5	463.3	447.8	433.0	420.4	410.0	404.9	402.6
12.5°	479.9	474.7	461.6	443.3	424.9	409.5	398.6	391.8	390.1
15°	482.7	477.0	461.0	438.7	417.0	398.6	386.6	380.3	378.0
17.5°	479.9	473.5	454.7	429.5	404.9	384.9	371.8	366.1	363.7
20°	470.1	463.3	442.1	415.3	389.0	368.4	355.2	349.5	346.6
22.5°	455.3	447.8	426.1	397.5	370.6	350.6	338.0	332.3	330.6
25°	436.4	428.9	406.0	376.9	350.6	331.2	320.2	315.1	313.4
27.5°	414.1	406.6	384.3	355.7	330.6	312.3	303.7	298.5	297.4
30°	387.1	379.8	358.0	331.7	308.3	291.1	284.3	280.3	279.7
32.5°	357.4	351.2	331.2	307.1	284.8	270.5	265.4	262.5	262.0
35°	328.3	321.4	303.7	282.0	262.5	249.9	245.4	244.8	244.8
37.5°	298.5	291.7	277.4	257.4	240.8	229.3	227.6	228.2	228.2
40°	269.4	263.1	250.5	234.0	219.1	210.4	209.8	211.1	211.7
42.5°	241.9	236.8	225.3	211.1	198.5	191.6	192.2	194.5	196.2
45°	217.4	212.8	202.5	189.9	179.0	173.9	175.6	178.4	180.1
47.5°	195.1	191.1	181.3	169.9	160.7	157.3	159.5	163.0	165.2
50°	174.5	171.0	161.8	149.9	142.4	140.1	142.9	146.5	147.6
52.5°	156.1	152.7	142.9	132.7	127.0	125.9	128.7	131.6	133.3
55°	137.2	134.4	126.4	117.2	112.7	112.1	114.9	117.2	118.4
57.5°	121.8	118.9	111.5	103.6	99.5	98.9	101.9	103.6	104.1
60°	107.0	104.1	97.2	89.8	86.9	86.9	88.7	89.8	90.4
62.5°	93.2	90.4	84.1	77.8	75.4	75.4	75.4	76.0	77.8
65°	80.1	77.8	72.0	66.3	64.6	63.5	63.5	63.5	64.6
67.5°	68.1	65.8	61.2	56.1	54.3	52.6	52.0	53.1	53.1
70°	56.7	54.9	50.3	46.3	44.6	42.9	42.3	44.6	44.6
72.5°	46.3	44.6	41.8	37.8	36.1	35.5	36.6	37.8	38.4
75°	36.6	34.9	32.5	30.3	28.6	29.1	30.8	31.4	32.0
77.5°	27.4	26.9	24.6	22.9	22.9	23.4	24.6	25.7	26.3
80°	19.5	18.9	17.8	16.6	17.2	18.3	18.9	20.0	19.5
82.5°	12.1	12.1	11.5	11.5	12.1	13.2	13.8	14.3	14.9
85°	6.3	6.3	6.3	6.8	7.4	8.0	8.5	9.1	9.1
87.5°	1.7	2.3	2.3	2.8	3.4	3.4	4.0	4.0	4.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°    - - 45°-225°    - - - - 90°-270°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)