

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581438

Luminaire Tested: **HCC4W07D010MW-HM40525830-41RWWC**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P581438
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-14)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4W07D010MW-HM40525830-41RWWC
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WALLWASH DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 881.8 lumens
Efficiency: N/A
Efficacy: 110.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.15 / 1.21
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P581438
CATALOG NUMBER: HCC4W07D010MW-HM40525830-41RWWC

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P581438

CATALOG NUMBER: HCC4W07D010MW-HM40525830-41RWWC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	111	107	103	100	108	105	102	99	101	98	96	97	95	93	93	92	90	88					88			
2	102	95	90	85	100	94	88	84	90	86	82	87	83	80	84	81	78	76					76			
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67					67			
4	87	77	69	63	85	76	68	63	73	67	62	71	66	61	69	64	60	58					58			
5	81	70	62	56	79	68	61	55	66	60	55	65	59	54	63	58	54	52					52			
6	75	63	55	49	74	62	55	49	61	54	49	59	53	48	58	52	48	46					46			
7	70	58	50	44	69	57	49	44	56	49	44	54	48	44	53	47	43	41					41			
8	66	53	45	40	64	53	45	40	51	44	40	50	44	39	49	43	39	37					37			
9	62	49	42	36	60	49	41	36	47	41	36	46	40	36	45	40	36	34					34			
10	58	46	38	33	57	45	38	33	44	38	33	43	37	33	42	37	33	31					31			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	52188	52188	52188
5°	54306	52672	52102
10°	56074	53130	51991
15°	58051	53301	51998
20°	58241	52019	51336
25°	56194	49417	49811
30°	52285	46018	47314
35°	47101	42101	43667
40°	41526	38290	40061
45°	36300	34521	36213
50°	32142	31048	32698
55°	28300	27440	28537
60°	25237	23411	24126
65°	22181	19029	18708
70°	19366	14029	12803
75°	16060	8483	6815
80°	12217	3267	1989
85°	5661	849	849



TEST NUMBER: P581438
 CATALOG NUMBER: HCC4W07D010MW-HM40525830-41RWWC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	40.8	4.6
10°-20°	119.1	13.5
20°-30°	172.5	19.6
30°-40°	182.0	20.6
40°-50°	157.5	17.9
50°-60°	116.7	13.2
60°-70°	67.2	7.6
70°-80°	23.5	2.7
80°-90°	2.5	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	332.4	37.7
0°-40°	514.4	58.3
0°-60°	788.6	89.4
0°-90°	881.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	881.8	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	423	423	423	423	423	
5°	439	433	425	422	421	42
15°	455	440	417	408	407	128
25°	413	392	363	361	366	189
35°	313	298	280	286	290	195
45°	208	202	198	205	208	162
55°	132	129	128	132	133	119
65°	76	72	65	62	64	76
75°	34	29	18	14	14	36
85°	4	2	1	1	1	6
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P581438

CATALOG NUMBER: HCC4W07D010MW-HM40525830-41RWWC

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1
2.5°	429.5	428.3	426.5	424.2	422.0	420.3	419.7	419.1	419.1
5°	438.6	436.3	432.9	428.3	425.4	423.7	422.0	420.8	420.8
7.5°	444.8	442.6	437.4	431.2	427.2	423.7	421.4	419.7	419.7
10°	447.7	444.8	438.6	430.6	424.2	419.7	416.3	415.1	415.1
12.5°	451.2	447.7	439.2	428.9	420.8	415.1	411.7	410.6	410.6
15°	454.6	450.6	439.7	427.8	417.4	410.6	407.7	407.2	407.2
17.5°	452.9	447.7	435.2	420.8	409.5	402.5	399.7	399.7	400.2
20°	443.7	438.6	424.2	408.3	396.3	391.1	388.9	390.0	391.1
22.5°	430.1	423.7	408.3	392.8	380.2	375.7	375.7	377.4	379.1
25°	412.9	407.2	392.3	375.1	363.1	359.7	360.9	363.7	366.0
27.5°	393.4	387.1	371.7	355.6	343.7	342.0	344.8	348.8	349.9
30°	367.1	362.0	348.8	333.3	323.1	322.5	326.5	329.3	332.2
32.5°	342.0	336.3	323.6	308.7	301.3	301.9	306.5	309.9	311.7
35°	312.8	307.6	298.5	286.4	279.6	280.7	285.9	289.4	290.0
37.5°	285.3	281.9	272.8	263.6	258.4	260.7	265.4	269.4	269.4
40°	257.9	255.0	248.2	240.7	237.8	240.7	245.4	248.8	248.8
42.5°	231.6	229.9	224.2	219.0	217.2	221.3	225.3	228.2	227.6
45°	208.1	206.4	202.5	198.5	197.9	201.9	205.3	207.0	207.6
47.5°	187.0	185.8	182.4	179.6	179.6	183.6	186.4	188.1	188.7
50°	167.5	166.4	163.5	161.3	161.8	165.8	168.1	169.8	170.4
52.5°	148.1	147.5	145.2	142.4	144.1	146.9	149.8	151.0	151.6
55°	131.6	131.6	128.7	126.3	127.6	130.4	132.1	132.7	132.7
57.5°	116.6	116.1	112.7	110.4	111.0	113.8	114.9	115.5	115.5
60°	102.3	101.7	98.3	94.9	94.9	96.6	97.2	97.8	97.8
62.5°	88.7	88.1	84.1	81.3	80.0	79.4	79.4	80.6	83.0
65°	76.0	75.4	71.5	66.9	65.2	63.5	61.8	62.9	64.1
67.5°	64.6	63.5	59.5	55.4	51.4	48.6	45.7	47.5	49.7
70°	53.7	52.6	48.0	43.5	38.9	34.3	32.0	34.3	35.5
72.5°	43.5	42.3	37.8	33.1	27.4	22.9	22.3	22.9	23.4
75°	33.7	33.1	28.6	23.4	17.8	14.3	14.3	14.3	14.3
77.5°	25.1	24.0	19.5	14.9	10.2	8.0	7.4	7.4	7.4
80°	17.2	16.0	12.1	8.5	4.6	3.4	3.4	2.8	2.8
82.5°	9.7	9.1	6.3	3.4	1.7	1.1	1.1	1.1	1.1
85°	4.0	3.4	2.3	1.1	0.6	0.6	0.6	0.6	0.6
87.5°	0.6	0.6	0.6	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)