

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581457

Luminaire Tested: **HCC4S07D010BZ-HM40525835-41RWWH**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P581457
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-15)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4S07D010BZ-HM40525835-41RWWH
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WALLWASH DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 909.3 lumens
Efficiency: N/A
Efficacy: 113.7 lumens/watt
Spacing Criteria (0/90/45): 1.14 / 1.08 / 1.16
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P581457
CATALOG NUMBER: HCC4S07D010BZ-HM40525835-41RWWH

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P581457

CATALOG NUMBER: HCC4S07D010BZ-HM40525835-41RWWH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	111	107	104	100	108	105	102	99	101	98	96	97	95	93	93	92	90	88					88			
2	103	96	90	85	100	94	89	84	90	86	82	87	84	80	84	81	79	77					77			
3	95	86	79	73	92	84	78	73	81	76	71	79	74	70	76	72	69	67					67			
4	88	77	70	64	86	76	69	63	74	67	62	71	66	62	69	65	61	59					59			
5	81	70	62	56	79	69	61	56	67	60	55	65	59	55	63	58	54	52					52			
6	76	64	56	50	74	63	55	50	61	54	49	60	54	49	58	53	49	47					47			
7	71	58	51	45	69	58	50	45	56	49	45	55	49	44	54	48	44	42					42			
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38					38			
9	62	50	42	37	61	49	42	37	48	41	37	47	41	37	46	41	37	35					35			
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32					32			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	58836	58836	58836
5°	60385	58838	57748
10°	61760	58341	56049
15°	63491	57515	54565
20°	63321	55301	52360
25°	60645	51771	49839
30°	55789	47685	47186
35°	49073	43291	43622
40°	42460	38741	40367
45°	36911	34416	36492
50°	32756	30357	32411
55°	29053	26623	27784
60°	25878	23115	23115
65°	23028	19204	18008
70°	19871	14534	12803
75°	16632	9579	7911
80°	12644	4617	4191
85°	6793	1557	1557



TEST NUMBER: P581457
 CATALOG NUMBER: HCC4S07D010BZ-HM40525835-41RWWH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	45.2	5.0
10°-20°	128.1	14.1
20°-30°	180.6	19.9
30°-40°	186.6	20.5
40°-50°	158.2	17.4
50°-60°	115.1	12.7
60°-70°	67.3	7.4
70°-80°	25.0	2.7
80°-90°	3.3	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	353.9	38.9
0°-40°	540.5	59.4
0°-60°	813.8	89.5
0°-90°	909.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	909.3	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	477	477	477	477	477	
5°	488	484	475	468	466	47
15°	497	482	450	431	427	140
25°	446	421	380	367	366	204
35°	326	312	288	288	290	204
45°	212	206	197	204	209	165
55°	135	129	124	128	129	122
65°	79	72	66	62	62	78
75°	35	29	20	16	17	38
85°	5	3	1	1	1	7
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P581457

CATALOG NUMBER: HCC4S07D010BZ-HM40525835-41RWWH

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	477.0	477.0	477.0	477.0	477.0	477.0	477.0	477.0	477.0
2.5°	481.1	480.0	478.9	477.0	474.7	473.0	471.1	469.9	469.9
5°	487.7	485.9	483.5	479.4	475.2	471.7	468.2	466.4	466.4
7.5°	492.4	490.1	485.4	479.4	472.3	466.9	461.7	459.3	458.0
10°	493.1	490.7	484.1	475.2	465.8	457.5	451.6	448.0	447.5
12.5°	494.2	491.3	483.0	470.6	458.0	448.0	441.5	437.9	436.8
15°	497.2	493.1	481.8	465.8	450.4	438.5	431.4	428.5	427.3
17.5°	494.2	488.3	474.7	455.7	438.5	425.5	418.3	415.4	415.4
20°	482.4	476.5	460.4	439.7	421.3	408.9	401.8	400.0	398.9
22.5°	465.8	459.3	442.1	420.1	401.8	390.6	385.8	383.4	382.8
25°	445.6	439.2	420.7	398.2	380.4	371.0	366.8	366.8	366.2
27.5°	423.1	414.8	395.9	376.3	359.2	352.0	350.3	350.3	350.8
30°	391.7	385.8	369.7	350.8	334.8	330.1	330.1	331.3	331.3
32.5°	357.9	353.8	339.6	323.0	310.6	307.6	308.7	311.1	311.7
35°	325.9	321.1	311.7	296.9	287.5	286.2	288.0	289.7	289.7
37.5°	294.5	289.7	283.2	271.4	264.2	264.9	267.3	269.6	271.4
40°	263.7	260.1	255.4	245.9	240.6	243.0	245.9	248.3	250.7
42.5°	236.5	232.9	229.3	222.3	218.7	221.7	225.2	227.6	229.9
45°	211.6	209.2	205.6	199.7	197.3	200.3	204.5	206.8	209.2
47.5°	190.3	189.0	184.4	179.0	177.8	180.7	184.4	187.3	189.0
50°	170.7	168.9	164.8	159.4	158.2	163.0	165.4	167.1	168.9
52.5°	151.7	149.9	145.2	140.4	140.4	144.0	145.8	146.3	148.2
55°	135.1	133.4	128.6	125.1	123.8	126.8	128.0	128.0	129.2
57.5°	119.7	117.9	113.2	109.0	108.5	110.3	110.3	110.3	110.8
60°	104.9	103.1	98.3	94.8	93.7	94.2	93.7	93.1	93.7
62.5°	91.3	89.4	84.8	80.6	79.4	79.4	77.6	77.0	77.6
65°	78.9	75.9	72.3	68.2	65.8	64.0	61.7	61.7	61.7
67.5°	66.3	64.0	59.9	55.6	52.7	49.7	46.2	47.5	48.0
70°	55.1	53.4	48.6	44.5	40.3	36.8	33.8	34.9	35.5
72.5°	45.1	42.7	38.5	33.8	30.3	25.5	23.7	24.9	24.9
75°	34.9	32.5	29.0	24.4	20.1	16.0	16.0	16.6	16.6
77.5°	26.1	23.7	20.1	16.0	12.4	9.4	10.1	10.1	10.1
80°	17.8	16.0	13.1	9.4	6.5	5.3	5.3	5.3	5.9
82.5°	10.1	8.9	7.1	4.8	3.0	3.0	3.0	3.0	3.0
85°	4.8	3.5	3.0	1.8	1.1	1.1	1.1	1.1	1.1
87.5°	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)