

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581459

Luminaire Tested: **HCC4S07D010SL-HM40525835-41WWW**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P581459
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4S07D010SL-HM40525835-41WWW
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WALLWASH DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 899.8 lumens
Efficiency: N/A
Efficacy: 112.5 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.03 / 1.1
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P581459
CATALOG NUMBER: HCC4S07D010SL-HM40525835-41WWW

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P581459

CATALOG NUMBER: HCC4S07D010SL-HM40525835-41WWW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	111	106	103	100	108	104	101	98	100	97	95	96	94	92	93	91	89	87					87			
2	102	95	89	84	100	93	88	83	90	85	81	87	83	80	84	81	78	76					76			
3	94	85	78	72	92	84	77	72	81	75	71	78	73	69	76	72	68	66					66			
4	87	77	69	63	85	76	68	63	73	67	62	71	66	61	69	64	60	58					58			
5	81	70	62	56	79	69	61	56	67	60	55	65	59	54	63	58	54	52					52			
6	76	64	56	50	74	63	55	50	61	54	49	59	53	49	58	53	48	47					47			
7	71	58	50	45	69	58	50	45	56	49	44	55	49	44	53	48	44	42					42			
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38					38			
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35					35			
10	59	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32					32			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	62142	62142	62142
5°	64880	61871	59011
10°	66519	60570	55322
15°	67896	58970	51321
20°	67534	56101	46992
25°	64687	51867	42762
30°	59777	47357	38754
35°	52401	42132	35069
40°	45632	37211	31591
45°	39702	32480	28224
50°	35385	27978	24908
55°	31612	24601	21526
60°	28221	21511	18576
65°	25071	18854	17628
70°	22035	16265	16445
75°	18634	13821	15250
80°	14277	11791	13922
85°	8350	9199	11746



TEST NUMBER: P581459
 CATALOG NUMBER: HCC4S07D010SL-HM40525835-41WWW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	47.2	5.2
10°-20°	130.3	14.5
20°-30°	178.0	19.8
30°-40°	178.7	19.9
40°-50°	147.8	16.4
50°-60°	107.2	11.9
60°-70°	67.9	7.5
70°-80°	34.3	3.8
80°-90°	8.4	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	355.5	39.5
0°-40°	534.2	59.4
0°-60°	789.2	87.7
0°-90°	899.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	899.8	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	504	504	504	504	504	
5°	524	516	500	483	477	50
15°	532	511	462	419	402	150
25°	475	444	381	333	314	217
35°	348	327	280	245	233	218
45°	228	215	186	168	162	177
55°	147	134	114	104	100	132
65°	86	76	65	58	60	86
75°	39	34	29	30	32	42
85°	6	6	6	8	8	8
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P581459

CATALOG NUMBER: HCC4S07D010SL-HM40525835-41WWW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	503.8	503.8	503.8	503.8	503.8	503.8	503.8	503.8	503.8
2.5°	513.4	511.5	508.6	505.0	500.8	496.2	492.0	489.6	488.4
5°	524.0	521.7	516.3	508.6	499.7	490.8	483.1	478.4	476.6
7.5°	530.5	527.0	519.3	507.4	493.8	480.7	469.4	462.9	461.1
10°	531.1	527.0	516.9	500.8	483.6	466.5	452.9	443.4	441.7
12.5°	531.7	526.3	513.9	494.9	473.6	452.2	435.6	424.5	421.4
15°	531.7	526.3	511.0	488.4	461.8	437.4	419.1	406.0	401.9
17.5°	527.0	521.1	502.7	476.6	447.6	420.3	399.0	385.3	381.1
20°	514.5	508.0	487.3	458.8	427.4	399.0	377.6	363.4	358.0
22.5°	496.7	489.0	467.1	436.3	404.9	375.8	355.1	340.3	335.5
25°	475.3	467.7	443.9	413.8	381.1	353.9	333.1	319.6	314.2
27.5°	449.3	441.0	417.9	387.7	357.4	330.1	311.2	298.7	293.4
30°	419.7	410.8	388.9	359.8	332.5	306.5	288.0	278.0	272.1
32.5°	385.3	377.6	358.0	332.0	306.5	281.5	266.2	257.3	252.5
35°	348.0	343.8	327.2	304.6	279.8	259.0	245.4	237.2	232.9
37.5°	314.8	310.6	296.3	277.4	255.5	236.5	225.2	218.2	214.6
40°	283.4	279.8	266.2	250.1	231.1	214.6	205.1	199.7	196.2
42.5°	252.5	250.7	239.4	224.6	208.0	193.8	186.2	182.0	179.0
45°	227.6	225.2	214.6	200.4	186.2	174.2	167.7	164.8	161.8
47.5°	205.6	202.7	191.4	179.0	165.9	155.3	149.4	146.5	145.2
50°	184.4	181.4	171.3	158.9	145.8	138.2	133.4	130.4	129.8
52.5°	165.4	162.4	151.1	139.3	129.3	122.7	118.6	115.6	114.4
55°	147.0	143.5	133.9	122.7	114.4	108.5	104.4	101.4	100.1
57.5°	130.4	126.9	118.6	107.9	100.1	94.8	91.3	88.3	87.2
60°	114.4	111.4	103.8	93.7	87.2	82.4	78.9	76.5	75.3
62.5°	99.6	97.2	89.6	80.6	75.3	71.1	68.2	65.8	67.0
65°	85.9	83.5	76.5	68.7	64.6	60.4	58.0	58.0	60.4
67.5°	72.9	70.6	64.6	58.0	54.5	51.6	49.8	51.6	53.4
70°	61.1	58.7	53.4	48.0	45.1	42.7	42.7	44.5	45.6
72.5°	49.8	47.5	43.2	39.1	36.8	34.9	36.8	37.9	39.1
75°	39.1	37.3	33.8	30.8	29.0	28.4	30.3	31.4	32.0
77.5°	29.0	27.9	25.5	23.1	22.0	22.5	24.4	24.9	25.5
80°	20.1	19.6	17.8	16.6	16.6	17.2	18.3	19.0	19.6
82.5°	12.4	12.4	11.3	10.7	11.3	12.4	13.1	13.7	13.7
85°	5.9	6.5	5.9	5.9	6.5	7.7	7.7	8.3	8.3
87.5°	1.8	1.8	2.4	2.4	3.0	3.0	3.0	3.0	3.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)