

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581495

Luminaire Tested: **HCC4S07D010MW-HM40525927-41WWW**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P581495
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4S07D010MW-HM40525927-41WWW
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WALLWASH DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 685.7 lumens
Efficiency: N/A
Efficacy: 85.7 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.03 / 1.1
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P581495
CATALOG NUMBER: HCC4S07D010MW-HM40525927-41WWW

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P581495

CATALOG NUMBER: HCC4S07D010MW-HM40525927-41WWW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100				
1	111	106	103	100	108	104	101	98	100	97	95	96	94	92	93	91	89	87				87				
2	102	95	89	84	100	93	88	83	90	85	81	87	83	80	84	81	78	76				76				
3	94	85	78	72	92	84	77	72	81	75	71	78	73	69	76	72	68	66				66				
4	87	77	69	63	85	76	68	63	73	67	62	71	66	61	69	64	60	58				58				
5	81	70	62	56	79	69	61	56	67	60	55	65	59	54	63	58	54	52				52				
6	76	64	56	50	74	63	55	50	61	54	49	59	53	49	58	53	48	47				47				
7	71	58	50	45	69	58	50	45	56	49	44	55	49	44	53	48	44	42				42				
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38				38				
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35				35				
10	59	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32				32				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	47365	47365	47365
5°	49440	47149	44958
10°	50701	46167	42146
15°	51743	44937	39101
20°	51455	42752	35808
25°	49294	39523	32582
30°	45548	36091	29525
35°	39933	32118	26727
40°	34763	28371	24072
45°	30247	24735	21526
50°	26942	21319	18978
55°	24085	18752	16430
60°	21511	16356	14160
65°	19117	14389	13455
70°	16770	12406	12550
75°	14202	10532	11628
80°	10939	8950	10584
85°	6510	7076	9057



TEST NUMBER: P581495
 CATALOG NUMBER: HCC4S07D010MW-HM40525927-41WWW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	36.0	5.2
10°-20°	99.3	14.5
20°-30°	135.6	19.8
30°-40°	136.2	19.9
40°-50°	112.7	16.4
50°-60°	81.7	11.9
60°-70°	51.7	7.5
70°-80°	26.1	3.8
80°-90°	6.4	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	270.9	39.5
0°-40°	407.1	59.4
0°-60°	601.4	87.7
0°-90°	685.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	685.7	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	384	384	384	384	384	
5°	399	393	381	368	363	38
15°	405	389	352	319	306	114
25°	362	338	290	254	239	166
35°	265	249	213	187	178	166
45°	173	164	142	128	123	135
55°	112	102	87	80	76	101
65°	66	58	49	44	46	65
75°	30	26	22	23	24	32
85°	5	5	5	6	6	6
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P581495

CATALOG NUMBER: HCC4S07D010MW-HM40525927-41WWW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	384.0	384.0	384.0	384.0	384.0	384.0	384.0	384.0	384.0
2.5°	391.1	389.9	387.6	384.9	381.7	378.0	375.0	373.2	372.2
5°	399.3	397.5	393.4	387.6	380.8	374.1	368.1	364.5	363.1
7.5°	404.3	401.6	395.7	386.7	376.2	366.3	357.8	352.8	351.4
10°	404.8	401.6	393.9	381.7	368.6	355.5	345.2	337.9	336.5
12.5°	405.2	401.1	391.6	377.1	361.0	344.7	332.0	323.4	321.1
15°	405.2	401.1	389.4	372.2	351.9	333.3	319.3	309.4	306.2
17.5°	401.6	397.0	383.1	363.1	341.1	320.2	304.0	293.6	290.4
20°	392.0	387.1	371.3	349.6	325.7	304.0	287.7	276.9	272.8
22.5°	378.5	372.7	356.0	332.4	308.5	286.4	270.6	259.2	255.7
25°	362.2	356.4	338.3	315.3	290.4	269.7	253.9	243.4	239.4
27.5°	342.4	336.1	318.4	295.4	272.4	251.6	237.2	227.7	223.6
30°	319.8	313.1	296.3	274.1	253.4	233.5	219.5	211.9	207.3
32.5°	293.6	287.7	272.8	253.0	233.5	214.5	202.8	196.1	192.4
35°	265.2	262.0	249.3	232.2	213.3	197.4	187.0	180.7	177.5
37.5°	239.9	236.7	225.9	211.4	194.7	180.3	171.6	166.3	163.5
40°	215.9	213.3	202.8	190.6	176.2	163.5	156.2	152.3	149.5
42.5°	192.4	191.1	182.5	171.2	158.5	147.7	141.8	138.7	136.4
45°	173.4	171.6	163.5	152.7	141.8	132.8	127.8	125.5	123.4
47.5°	156.7	154.5	145.9	136.4	126.4	118.4	113.8	111.5	110.6
50°	140.4	138.3	130.5	121.1	111.1	105.3	101.6	99.3	98.9
52.5°	126.0	123.8	115.2	106.2	98.4	93.5	90.4	88.1	87.2
55°	112.0	109.4	102.1	93.5	87.2	82.6	79.5	77.3	76.4
57.5°	99.3	96.6	90.4	82.2	76.4	72.3	69.5	67.3	66.3
60°	87.2	84.9	79.1	71.4	66.3	62.8	60.1	58.3	57.4
62.5°	75.9	74.1	68.2	61.5	57.4	54.2	51.9	50.2	51.1
65°	65.5	63.7	58.3	52.3	49.3	46.1	44.3	44.3	46.1
67.5°	55.5	53.7	49.3	44.3	41.5	39.3	37.9	39.3	40.6
70°	46.5	44.7	40.6	36.6	34.4	32.5	32.5	33.9	34.8
72.5°	37.9	36.2	33.0	29.8	28.0	26.6	28.0	28.9	29.8
75°	29.8	28.4	25.7	23.4	22.1	21.7	23.0	23.9	24.4
77.5°	22.1	21.3	19.5	17.6	16.7	17.2	18.5	19.0	19.5
80°	15.4	14.9	13.5	12.6	12.6	13.1	14.0	14.5	14.9
82.5°	9.4	9.4	8.5	8.1	8.5	9.4	9.9	10.4	10.4
85°	4.6	5.0	4.6	4.6	5.0	5.9	5.9	6.4	6.4
87.5°	1.4	1.4	1.8	1.8	2.3	2.3	2.3	2.3	2.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)