

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581494

Luminaire Tested: **HCC4W07D010BZ-HM40525927-41WWBB**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P581494
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-17)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4W07D010BZ-HM40525927-41WWBB
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WALLWASH DISTRIBUTION, WHITE BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 548.4 lumens
Efficiency: N/A
Efficacy: 68.5 lumens/watt
Spacing Criteria (0/90/45): 1.11 / 1.04 / 1.12
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P581494
CATALOG NUMBER: HCC4W07D010BZ-HM40525927-41WWBB

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P581494

CATALOG NUMBER: HCC4W07D010BZ-HM40525927-41WWBB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	111	108	104	101	109	105	102	100	101	99	97	97	95	94	94	92	91	89					89			
2	103	97	91	87	101	95	90	86	92	87	84	88	85	82	85	83	80	78					78			
3	96	87	80	75	94	86	79	74	83	78	73	80	76	72	78	74	71	69					69			
4	89	79	72	66	87	78	71	65	75	69	65	73	68	64	71	67	63	61					61			
5	83	72	64	58	81	71	64	58	69	62	58	67	61	57	65	60	56	55					55			
6	77	66	58	52	75	65	57	52	63	57	52	61	56	51	60	55	51	49					49			
7	72	60	53	47	71	59	52	47	58	51	47	57	51	46	55	50	46	44					44			
8	68	56	48	43	66	55	48	43	54	47	42	53	47	42	51	46	42	40					40			
9	64	52	44	39	62	51	44	39	50	43	39	49	43	39	48	43	39	37					37			
10	60	48	41	36	59	47	41	36	46	40	36	46	40	36	45	39	36	34					34			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	39162	39162	39162
5°	41479	39027	37071
10°	43211	38401	34894
15°	44860	37479	32818
20°	45285	35690	30348
25°	43810	33003	27791
30°	40976	29910	25267
35°	36515	26592	22707
40°	31913	23122	20208
45°	27805	19607	17496
50°	24255	16637	14987
55°	21268	13784	12129
60°	18601	11150	8906
65°	16198	8289	5020
70°	14173	5374	1659
75°	11628	2812	429
80°	8666	1279	355
85°	5095	708	708



TEST NUMBER: P581494
 CATALOG NUMBER: HCC4W07D010BZ-HM40525927-41WWBB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	30.0	5.5
10°-20°	83.9	15.3
20°-30°	115.9	21.1
30°-40°	116.6	21.3
40°-50°	94.1	17.2
50°-60°	63.6	11.6
60°-70°	32.4	5.9
70°-80°	10.4	1.9
80°-90°	1.6	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	229.8	41.9
0°-40°	346.3	63.2
0°-60°	504.0	91.9
0°-90°	548.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	548.4	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	318	318	318	318	318	
5°	335	329	315	304	299	32
15°	351	332	294	266	257	99
25°	322	294	242	213	204	147
35°	242	219	177	154	151	152
45°	159	143	112	100	100	124
55°	99	85	64	56	56	89
65°	56	45	28	18	17	56
75°	24	17	6	1	1	26
85°	4	2	0	0	0	5
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P581494

CATALOG NUMBER: HCC4W07D010BZ-HM40525927-41WWBB

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	317.5	317.5	317.5	317.5	317.5	317.5	317.5	317.5	317.5
2.5°	326.0	324.2	322.4	319.3	315.7	312.0	309.8	307.9	307.0
5°	335.0	332.9	328.8	321.9	315.2	308.9	304.0	300.8	299.4
7.5°	342.3	339.1	332.4	322.9	312.5	302.6	296.2	291.7	290.0
10°	345.0	341.4	332.4	319.7	306.6	294.4	285.4	280.9	278.6
12.5°	348.1	344.1	332.9	317.0	300.8	286.3	276.0	270.0	267.8
15°	351.3	346.0	332.4	313.0	293.5	276.8	265.5	259.7	257.0
17.5°	351.3	345.0	328.8	306.1	284.0	266.4	253.8	247.1	244.8
20°	345.0	337.8	320.1	295.3	271.9	252.9	240.7	234.0	231.2
22.5°	335.0	326.9	307.9	282.2	257.4	238.9	226.7	220.3	217.7
25°	321.9	313.9	293.9	267.3	242.5	224.0	212.7	206.8	204.2
27.5°	306.6	297.6	277.7	251.0	226.7	209.1	198.7	193.2	191.1
30°	287.7	279.0	259.7	233.5	210.0	193.7	184.2	179.2	177.4
32.5°	265.5	258.3	239.3	215.0	192.8	177.9	169.3	165.2	163.4
35°	242.5	235.7	219.1	196.4	176.6	162.6	154.4	151.7	150.8
37.5°	220.8	215.0	198.7	177.9	159.9	147.7	140.4	138.6	137.7
40°	198.2	194.1	179.2	160.3	143.6	132.8	126.9	125.5	125.5
42.5°	177.9	173.4	160.3	143.2	128.3	117.4	113.3	112.0	112.4
45°	159.4	154.9	142.7	126.9	112.4	103.4	100.3	100.3	100.3
47.5°	142.2	138.2	126.9	110.6	98.9	91.7	88.5	88.5	89.0
50°	126.4	123.7	111.1	97.1	86.7	79.9	77.7	77.3	78.1
52.5°	111.5	108.3	97.1	84.4	74.5	69.1	66.8	66.3	66.8
55°	98.9	95.3	85.4	73.2	64.1	58.7	56.0	55.5	56.4
57.5°	86.7	84.0	73.6	62.8	54.2	48.8	46.5	45.6	46.1
60°	75.4	72.7	63.3	52.8	45.2	39.7	36.5	35.6	36.1
62.5°	65.0	62.8	53.7	43.8	36.1	31.2	28.0	25.7	26.6
65°	55.5	53.3	45.2	35.3	28.4	23.0	18.5	16.7	17.2
67.5°	47.5	44.7	37.0	28.0	21.3	15.4	10.4	9.4	9.4
70°	39.3	36.5	29.8	21.6	14.9	8.1	4.6	4.6	4.6
72.5°	31.6	29.4	23.0	16.3	9.4	3.6	1.8	1.8	1.8
75°	24.4	22.5	17.2	11.3	5.9	1.8	1.4	0.9	0.9
77.5°	18.1	16.3	12.2	7.6	3.6	0.9	0.9	0.9	0.9
80°	12.2	10.8	8.1	4.6	1.8	0.5	0.5	0.5	0.5
82.5°	7.2	6.4	4.6	2.3	0.9	0.5	0.5	0.5	0.5
85°	3.6	2.7	1.8	0.9	0.5	0.5	0.5	0.5	0.5
87.5°	0.9	0.5	0.5	0.5	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)