

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581496

Luminaire Tested: **HCC4W07D010SL-HM40525927-41WWWB**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P581496
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-18)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4W07D010SL-HM40525927-41WWWB
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WALLWASH DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 682.5 lumens
Efficiency: N/A
Efficacy: 85.3 lumens/watt
Spacing Criteria (0/90/45): 1.13 / 1.07 / 1.15
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P581496
CATALOG NUMBER: HCC4W07D010SL-HM40525927-41WWWB

Luminous Intensity Polar Plot





TEST NUMBER: P581496

CATALOG NUMBER: HCC4W07D010SL-HM40525927-41WWWB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	92	91	89	87								
2	102	95	89	84	99	93	87	83	89	85	81	86	82	79	83	80	77	75								
3	94	85	77	72	92	83	76	71	80	75	70	78	73	69	75	71	68	66								
4	87	76	68	62	85	75	68	62	72	66	61	70	65	60	68	63	60	58								
5	81	69	61	55	79	68	60	55	66	59	54	64	58	53	62	57	53	51								
6	75	63	55	49	73	62	54	49	60	53	48	59	53	48	57	52	47	46								
7	70	58	50	44	68	57	49	44	55	48	43	54	48	43	53	47	43	41								
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37								
9	61	49	41	36	60	48	41	36	47	41	36	46	40	36	45	40	36	34								
10	58	45	38	33	57	45	38	33	44	38	33	43	37	33	42	37	33	31								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	43405	43405	43405
5°	45639	43361	41726
10°	47244	42835	39842
15°	48691	42051	38130
20°	48737	40310	35939
25°	46913	37699	33684
30°	43568	34681	31462
35°	39060	31215	29107
40°	34264	27856	26922
45°	29951	24683	24805
50°	26443	21569	22355
55°	23333	19139	20107
60°	20821	16923	17614
65°	18475	14914	14914
70°	16121	12731	12731
75°	13773	10723	12057
80°	10939	9589	10939
85°	7076	8350	10331



TEST NUMBER: P581496
 CATALOG NUMBER: HCC4W07D010SL-HM40525927-41WWWB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	33.3	4.9
10°-20°	93.9	13.8
20°-30°	131.6	19.3
30°-40°	135.5	19.9
40°-50°	115.4	16.9
50°-60°	85.5	12.5
60°-70°	53.7	7.9
70°-80°	26.7	3.9
80°-90°	7.0	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	258.8	37.9
0°-40°	394.3	57.8
0°-60°	595.2	87.2
0°-90°	682.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	682.5	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	352	352	352	352	352	
5°	369	362	350	340	337	35
15°	381	364	329	305	299	107
25°	345	321	277	253	248	158
35°	259	240	207	194	193	162
45°	172	160	142	139	142	133
55°	108	100	89	91	94	98
65°	63	57	51	50	51	63
75°	29	26	22	24	25	31
85°	5	5	6	7	7	6
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P581496

CATALOG NUMBER: HCC4W07D010SL-HM40525927-41WWWB

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	351.9	351.9	351.9	351.9	351.9	351.9	351.9	351.9	351.9
2.5°	359.6	358.2	356.4	353.2	350.2	347.4	344.7	343.3	342.9
5°	368.6	366.0	362.3	356.4	350.2	344.7	340.1	337.9	337.0
7.5°	375.0	372.2	366.4	357.3	348.3	340.1	333.0	329.8	328.9
10°	377.2	374.1	366.0	353.7	342.0	332.1	323.9	319.9	318.1
12.5°	379.1	375.0	364.6	350.2	335.7	323.4	314.9	309.4	308.1
15°	381.3	376.8	364.2	346.5	329.3	314.9	305.4	300.4	298.6
17.5°	379.1	374.1	359.2	339.2	319.9	304.1	293.6	289.2	287.3
20°	371.3	366.0	349.3	328.0	307.1	291.0	280.5	276.1	273.8
22.5°	359.6	353.7	336.6	314.0	292.7	277.0	267.0	262.4	261.2
25°	344.7	338.8	320.8	297.7	277.0	261.6	253.0	248.9	247.5
27.5°	327.1	321.3	303.6	281.0	261.2	246.7	239.9	235.8	234.9
30°	305.9	300.0	282.8	262.0	243.5	230.0	224.5	221.3	220.9
32.5°	282.3	277.3	261.6	242.6	225.0	213.7	209.6	207.3	206.9
35°	259.4	253.9	239.9	222.7	207.3	197.4	193.8	193.3	193.3
37.5°	235.8	230.4	219.1	203.2	190.2	181.2	179.8	180.3	180.3
40°	212.8	207.8	197.9	184.8	173.0	166.3	165.8	166.7	167.2
42.5°	191.1	187.1	178.0	166.7	156.8	151.4	151.8	153.6	155.0
45°	171.7	168.1	159.9	150.0	141.5	137.4	138.7	141.0	142.2
47.5°	154.1	150.9	143.2	134.2	127.0	124.3	126.1	128.7	130.5
50°	137.8	135.1	127.8	118.4	112.4	110.7	112.9	115.6	116.5
52.5°	123.4	120.6	112.9	104.8	100.3	99.3	101.6	103.9	105.3
55°	108.5	106.2	99.8	92.6	89.0	88.5	90.8	92.6	93.5
57.5°	96.3	94.0	88.1	81.8	78.6	78.2	80.5	81.8	82.3
60°	84.4	82.3	76.8	70.9	68.6	68.6	70.0	70.9	71.4
62.5°	73.6	71.4	66.5	61.5	59.6	59.6	59.6	60.1	61.5
65°	63.3	61.5	56.9	52.3	51.1	50.2	50.2	50.2	51.1
67.5°	53.7	52.0	48.4	44.3	42.9	41.5	41.1	42.0	42.0
70°	44.7	43.4	39.7	36.6	35.3	33.9	33.5	35.3	35.3
72.5°	36.6	35.3	33.0	29.8	28.4	28.0	28.9	29.8	30.3
75°	28.9	27.5	25.7	23.9	22.5	23.0	24.4	24.8	25.3
77.5°	21.7	21.3	19.5	18.1	18.1	18.5	19.5	20.4	20.8
80°	15.4	14.9	14.0	13.1	13.5	14.5	14.9	15.8	15.4
82.5°	9.4	9.4	9.0	9.0	9.4	10.4	10.8	11.3	11.7
85°	5.0	5.0	5.0	5.5	5.9	6.4	6.8	7.3	7.3
87.5°	1.4	1.8	1.8	2.3	2.7	2.7	3.2	3.2	3.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)