

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581530

Luminaire Tested: **HCC4W07D010MB-HM40525935-41WWBB**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P581530
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-17)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4W07D010MB-HM40525935-41WWBB
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WALLWASH DISTRIBUTION, WHITE BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 642.6 lumens
Efficiency: N/A
Efficacy: 80.3 lumens/watt
Spacing Criteria (0/90/45): 1.11 / 1.04 / 1.12
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P581530
CATALOG NUMBER: HCC4W07D010MB-HM40525935-41WWBB

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P581530

CATALOG NUMBER: HCC4W07D010MB-HM40525935-41WWBB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	108	104	101	109	105	102	100	101	99	97	97	95	94	94	92	91	89								
2	103	97	91	87	101	95	90	86	92	87	84	88	85	82	85	83	80	78								
3	96	87	80	75	94	86	79	74	83	78	73	80	76	72	78	74	71	69								
4	89	79	72	66	87	78	71	65	75	69	65	73	68	64	71	67	63	61								
5	83	72	64	58	81	71	64	58	69	62	58	67	61	57	65	60	56	55								
6	77	66	58	52	75	65	57	52	63	57	52	61	56	51	60	55	51	49								
7	72	60	53	47	71	59	52	47	58	51	47	57	51	46	55	50	46	44								
8	68	56	48	43	66	55	48	43	54	47	42	53	47	42	51	46	42	40								
9	64	52	44	39	62	51	44	39	50	43	39	49	43	39	48	43	39	37								
10	60	48	41	36	59	47	41	36	46	40	36	46	40	36	45	39	36	34								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	45885	45885	45885
5°	48623	45738	43435
10°	50638	45014	40894
15°	52573	43928	38450
20°	53069	41820	35572
25°	51363	38679	32554
30°	48012	35037	29625
35°	42794	31154	26607
40°	37420	27099	23685
45°	32602	22991	20479
50°	28438	19496	17577
55°	24902	16150	14215
60°	21808	13050	10435
65°	19000	9719	5866
70°	16625	6275	1911
75°	13630	3241	477
80°	10158	1563	426
85°	5944	849	849



TEST NUMBER: P581530
 CATALOG NUMBER: HCC4W07D010MB-HM40525935-41WWBB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	35.1	5.5
10°-20°	98.3	15.3
20°-30°	135.9	21.1
30°-40°	136.6	21.3
40°-50°	110.2	17.2
50°-60°	74.5	11.6
60°-70°	37.9	5.9
70°-80°	12.2	1.9
80°-90°	1.9	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	269.3	41.9
0°-40°	405.9	63.2
0°-60°	590.7	91.9
0°-90°	642.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	642.6	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	372	372	372	372	372	
5°	393	385	369	356	351	38
15°	412	390	344	311	301	116
25°	377	344	284	249	239	173
35°	284	257	207	181	177	178
45°	187	167	132	117	117	145
55°	116	100	75	66	66	104
65°	65	53	33	22	20	65
75°	29	20	7	2	1	31
85°	4	2	1	1	1	6
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P581530

CATALOG NUMBER: HCC4W07D010MB-HM40525935-41WWBB

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	372.0	372.0	372.0	372.0	372.0	372.0	372.0	372.0	372.0
2.5°	382.1	380.0	377.8	374.2	370.0	365.6	363.0	361.0	359.8
5°	392.7	390.0	385.3	377.4	369.4	362.0	356.2	352.4	350.8
7.5°	401.1	397.4	389.5	378.4	366.2	354.6	347.2	341.9	339.8
10°	404.3	400.1	389.5	374.7	359.4	345.0	334.5	329.2	326.5
12.5°	408.0	403.3	390.0	371.6	352.4	335.5	323.3	316.5	313.9
15°	411.7	405.4	389.5	366.8	344.0	324.4	311.1	304.3	301.1
17.5°	411.7	404.3	385.3	358.8	332.9	312.3	297.5	289.5	286.9
20°	404.3	395.9	375.2	346.1	318.6	296.3	282.1	274.1	271.0
22.5°	392.7	383.2	361.0	330.8	301.7	279.9	265.7	258.2	255.1
25°	377.4	367.8	344.5	313.3	284.2	262.5	249.2	242.4	239.2
27.5°	359.4	348.8	325.5	294.3	265.7	245.0	232.8	226.5	223.8
30°	337.1	327.1	304.3	273.6	246.0	227.0	215.9	210.1	208.0
32.5°	311.1	302.7	280.5	252.0	226.0	208.5	198.5	193.7	191.5
35°	284.2	276.3	256.6	230.2	206.9	190.5	180.9	177.9	176.7
37.5°	258.8	252.0	232.8	208.5	187.3	173.1	164.6	162.5	161.4
40°	232.4	227.6	210.1	187.9	168.3	155.6	148.7	147.1	147.1
42.5°	208.5	203.2	187.9	167.7	150.3	137.6	132.8	131.2	131.8
45°	186.9	181.5	167.3	148.7	131.8	121.2	117.4	117.4	117.4
47.5°	166.7	161.9	148.7	129.6	115.8	107.4	103.7	103.7	104.2
50°	148.2	145.0	130.2	113.8	101.6	93.7	91.0	90.5	91.6
52.5°	130.8	127.0	113.8	99.0	87.3	81.0	78.3	77.8	78.3
55°	115.8	111.6	100.0	85.7	75.1	68.8	65.7	65.1	66.1
57.5°	101.6	98.4	86.3	73.5	63.5	57.1	54.5	53.5	53.9
60°	88.4	85.2	74.1	61.9	52.9	46.5	42.9	41.8	42.3
62.5°	76.2	73.5	62.9	51.3	42.3	36.5	32.8	30.2	31.2
65°	65.1	62.5	52.9	41.3	33.3	27.0	21.7	19.6	20.1
67.5°	55.5	52.3	43.4	32.8	24.9	18.0	12.2	11.2	11.2
70°	46.1	42.9	34.9	25.4	17.4	9.6	5.3	5.3	5.3
72.5°	37.1	34.4	27.0	19.0	11.2	4.2	2.2	2.2	2.2
75°	28.6	26.5	20.1	13.2	6.8	2.2	1.6	1.0	1.0
77.5°	21.2	19.0	14.3	9.0	4.2	1.0	1.0	1.0	1.0
80°	14.3	12.7	9.6	5.3	2.2	0.6	0.6	0.6	0.6
82.5°	8.4	7.4	5.3	2.6	1.0	0.6	0.6	0.6	0.6
85°	4.2	3.2	2.2	1.0	0.6	0.6	0.6	0.6	0.6
87.5°	1.0	0.6	0.6	0.6	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)