

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581550

Luminaire Tested: **HCC4W07D010MW-HM40525950-41WWWB**

Issue Date: 9/9/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P581550  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-18)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC4W07D010MW-HM40525950-41WWWB  
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WALLWASH DISTRIBUTION, BLACK BAFFLE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 828.8 lumens  
Efficiency: N/A  
Efficacy: 103.6 lumens/watt  
Spacing Criteria (0/90/45): 1.13 / 1.07 / 1.15  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P581550  
CATALOG NUMBER: HCC4W07D010MW-HM40525950-41WWWB

### Luminous Intensity Polar Plot





TEST NUMBER: P581550

CATALOG NUMBER: HCC4W07D010MW-HM40525950-41WWWB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	92	91	89	87								
2	102	95	89	84	99	93	87	83	89	85	81	86	82	79	83	80	77	75								
3	94	85	77	72	92	83	76	71	80	75	70	78	73	69	75	71	68	66								
4	87	76	68	62	85	75	68	62	72	66	61	70	65	60	68	63	60	58								
5	81	69	61	55	79	68	60	55	66	59	54	64	58	53	62	57	53	51								
6	75	63	55	49	73	62	54	49	60	53	48	59	53	48	57	52	47	46								
7	70	58	50	44	68	57	49	44	55	48	43	54	48	43	53	47	43	41								
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37								
9	61	49	41	36	60	48	41	36	47	41	36	46	40	36	45	40	36	34								
10	58	45	38	33	57	45	38	33	44	38	33	43	37	33	42	37	33	31								

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	52706	52706	52706
5°	55433	52647	50666
10°	57364	52016	48371
15°	59136	51066	46303
20°	59199	48961	43631
25°	56970	45769	40924
30°	52897	42116	38199
35°	47417	37915	35356
40°	41607	33830	32686
45°	36370	29951	30160
50°	32103	26212	27172
55°	28322	23247	24429
60°	25286	20574	21388
65°	22415	18095	18095
70°	19583	15435	15435
75°	16775	13058	14631
80°	13283	11720	13283
85°	8491	10190	12454



TEST NUMBER: P581550

CATALOG NUMBER: HCC4W07D010MW-HM40525950-41WWWB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	40.5	4.9
10°-20°	114.0	13.8
20°-30°	159.7	19.3
30°-40°	164.6	19.9
40°-50°	140.1	16.9
50°-60°	103.8	12.5
60°-70°	65.2	7.9
70°-80°	32.4	3.9
80°-90°	8.5	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	314.3	37.9
0°-40°	478.8	57.8
0°-60°	722.8	87.2
0°-90°	828.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	828.8	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	427	427	427	427	427	
5°	448	440	425	413	409	43
15°	463	442	400	371	363	130
25°	419	390	336	307	301	191
35°	315	291	252	235	235	196
45°	208	194	172	168	173	162
55°	132	121	108	110	114	119
65°	77	69	62	61	62	77
75°	35	31	27	30	31	38
85°	6	6	7	8	9	8
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P581550

CATALOG NUMBER: HCC4W07D010MW-HM40525950-41WWWB

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	427.3	427.3	427.3	427.3	427.3	427.3	427.3	427.3	427.3
2.5°	436.7	435.1	432.9	429.0	425.2	421.9	418.6	417.0	416.4
5°	447.7	444.4	440.0	432.9	425.2	418.6	413.1	410.4	409.2
7.5°	455.3	452.0	445.0	433.9	423.0	413.1	404.3	400.5	399.3
10°	458.0	454.3	444.4	429.6	415.3	403.2	393.3	388.4	386.2
12.5°	460.3	455.3	442.7	425.2	407.6	392.8	382.4	375.8	374.2
15°	463.1	457.5	442.2	420.7	399.9	382.4	370.9	364.8	362.6
17.5°	460.3	454.3	436.1	412.0	388.4	369.2	356.5	351.1	348.9
20°	451.0	444.4	424.0	398.3	373.0	353.3	340.7	335.1	332.4
22.5°	436.7	429.6	408.7	381.2	355.5	336.3	324.2	318.8	317.0
25°	418.6	411.5	389.5	361.5	336.3	317.6	307.3	302.3	300.7
27.5°	397.2	390.1	368.7	341.2	317.0	299.5	291.3	286.3	285.3
30°	371.4	364.3	343.4	318.2	295.7	279.3	272.7	268.8	268.2
32.5°	342.9	336.8	317.6	294.6	273.2	259.5	254.6	251.8	251.3
35°	314.9	308.3	291.3	270.5	251.8	239.8	235.3	234.8	234.8
37.5°	286.3	279.8	266.1	246.8	231.0	220.0	218.4	218.8	218.8
40°	258.4	252.4	240.2	224.4	210.1	201.9	201.3	202.5	203.0
42.5°	232.0	227.1	216.1	202.5	190.4	183.8	184.4	186.5	188.2
45°	208.5	204.0	194.3	182.1	171.7	166.7	168.4	171.2	172.9
47.5°	187.1	183.2	173.9	163.0	154.2	150.9	153.1	156.4	158.5
50°	167.3	164.0	155.2	143.7	136.6	134.4	137.1	140.4	141.6
52.5°	149.8	146.5	137.1	127.2	121.8	120.7	123.5	126.2	127.8
55°	131.7	128.9	121.2	112.4	108.1	107.5	110.3	112.4	113.6
57.5°	116.9	114.1	107.0	99.3	95.5	94.9	97.6	99.3	99.8
60°	102.5	99.8	93.3	86.1	83.4	83.4	85.0	86.1	86.7
62.5°	89.4	86.7	80.7	74.7	72.4	72.4	72.4	72.9	74.7
65°	76.8	74.7	69.1	63.6	62.0	60.9	60.9	60.9	62.0
67.5°	65.3	63.0	58.7	53.7	52.1	50.5	50.0	51.0	51.0
70°	54.3	52.7	48.3	44.4	42.8	41.2	40.6	42.8	42.8
72.5°	44.4	42.8	40.1	36.2	34.6	34.0	35.2	36.2	36.8
75°	35.2	33.5	31.3	29.0	27.4	28.0	29.6	30.2	30.7
77.5°	26.3	25.8	23.6	22.0	22.0	22.5	23.6	24.7	25.3
80°	18.7	18.1	17.0	15.9	16.5	17.5	18.1	19.2	18.7
82.5°	11.5	11.5	10.9	10.9	11.5	12.6	13.2	13.8	14.2
85°	6.0	6.0	6.0	6.6	7.2	7.6	8.2	8.8	8.8
87.5°	1.6	2.2	2.2	2.7	3.3	3.3	3.9	3.9	3.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°    - - 45°-225°    - - - - 90°-270°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)