

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581549

Luminaire Tested: **HCC4W07D010SL-HM40525950-41WWW**

Issue Date: 9/9/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P581549  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-16)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC4W07D010SL-HM40525950-41WWW  
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WALLWASH DISTRIBUTION, WHITE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 832.6 lumens  
Efficiency: N/A  
Efficacy: 104.1 lumens/watt  
Spacing Criteria (0/90/45): 1.06 / 1.03 / 1.1  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P581549  
CATALOG NUMBER: HCC4W07D010SL-HM40525950-41WWW

### Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P581549

CATALOG NUMBER: HCC4W07D010SL-HM40525950-41WWW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	106	103	100	108	104	101	98	100	97	95	96	94	92	93	91	89	87								
2	102	95	89	84	100	93	88	83	90	85	81	87	83	80	84	81	78	76								
3	94	85	78	72	92	84	77	72	81	75	71	78	73	69	76	72	68	66								
4	87	77	69	63	85	76	68	63	73	67	62	71	66	61	69	64	60	58								
5	81	70	62	56	79	69	61	56	67	60	55	65	59	54	63	58	54	52								
6	76	64	56	50	74	63	55	50	61	54	49	59	53	49	58	53	48	47								
7	71	58	50	45	69	58	50	45	56	49	44	55	49	44	53	48	44	42								
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38								
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35								
10	59	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32								

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	57504	57504	57504
5°	60039	57253	54603
10°	61560	56061	51189
15°	62840	54565	47490
20°	62494	51914	43487
25°	59883	48001	39577
30°	55319	43825	35849
35°	48471	38984	32449
40°	42218	34441	29224
45°	36736	30056	26131
50°	32737	25905	23065
55°	29246	22752	19935
60°	26100	19908	17170
65°	23203	17424	16344
70°	20340	15039	15219
75°	17252	12820	14106
80°	13283	10939	12857
85°	7784	8491	10756



TEST NUMBER: P581549  
 CATALOG NUMBER: HCC4W07D010SL-HM40525950-41WWW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	43.7	5.2
10°-20°	120.6	14.5
20°-30°	164.7	19.8
30°-40°	165.4	19.9
40°-50°	136.8	16.4
50°-60°	99.1	11.9
60°-70°	62.8	7.5
70°-80°	31.8	3.8
80°-90°	7.8	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	329.0	39.5
0°-40°	494.3	59.4
0°-60°	730.3	87.7
0°-90°	832.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	832.6	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	466	466	466	466	466	
5°	485	478	462	447	441	46
15°	492	473	427	388	372	138
25°	440	411	353	308	291	201
35°	322	303	259	227	216	202
45°	211	199	172	155	150	164
55°	136	124	106	96	93	122
65°	80	71	60	54	56	79
75°	36	31	27	28	30	39
85°	6	6	6	7	8	8
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P581549

CATALOG NUMBER: HCC4W07D010SL-HM40525950-41WWW

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	466.2	466.2	466.2	466.2	466.2	466.2	466.2	466.2	466.2
2.5°	475.0	473.4	470.7	467.4	463.5	459.1	455.3	453.0	452.0
5°	484.9	482.7	477.7	470.7	462.4	454.2	447.0	442.7	441.0
7.5°	490.9	487.6	480.5	469.5	456.9	444.8	434.5	428.5	426.7
10°	491.5	487.6	478.3	463.5	447.6	431.6	419.1	410.2	408.7
12.5°	492.1	487.1	475.6	458.0	438.2	418.6	403.2	392.7	390.0
15°	492.1	487.1	472.8	452.0	427.3	404.8	387.8	375.8	371.9
17.5°	487.6	482.2	465.1	441.0	414.1	388.9	369.2	356.5	352.7
20°	476.1	470.1	450.9	424.6	395.5	369.2	349.4	336.3	331.3
22.5°	459.6	452.6	432.2	403.8	374.6	347.8	328.5	314.9	310.4
25°	440.0	432.8	410.8	382.8	352.7	327.5	308.3	295.7	290.8
27.5°	415.8	408.1	386.7	358.7	330.8	305.6	288.0	276.4	271.5
30°	388.4	380.1	359.8	333.0	307.7	283.6	266.6	257.3	251.7
32.5°	356.5	349.4	331.3	307.1	283.6	260.6	246.3	238.1	233.6
35°	321.9	318.2	302.8	282.0	258.9	239.7	227.1	219.4	215.5
37.5°	291.2	287.5	274.3	256.7	236.4	218.8	208.5	201.9	198.6
40°	262.2	258.9	246.3	231.5	213.9	198.6	189.8	184.8	181.5
42.5°	233.6	232.0	221.6	207.9	192.5	179.3	172.3	168.4	165.7
45°	210.6	208.5	198.6	185.4	172.3	161.3	155.2	152.5	149.8
47.5°	190.4	187.5	177.2	165.7	153.6	143.7	138.3	135.5	134.4
50°	170.6	167.9	158.5	147.0	135.0	127.8	123.5	120.6	120.2
52.5°	153.1	150.3	139.9	128.9	119.6	113.6	109.7	107.0	105.8
55°	136.0	132.7	123.9	113.6	105.8	100.4	96.5	93.8	92.7
57.5°	120.6	117.4	109.7	99.8	92.7	87.7	84.4	81.7	80.7
60°	105.8	103.1	96.0	86.7	80.7	76.2	72.9	70.8	69.6
62.5°	92.2	90.0	82.8	74.7	69.6	65.8	63.0	60.9	62.0
65°	79.5	77.4	70.8	63.6	59.7	56.0	53.7	53.7	56.0
67.5°	67.5	65.3	59.7	53.7	50.4	47.7	46.1	47.7	49.4
70°	56.4	54.3	49.4	44.4	41.7	39.5	39.5	41.2	42.2
72.5°	46.1	43.9	40.1	36.2	34.0	32.3	34.0	35.1	36.2
75°	36.2	34.6	31.3	28.6	26.9	26.3	28.0	29.0	29.6
77.5°	26.9	25.8	23.6	21.4	20.3	20.8	22.5	23.0	23.6
80°	18.7	18.1	16.5	15.4	15.4	15.9	17.0	17.5	18.1
82.5°	11.5	11.5	10.5	9.9	10.5	11.5	12.1	12.6	12.6
85°	5.5	6.0	5.5	5.5	6.0	7.2	7.2	7.6	7.6
87.5°	1.6	1.6	2.2	2.2	2.7	2.7	2.7	2.7	3.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°    - - 45°-225°    - - - - 90°-270°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)