

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581565

Luminaire Tested: **HCC6W10D010MB-HM60525827-61WWBB**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P581565
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-17)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6W10D010MB-HM60525827-61WWBB
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, WHITE BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 919.4 lumens
Efficiency: N/A
Efficacy: 92.9 lumens/watt
Spacing Criteria (0/90/45): 1.15 / 1.06 / 1.14
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P581565
CATALOG NUMBER: HCC6W10D010MB-HM60525827-61WWBB

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P581565

CATALOG NUMBER: HCC6W10D010MB-HM60525827-61WWBB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20										
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	108	104	101	109	105	102	100	101	99	97	97	95	94	94	92	91	89								
2	103	97	91	87	101	95	90	86	91	87	84	88	85	82	85	83	80	78								
3	96	87	80	75	93	86	79	74	83	77	73	80	76	72	78	74	71	69								
4	89	79	71	66	87	78	71	65	75	69	64	73	68	64	71	66	63	61								
5	83	72	64	58	81	71	63	58	69	62	57	67	61	57	65	60	56	54								
6	77	65	58	52	75	65	57	52	63	56	51	61	55	51	60	55	51	49								
7	72	60	52	47	70	59	52	47	58	51	46	56	51	46	55	50	46	44								
8	67	55	48	43	66	55	47	42	53	47	42	52	46	42	51	46	42	40								
9	63	51	44	39	62	51	44	39	50	43	39	49	43	38	48	42	38	37								
10	60	48	40	36	58	47	40	36	46	40	36	45	40	35	45	39	35	34								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	28287	28287	28287
5°	28830	28230	27592
10°	29809	27872	26697
15°	30721	27389	25863
20°	31199	26246	24508
25°	30637	24443	22822
30°	29118	22276	20946
35°	26174	19910	18892
40°	22585	17447	16874
45°	19126	15025	14629
50°	16400	12682	12562
55°	14212	10676	10265
60°	12411	8673	7324
65°	10922	6680	4047
70°	9425	4424	1971
75°	7985	2160	763
80°	6188	916	474
85°	3648	440	440



TEST NUMBER: P581565
 CATALOG NUMBER: HCC6W10D010MB-HM60525827-61WWBB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	48.7	5.3
10°-20°	137.7	15.0
20°-30°	193.9	21.1
30°-40°	198.1	21.5
40°-50°	159.7	17.4
50°-60°	107.1	11.7
60°-70°	54.2	5.9
70°-80°	17.3	1.9
80°-90°	2.7	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	380.2	41.4
0°-40°	578.3	62.9
0°-60°	845.2	91.9
0°-90°	919.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	919.4	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	516	516	516	516	516	
5°	524	520	513	505	501	50
15°	541	520	483	461	456	153
25°	506	467	404	379	377	232
35°	391	356	298	281	282	243
45°	247	227	194	187	189	192
55°	149	132	112	107	107	134
65°	84	70	52	34	31	84
75°	38	27	10	4	4	41
85°	6	3	1	1	1	8
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P581565

CATALOG NUMBER: HCC6W10D010MB-HM60525827-61WWBB

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	516.0	516.0	516.0	516.0	516.0	516.0	516.0	516.0	516.0
2.5°	518.1	517.3	516.6	515.2	513.0	510.9	509.4	507.9	507.2
5°	523.9	522.4	520.3	517.3	513.0	507.9	505.0	502.2	501.4
7.5°	531.9	529.0	523.2	516.6	509.4	502.2	497.1	494.1	492.0
10°	535.5	530.5	522.4	511.6	500.7	492.0	485.4	481.1	479.6
12.5°	538.4	532.6	520.9	506.5	492.0	480.4	473.1	469.4	468.1
15°	541.3	535.5	519.6	500.7	482.6	468.8	460.7	457.1	455.7
17.5°	541.3	533.3	514.5	490.5	468.8	452.1	444.1	440.5	439.8
20°	534.8	526.0	502.8	474.5	449.9	431.1	423.8	421.6	420.1
22.5°	522.4	512.3	486.2	454.3	427.4	409.2	401.3	399.8	398.4
25°	506.5	496.4	466.6	432.4	404.1	386.0	379.4	378.1	377.3
27.5°	486.2	475.3	444.1	409.2	378.8	361.3	355.6	355.6	354.9
30°	460.0	447.7	417.3	382.4	351.9	336.0	331.6	331.6	330.9
32.5°	428.1	415.8	388.2	354.9	325.8	309.1	305.5	306.9	306.2
35°	391.1	380.9	355.6	323.0	297.5	282.3	280.8	282.3	282.3
37.5°	354.1	344.7	323.0	294.7	270.7	256.9	256.9	259.0	258.3
40°	315.6	308.4	288.1	263.4	243.8	234.3	233.0	235.1	235.8
42.5°	279.4	273.6	256.2	235.8	218.4	209.0	211.1	212.6	213.4
45°	246.7	240.9	227.1	206.0	193.8	187.2	187.2	189.4	188.7
47.5°	217.7	213.4	199.6	179.2	168.3	165.5	166.9	168.3	168.3
50°	192.3	185.8	172.7	156.8	148.7	145.1	146.6	147.3	147.3
52.5°	168.3	164.0	150.9	136.4	129.2	127.0	127.0	127.7	127.7
55°	148.7	143.7	132.1	117.5	111.7	108.9	106.6	106.0	107.4
57.5°	129.8	125.5	114.7	100.9	94.3	91.5	87.1	85.6	87.1
60°	113.2	109.6	98.7	85.6	79.1	73.2	68.3	65.3	66.8
62.5°	98.7	94.3	83.4	72.6	65.3	58.8	50.8	46.4	48.6
65°	84.2	80.6	69.6	58.8	51.5	43.6	34.1	31.2	31.2
67.5°	71.1	67.5	57.3	47.9	39.2	29.8	21.1	20.3	21.1
70°	58.8	55.1	46.4	37.0	27.6	18.1	12.3	12.3	12.3
72.5°	48.6	44.3	36.3	26.8	17.4	9.4	6.6	7.2	7.2
75°	37.7	34.1	26.8	18.1	10.2	4.3	3.6	3.6	3.6
77.5°	28.3	25.4	18.9	11.7	5.1	1.5	1.5	1.5	1.5
80°	19.6	16.6	12.3	7.2	2.9	1.5	1.5	1.5	1.5
82.5°	11.7	10.2	7.2	3.6	1.5	0.7	0.7	0.7	0.7
85°	5.8	5.1	2.9	1.5	0.7	0.7	0.7	0.7	0.7
87.5°	1.5	1.5	0.7	0.7	0.0	0.7	0.7	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)