

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581576

Luminaire Tested: **HCC6S10D010MW-HM60525830-61RWWC**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P581576
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-14)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6S10D010MW-HM60525830-61RWWC
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1162.8 lumens
Efficiency: N/A
Efficacy: 117.5 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.15 / 1.2
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P581576
CATALOG NUMBER: HCC6S10D010MW-HM60525830-61RWWC

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P581576

CATALOG NUMBER: HCC6S10D010MW-HM60525830-61RWWC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	88					88			
2	103	96	90	86	100	94	89	85	91	86	83	88	84	81	85	82	79	77					77			
3	95	86	79	74	93	85	78	73	82	76	72	79	75	71	77	73	69	68					68			
4	88	78	70	64	86	76	69	64	74	68	63	72	67	62	70	65	61	60					60			
5	82	70	62	57	80	69	62	56	67	61	56	65	60	55	64	59	55	53					53			
6	76	64	56	50	74	63	56	50	62	55	50	60	54	49	58	53	49	47					47			
7	71	59	51	45	69	58	50	45	56	50	45	55	49	45	54	48	44	42					42			
8	66	54	46	41	65	53	46	41	52	45	41	51	45	40	50	44	40	38					38			
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35					35			
10	59	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32					32			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	31576	31576	31576
5°	31741	31912	31912
10°	32626	32064	31930
15°	33666	32248	32248
20°	34058	31509	32232
25°	33371	29929	31345
30°	31574	27814	29441
35°	28569	25437	26689
40°	24854	23015	23909
45°	21235	20506	21235
50°	18635	17978	18703
55°	16257	15149	15741
60°	14374	12576	12411
65°	12764	9923	8496
70°	11268	7004	5129
75°	9595	3961	2478
80°	7135	1200	758
85°	3900	503	503



TEST NUMBER: P581576
 CATALOG NUMBER: HCC6S10D010MW-HM60525830-61RWWC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	55.3	4.8
10°-20°	161.6	13.9
20°-30°	236.1	20.3
30°-40°	247.6	21.3
40°-50°	208.6	17.9
50°-60°	146.1	12.6
60°-70°	78.4	6.7
70°-80°	26.3	2.3
80°-90°	2.9	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	453.0	39.0
0°-40°	700.6	60.2
0°-60°	1055.3	90.8
0°-90°	1162.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1162.8	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	576	576	576	576	576	
5°	577	579	580	580	580	55
15°	593	585	568	565	568	167
25°	552	528	495	503	518	253
35°	427	405	380	391	399	265
45°	274	269	264	272	274	213
55°	170	165	158	162	165	153
65°	98	90	76	63	66	98
75°	45	35	19	12	12	48
85°	6	3	1	1	1	9
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P581576

CATALOG NUMBER: HCC6S10D010MW-HM60525830-61RWWC

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	576.0	576.0	576.0	576.0	576.0	576.0	576.0	576.0	576.0
2.5°	572.1	572.1	573.6	575.2	576.8	576.8	577.5	578.3	577.5
5°	576.8	576.8	579.1	579.9	579.9	579.1	579.9	579.9	579.9
7.5°	583.8	582.2	583.0	581.4	579.9	579.1	578.3	578.3	578.3
10°	586.1	584.6	583.0	579.9	576.0	573.6	572.9	573.6	573.6
12.5°	589.2	587.7	583.8	577.5	572.9	568.9	568.2	569.7	569.7
15°	593.2	591.6	585.4	575.2	568.2	564.3	565.1	566.6	568.2
17.5°	593.2	590.0	579.9	566.6	558.1	554.1	557.3	561.1	563.5
20°	583.8	580.7	566.6	550.3	540.1	537.7	543.2	550.3	552.5
22.5°	571.3	565.1	548.7	529.1	518.2	518.2	526.0	534.6	537.7
25°	551.7	547.1	528.4	505.8	494.8	494.0	503.4	515.1	518.2
27.5°	529.9	523.7	503.4	480.0	468.3	469.1	479.2	490.9	494.0
30°	498.8	490.9	472.9	450.3	439.4	442.5	452.7	461.3	465.1
32.5°	463.6	456.5	440.2	419.1	409.8	412.8	421.4	429.3	432.4
35°	426.9	419.1	405.0	386.4	380.1	383.2	391.0	397.2	398.8
37.5°	385.6	380.1	369.9	355.1	350.5	354.3	360.5	364.5	366.1
40°	347.3	342.7	334.1	323.1	321.6	324.7	330.9	333.3	334.1
42.5°	309.8	306.0	300.4	292.6	292.6	295.8	301.2	302.8	303.6
45°	273.9	271.6	269.3	263.0	264.5	268.5	271.6	273.9	273.9
47.5°	242.7	243.5	240.4	235.7	237.3	241.1	243.5	245.9	245.9
50°	218.5	216.2	213.0	208.4	210.8	213.8	217.0	218.5	219.3
52.5°	190.4	189.6	187.3	181.8	183.4	185.0	188.1	190.4	191.2
55°	170.1	167.8	164.7	158.5	158.5	160.0	161.5	163.1	164.7
57.5°	150.7	148.3	143.7	136.6	135.8	135.8	135.0	136.6	138.9
60°	131.1	130.3	123.3	117.0	114.7	112.4	109.2	110.0	113.2
62.5°	114.0	112.4	106.2	98.4	93.6	89.8	85.8	85.1	88.2
65°	98.4	96.8	89.8	82.0	76.5	69.5	63.2	63.2	65.5
67.5°	84.3	81.2	74.9	66.3	59.3	50.7	44.5	46.1	46.9
70°	70.3	67.9	60.9	52.3	43.7	35.1	31.2	32.0	32.0
72.5°	57.7	54.7	47.7	39.1	30.5	22.6	21.1	20.3	20.3
75°	45.3	42.1	35.1	26.5	18.7	13.2	11.7	11.7	11.7
77.5°	32.8	30.5	24.2	16.4	10.2	6.2	5.4	4.6	4.6
80°	22.6	20.3	14.8	8.6	3.8	2.4	2.4	2.4	2.4
82.5°	13.2	11.0	7.0	3.8	1.6	0.8	0.8	0.8	0.8
85°	6.2	4.6	3.2	1.6	0.8	0.8	0.8	0.8	0.8
87.5°	0.8	0.8	0.8	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)