

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581602

Luminaire Tested: **HCC6S10D010BZ-HM60525835-61WWBB**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P581602
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-17)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6S10D010BZ-HM60525835-61WWBB
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, WHITE BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1004.7 lumens
Efficiency: N/A
Efficacy: 101.5 lumens/watt
Spacing Criteria (0/90/45): 1.15 / 1.06 / 1.14
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P581602
CATALOG NUMBER: HCC6S10D010BZ-HM60525835-61WWBB

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P581602

CATALOG NUMBER: HCC6S10D010BZ-HM60525835-61WWBB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	111	108	104	101	109	105	102	100	101	99	97	97	95	94	94	92	91	89					89			
2	103	97	91	87	101	95	90	86	91	87	84	88	85	82	85	83	80	78					78			
3	96	87	80	75	93	86	79	74	83	77	73	80	76	72	78	74	71	69					69			
4	89	79	71	66	87	78	71	65	75	69	64	73	68	64	71	66	63	61					61			
5	83	72	64	58	81	71	63	58	69	62	57	67	61	57	65	60	56	54					54			
6	77	65	58	52	75	65	57	52	63	56	51	61	55	51	60	55	51	49					49			
7	72	60	52	47	70	59	52	47	58	51	46	56	51	46	55	50	46	44					44			
8	67	55	48	43	66	55	47	42	53	47	42	52	46	42	51	46	42	40					40			
9	63	51	44	39	62	51	44	39	50	43	39	49	43	38	48	42	38	37					37			
10	60	48	40	36	58	47	40	36	46	40	36	45	40	35	45	39	35	34					34			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	30902	30902	30902
5°	31504	30850	30151
10°	32576	30455	29174
15°	33576	29926	28263
20°	34099	28679	26783
25°	33474	26717	24939
30°	31821	24339	22890
35°	28603	21757	20646
40°	24682	19071	18449
45°	20901	16413	15978
50°	17918	13867	13731
55°	15541	11670	11221
60°	13563	9484	7993
65°	11934	7303	4423
70°	10290	4825	2164
75°	8727	2351	847
80°	6756	1010	505
85°	3963	503	503



TEST NUMBER: P581602
 CATALOG NUMBER: HCC6S10D010BZ-HM60525835-61WWBB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	53.2	5.3
10°-20°	150.4	15.0
20°-30°	211.9	21.1
30°-40°	216.5	21.5
40°-50°	174.5	17.4
50°-60°	117.1	11.7
60°-70°	59.2	5.9
70°-80°	18.9	1.9
80°-90°	2.9	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	415.5	41.4
0°-40°	632.0	62.9
0°-60°	923.6	91.9
0°-90°	1004.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1004.7	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	564	564	564	564	564	
5°	572	568	561	552	548	55
15°	592	568	527	504	498	167
25°	553	510	442	415	412	253
35°	427	388	325	307	308	266
45°	270	248	212	205	206	210
55°	163	144	122	117	117	146
65°	92	76	56	37	34	92
75°	41	29	11	4	4	44
85°	6	3	1	1	1	9
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P581602

CATALOG NUMBER: HCC6S10D010BZ-HM60525835-61WWBB

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	563.7	563.7	563.7	563.7	563.7	563.7	563.7	563.7	563.7
2.5°	566.1	565.3	564.5	562.9	560.6	558.2	556.6	555.0	554.2
5°	572.5	570.9	568.5	565.3	560.6	555.0	551.8	548.7	547.9
7.5°	581.3	578.0	571.7	564.5	556.6	548.7	543.1	540.0	537.6
10°	585.2	579.7	570.9	559.0	547.1	537.6	530.5	525.7	524.1
12.5°	588.4	582.1	569.3	553.4	537.6	524.9	517.0	513.0	511.4
15°	591.6	585.2	567.7	547.1	527.3	512.2	503.5	499.6	498.0
17.5°	591.6	582.9	562.2	536.0	512.2	494.0	485.3	481.3	480.5
20°	584.5	574.8	549.5	518.6	491.6	471.0	463.1	460.7	459.1
22.5°	570.9	559.8	531.2	496.4	467.1	447.3	438.5	437.0	435.4
25°	553.4	542.3	509.9	472.6	441.7	421.9	414.8	413.1	412.3
27.5°	531.2	519.4	485.3	447.3	414.0	394.8	388.5	388.5	387.7
30°	502.7	489.3	456.0	417.9	384.5	367.1	362.4	362.4	361.6
32.5°	467.9	454.4	424.3	387.7	356.0	337.8	333.8	335.4	334.6
35°	427.4	416.3	388.5	352.8	325.1	308.5	306.9	308.5	308.5
37.5°	386.9	376.6	352.8	321.9	295.8	280.7	280.7	283.1	282.3
40°	344.9	337.0	314.8	287.9	266.5	256.2	254.6	257.0	257.8
42.5°	305.3	299.0	279.9	257.8	238.6	228.3	230.7	232.3	233.1
45°	269.6	263.3	248.1	225.2	211.7	204.6	204.6	206.9	206.1
47.5°	237.8	233.1	218.0	195.8	184.0	180.8	182.4	184.0	184.0
50°	210.1	203.0	188.7	171.3	162.6	158.6	160.2	161.0	161.0
52.5°	184.0	179.2	164.9	149.1	141.2	138.8	138.8	139.6	139.6
55°	162.6	157.0	144.3	128.5	122.1	119.0	116.6	115.8	117.4
57.5°	142.0	137.2	125.3	110.3	103.1	100.0	95.2	93.6	95.2
60°	123.7	119.8	107.9	93.6	86.5	80.0	74.5	71.3	72.9
62.5°	107.9	103.1	91.2	79.2	71.3	64.2	55.5	50.7	53.1
65°	92.0	88.1	76.1	64.2	56.3	47.5	37.2	34.1	34.1
67.5°	77.7	73.7	62.6	52.3	42.8	32.5	23.0	22.2	23.0
70°	64.2	60.2	50.7	40.4	30.1	19.8	13.5	13.5	13.5
72.5°	53.1	48.3	39.6	29.3	19.0	10.3	7.1	7.9	7.9
75°	41.2	37.2	29.3	19.8	11.1	4.8	4.0	4.0	4.0
77.5°	30.9	27.7	20.6	12.7	5.5	1.6	1.6	1.6	1.6
80°	21.4	18.2	13.5	7.9	3.2	1.6	1.6	1.6	1.6
82.5°	12.7	11.1	7.9	4.0	1.6	0.8	0.8	0.8	0.8
85°	6.3	5.5	3.2	1.6	0.8	0.8	0.8	0.8	0.8
87.5°	1.6	1.6	0.8	0.8	0.0	0.8	0.8	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)