

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581603

Luminaire Tested: **HCC6W10D010SL-HM60525835-61WWW**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P581603
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6W10D010SL-HM60525835-61WWW
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1097.4 lumens
Efficiency: N/A
Efficacy: 110.9 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.06 / 1.14
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P581603
CATALOG NUMBER: HCC6W10D010SL-HM60525835-61WWW

Luminous Intensity Polar Plot





TEST NUMBER: P581603

CATALOG NUMBER: HCC6W10D010SL-HM60525835-61WWW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	93	91	89	87								
2	102	95	89	84	99	93	88	83	90	85	81	86	83	79	83	80	78	76								
3	94	85	78	72	92	83	77	71	80	75	70	78	73	69	75	71	68	66								
4	87	76	69	63	85	75	68	62	73	67	62	71	65	61	69	64	60	58								
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51								
6	75	63	55	49	73	62	55	49	61	54	49	59	53	48	57	52	48	46								
7	70	58	50	44	69	57	50	44	56	49	44	54	48	44	53	48	43	42								
8	66	53	46	40	64	53	45	40	51	45	40	50	44	40	49	44	39	38								
9	62	49	42	37	60	49	42	37	48	41	36	47	41	36	46	40	36	34								
10	58	46	39	34	57	45	38	34	44	38	33	44	38	33	43	37	33	32								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	32300	32300	32300
5°	33733	32198	30718
10°	34652	31646	28868
15°	35511	30959	27049
20°	35668	29560	24846
25°	34913	27679	22780
30°	33125	25447	20883
35°	30089	22874	18732
40°	26213	20374	16853
45°	22685	17824	14815
50°	19812	15351	12989
55°	17510	13495	11144
60°	15733	11830	9659
65°	14100	10273	9352
70°	12566	8768	8768
75°	10908	7392	8218
80°	8745	6251	7514
85°	5975	5472	6479



TEST NUMBER: P581603
 CATALOG NUMBER: HCC6W10D010SL-HM60525835-61WWW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	55.4	5.0
10°-20°	153.9	14.0
20°-30°	214.5	19.5
30°-40°	221.0	20.1
40°-50°	183.2	16.7
50°-60°	131.7	12.0
60°-70°	83.8	7.6
70°-80°	43.0	3.9
80°-90°	10.9	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	423.8	38.6
0°-40°	644.8	58.8
0°-60°	959.6	87.4
0°-90°	1097.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1097.4	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	589	589	589	589	589	
5°	613	604	585	566	558	59
15°	626	602	546	496	477	176
25°	577	538	458	399	377	264
35°	450	413	342	297	280	279
45°	293	272	230	201	191	226
55°	183	168	141	125	117	165
65°	109	97	79	69	72	109
75°	52	44	35	36	39	55
85°	10	9	9	10	10	12
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P581603

CATALOG NUMBER: HCC6W10D010SL-HM60525835-61WWW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	589.2	589.2	589.2	589.2	589.2	589.2	589.2	589.2	589.2
2.5°	600.3	597.9	594.8	591.6	586.7	581.2	576.4	574.8	572.5
5°	613.0	609.8	603.5	595.5	585.1	574.8	566.1	560.6	558.2
7.5°	620.9	616.9	608.2	594.8	579.6	564.5	551.8	543.9	540.8
10°	622.5	618.5	606.6	588.3	568.5	547.9	532.0	522.5	518.6
12.5°	624.9	619.3	604.3	582.8	557.4	533.6	513.8	501.9	498.0
15°	625.7	619.3	601.9	575.6	545.5	517.0	495.6	481.3	476.6
17.5°	622.5	615.4	594.8	562.9	528.9	498.8	473.4	458.3	452.0
20°	611.4	603.5	579.6	543.9	506.7	475.0	448.8	433.0	425.9
22.5°	597.1	586.7	559.8	521.7	482.9	449.6	423.5	407.5	400.4
25°	577.2	567.7	537.6	497.2	457.6	422.7	398.8	382.2	376.6
27.5°	554.2	543.1	512.2	471.8	431.4	396.4	373.4	358.4	351.3
30°	523.3	513.0	482.1	441.7	402.0	369.5	345.7	333.0	329.9
32.5°	486.9	478.2	448.0	409.9	371.9	341.8	321.9	308.5	305.3
35°	449.6	439.3	413.1	377.4	341.8	314.8	296.6	284.7	279.9
37.5°	409.1	399.6	377.4	345.7	314.0	288.7	272.8	262.5	257.8
40°	366.3	359.2	338.6	313.2	284.7	262.5	248.9	240.2	235.5
42.5°	326.7	319.6	305.3	281.5	257.8	237.8	225.9	218.0	214.1
45°	292.6	286.3	272.0	251.3	229.9	213.3	200.6	195.0	191.1
47.5°	258.5	255.4	242.6	223.6	203.8	189.5	180.8	174.4	171.3
50°	232.3	228.3	216.4	196.6	180.0	168.9	161.0	155.4	152.3
52.5°	205.3	201.4	190.3	173.6	160.2	149.9	142.0	137.2	134.0
55°	183.2	180.0	168.1	153.0	141.2	132.4	125.3	119.8	116.6
57.5°	162.6	159.4	148.3	134.0	123.7	115.8	109.5	104.7	100.7
60°	143.5	141.2	130.1	116.6	107.9	100.0	94.4	90.4	88.1
62.5°	126.9	122.1	112.6	100.7	92.8	86.5	80.8	78.4	80.0
65°	108.7	106.3	96.8	86.5	79.2	72.9	68.9	70.5	72.1
67.5°	93.6	90.4	82.4	72.9	66.6	61.8	59.4	62.6	63.4
70°	78.4	75.3	68.1	60.2	54.7	51.5	51.5	53.9	54.7
72.5°	64.2	61.8	55.5	49.1	45.2	42.8	44.4	46.0	46.8
75°	51.5	49.1	44.4	38.8	34.9	34.9	36.5	38.0	38.8
77.5°	39.6	38.0	33.3	29.3	27.7	27.7	29.3	30.1	30.9
80°	27.7	26.1	23.8	21.4	19.8	21.4	23.0	23.0	23.8
82.5°	18.2	17.4	15.8	14.3	14.3	15.1	15.8	16.6	16.6
85°	9.5	9.5	8.7	7.9	8.7	9.5	9.5	10.3	10.3
87.5°	3.2	3.2	3.2	3.2	4.0	4.0	4.0	4.0	4.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)