

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P593069

Luminaire Tested: **HCC6S10D010MB-HM60525850-61WWWB**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P593069
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-18)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6S10D010MB-HM60525850-61WWWB
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 5000K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1172.9 lumens
Efficiency: N/A
Efficacy: 118.5 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.09 / 1.17
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P593069
CATALOG NUMBER: HCC6S10D010MB-HM60525850-61WWWB

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P593069

CATALOG NUMBER: HCC6S10D010MB-HM60525850-61WWWB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100				
1	111	107	103	100	108	104	101	98	100	97	95	96	94	92	93	91	89	87				87				
2	102	95	89	84	100	93	88	83	90	85	81	87	83	80	84	81	78	76				76				
3	94	85	78	72	92	84	77	72	81	75	71	78	73	69	76	72	68	66				66				
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58				58				
5	81	70	61	56	79	68	61	55	66	60	55	65	59	54	63	58	54	52				52				
6	75	63	55	49	74	62	55	49	61	54	49	59	53	48	58	52	48	46				46				
7	70	58	50	44	69	57	50	44	56	49	44	54	48	44	53	48	43	42				42				
8	66	53	46	40	64	53	45	40	51	45	40	50	44	40	49	44	39	38				38				
9	62	49	42	37	60	49	42	37	48	41	36	47	41	36	46	40	36	34				34				
10	58	46	38	34	57	45	38	33	44	38	33	43	37	33	43	37	33	31				31				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	32832	32832	32832
5°	33546	32825	32236
10°	34568	32520	31423
15°	35664	32083	30647
20°	36228	30879	29403
25°	35633	29052	27715
30°	33923	26928	25896
35°	30939	24313	23932
40°	27051	21841	21726
45°	23281	19219	19669
50°	20238	16750	17100
55°	17672	14700	14853
60°	15700	12729	11666
65°	14009	10715	8911
70°	12326	8784	7469
75°	10569	6926	7096
80°	8555	5935	6977
85°	5724	5158	6164



TEST NUMBER: P593069
 CATALOG NUMBER: HCC6S10D010MB-HM60525850-61WWWB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	56.7	4.8
10°-20°	161.4	13.8
20°-30°	230.5	19.6
30°-40°	241.4	20.6
40°-50°	203.2	17.3
50°-60°	144.6	12.3
60°-70°	84.7	7.2
70°-80°	40.1	3.4
80°-90°	10.3	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	448.6	38.2
0°-40°	690.0	58.8
0°-60°	1037.9	88.5
0°-90°	1172.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1172.9	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	599	599	599	599	599	
5°	610	605	596	588	586	59
15°	628	606	565	542	540	177
25°	589	547	480	457	458	270
35°	462	424	363	351	358	287
45°	300	278	248	249	254	233
55°	185	169	154	154	155	167
65°	108	96	83	70	69	108
75°	50	42	33	32	34	54
85°	9	7	8	10	10	12
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P593069

CATALOG NUMBER: HCC6S10D010MB-HM60525850-61WWWB

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	598.9	598.9	598.9	598.9	598.9	598.9	598.9	598.9	598.9
2.5°	599.7	599.7	598.9	598.1	596.5	594.0	592.4	590.8	590.8
5°	609.6	607.9	604.6	600.5	596.5	591.6	588.3	585.8	585.8
7.5°	617.7	614.4	607.9	600.5	593.2	586.6	580.9	577.7	576.9
10°	621.0	616.9	607.1	595.7	584.2	575.2	568.6	564.5	564.5
12.5°	624.3	619.3	606.3	589.9	575.2	562.9	556.4	553.1	552.3
15°	628.4	621.8	605.5	585.0	565.3	551.5	542.5	540.0	540.0
17.5°	628.4	620.2	599.7	574.4	549.8	534.3	526.2	523.7	524.5
20°	621.0	612.0	587.5	556.4	529.3	513.0	504.9	503.2	504.0
22.5°	607.1	596.5	568.6	535.1	505.7	488.5	481.1	481.1	480.3
25°	589.1	577.7	547.3	512.2	480.3	463.1	457.3	458.2	458.2
27.5°	565.3	553.9	523.7	486.0	454.0	437.0	432.9	434.5	435.3
30°	535.9	523.7	491.7	455.0	425.4	408.3	405.8	408.3	409.1
32.5°	499.9	490.9	459.8	422.2	394.4	379.7	378.9	381.3	384.5
35°	462.3	452.5	423.8	389.4	363.3	351.0	351.0	355.1	357.6
37.5°	421.3	411.6	385.3	356.7	334.6	323.2	324.8	329.0	329.8
40°	378.0	370.6	348.5	324.0	305.2	296.1	298.6	302.7	303.6
42.5°	337.1	330.5	312.5	290.5	276.5	270.0	273.3	278.1	279.8
45°	300.3	293.0	278.1	259.3	247.9	244.6	248.7	252.0	253.7
47.5°	266.7	260.1	247.9	230.7	222.6	221.0	225.0	226.6	228.3
50°	237.3	230.7	218.5	203.0	196.4	196.4	199.7	201.3	200.5
52.5°	208.6	203.0	191.4	178.4	174.3	174.3	176.7	177.5	179.2
55°	184.9	179.2	169.3	157.1	153.8	152.1	153.8	153.8	155.4
57.5°	162.8	157.9	148.9	137.4	133.3	131.8	130.9	130.1	131.8
60°	143.2	139.1	129.3	119.4	116.1	112.1	108.8	105.5	106.4
62.5°	125.2	121.1	112.1	102.2	99.0	93.3	89.2	85.1	86.7
65°	108.0	103.9	95.8	87.5	82.6	76.1	69.5	67.1	68.7
67.5°	92.5	89.2	81.1	72.8	68.7	61.4	54.8	54.8	55.6
70°	76.9	73.7	67.1	59.8	54.8	48.2	45.8	46.6	46.6
72.5°	63.1	60.6	54.0	47.4	42.6	38.5	38.5	39.3	40.1
75°	49.9	48.2	41.8	36.0	32.7	30.2	31.9	32.7	33.5
77.5°	38.5	36.0	31.1	27.1	24.6	25.4	27.1	27.8	28.6
80°	27.1	26.1	22.1	19.6	18.8	19.6	21.3	22.1	22.1
82.5°	17.2	16.4	13.9	13.1	13.1	13.9	15.5	15.5	15.5
85°	9.1	8.2	7.4	7.4	8.2	9.1	9.8	9.8	9.8
87.5°	3.3	2.5	3.3	3.3	4.1	4.1	4.1	4.1	4.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)