

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581639

Luminaire Tested: **HCC6W10D010BZ-HM60525927-61WWWB**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P581639
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-18)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6W10D010BZ-HM60525927-61WWWB
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 878.2 lumens
Efficiency: N/A
Efficacy: 88.7 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.09 / 1.17
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P581639
CATALOG NUMBER: HCC6W10D010BZ-HM60525927-61WWWB

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P581639

CATALOG NUMBER: HCC6W10D010BZ-HM60525927-61WWWB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	111	107	103	100	108	104	101	98	100	97	95	96	94	92	93	91	89	87					87			
2	102	95	89	84	100	93	88	83	90	85	81	87	83	80	84	81	78	76					76			
3	94	85	78	72	92	84	77	72	81	75	71	78	73	69	76	72	68	66					66			
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58					58			
5	81	70	61	56	79	68	61	55	66	60	55	65	59	54	63	58	54	52					52			
6	75	63	55	49	74	62	55	49	61	54	49	59	53	48	58	52	48	46					46			
7	70	58	50	44	69	57	50	44	56	49	44	54	48	44	53	48	43	42					42			
8	66	53	46	40	64	53	45	40	51	45	40	50	44	40	49	44	39	38					38			
9	62	49	42	37	60	49	42	37	48	41	36	47	41	36	46	40	36	34					34			
10	58	46	38	34	57	45	38	33	44	38	33	43	37	33	43	37	33	31					31			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	24581	24581	24581
5°	25115	24576	24136
10°	25879	24348	23530
15°	26703	24024	22951
20°	27122	23120	22017
25°	26675	21751	20753
30°	25403	20161	19389
35°	23169	18203	17915
40°	20252	16359	16266
45°	17428	14389	14722
50°	15147	12537	12801
55°	13228	11001	11125
60°	11753	9528	8738
65°	10481	8029	6680
70°	9232	6588	5594
75°	7922	5189	5316
80°	6409	4420	5209
85°	4277	3837	4655



TEST NUMBER: P581639
 CATALOG NUMBER: HCC6W10D010BZ-HM60525927-61WWWB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	42.5	4.8
10°-20°	120.9	13.8
20°-30°	172.5	19.6
30°-40°	180.7	20.6
40°-50°	152.2	17.3
50°-60°	108.3	12.3
60°-70°	63.4	7.2
70°-80°	30.0	3.4
80°-90°	7.7	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	335.9	38.2
0°-40°	516.6	58.8
0°-60°	777.0	88.5
0°-90°	878.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	878.2	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	448	448	448	448	448	
5°	456	453	447	440	439	44
15°	470	453	423	406	404	133
25°	441	410	360	342	343	202
35°	346	317	272	263	268	215
45°	225	208	186	186	190	175
55°	138	127	115	115	116	125
65°	81	72	62	52	52	81
75°	37	31	24	24	25	40
85°	7	6	6	7	7	9
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P581639

CATALOG NUMBER: HCC6W10D010BZ-HM60525927-61WWWB

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	448.4	448.4	448.4	448.4	448.4	448.4	448.4	448.4	448.4
2.5°	449.1	449.1	448.4	447.8	446.6	444.8	443.5	442.3	442.3
5°	456.4	455.2	452.7	449.6	446.6	443.0	440.5	438.6	438.6
7.5°	462.5	460.0	455.2	449.6	444.1	439.2	434.9	432.5	431.9
10°	464.9	461.9	454.5	446.0	437.4	430.6	425.7	422.7	422.7
12.5°	467.4	463.8	453.9	441.7	430.6	421.4	416.6	414.1	413.5
15°	470.5	465.6	453.4	438.0	423.3	412.8	406.2	404.4	404.4
17.5°	470.5	464.3	449.1	430.0	411.7	400.0	393.9	392.0	392.7
20°	464.9	458.2	439.9	416.6	396.3	384.1	378.0	376.7	377.4
22.5°	454.5	446.6	425.7	400.6	378.5	365.7	360.2	360.2	359.6
25°	441.0	432.5	409.8	383.5	359.6	346.7	342.4	343.1	343.1
27.5°	423.3	414.8	392.0	363.9	339.9	327.1	324.1	325.3	325.9
30°	401.3	392.0	368.1	340.6	318.5	305.6	303.8	305.6	306.3
32.5°	374.4	367.6	344.2	316.1	295.2	284.2	283.7	285.5	287.9
35°	346.2	338.8	317.3	291.6	272.0	262.9	262.9	265.9	267.7
37.5°	315.5	308.1	288.5	267.0	250.5	242.0	243.2	246.2	246.9
40°	283.0	277.5	260.9	242.6	228.6	221.8	223.6	226.6	227.3
42.5°	252.4	247.5	234.0	217.5	207.0	202.2	204.7	208.3	209.5
45°	224.8	219.3	208.3	194.3	185.6	183.2	186.2	188.7	189.9
47.5°	199.7	194.8	185.6	172.7	166.6	165.4	168.4	169.7	170.9
50°	177.6	172.7	163.6	151.9	147.0	147.0	149.4	150.7	150.1
52.5°	156.2	151.9	143.3	133.6	130.5	130.5	132.3	132.9	134.1
55°	138.4	134.1	126.8	117.6	115.1	114.0	115.1	115.1	116.4
57.5°	121.9	118.2	111.5	102.9	99.8	98.6	98.0	97.4	98.6
60°	107.2	104.1	96.8	89.4	86.9	83.9	81.5	79.0	79.7
62.5°	93.7	90.7	83.9	76.5	74.1	69.8	66.8	63.7	65.0
65°	80.8	77.8	71.7	65.5	61.9	56.9	52.1	50.3	51.5
67.5°	69.3	66.8	60.7	54.6	51.5	46.0	41.1	41.1	41.7
70°	57.6	55.1	50.3	44.7	41.1	36.1	34.3	34.9	34.9
72.5°	47.2	45.3	40.4	35.5	31.8	28.8	28.8	29.4	30.0
75°	37.4	36.1	31.2	26.9	24.5	22.6	23.9	24.5	25.1
77.5°	28.8	26.9	23.3	20.3	18.3	19.0	20.3	20.8	21.4
80°	20.3	19.6	16.5	14.7	14.0	14.7	16.0	16.5	16.5
82.5°	12.9	12.2	10.4	9.8	9.8	10.4	11.7	11.7	11.7
85°	6.8	6.1	5.5	5.5	6.1	6.8	7.4	7.4	7.4
87.5°	2.5	1.8	2.5	2.5	3.1	3.1	3.1	3.1	3.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)