

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581649

Luminaire Tested: **HCC6S10D010SL-HM60525930-61RWWH**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P581649
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-15)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6S10D010SL-HM60525930-61RWWH
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1000.2 lumens
Efficiency: N/A
Efficacy: 101.0 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.12 / 1.19
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P581649
CATALOG NUMBER: HCC6S10D010SL-HM60525930-61RWWH

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P581649

CATALOG NUMBER: HCC6S10D010SL-HM60525930-61RWWH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88								
2	103	96	90	85	100	94	89	84	91	86	83	87	84	81	85	82	79	77								
3	95	86	79	74	93	84	78	73	82	76	72	79	74	70	77	73	69	67								
4	88	78	70	64	86	76	69	64	74	68	63	72	66	62	70	65	61	59								
5	82	70	62	57	80	69	62	56	67	61	56	65	60	55	64	59	55	53								
6	76	64	56	50	74	63	56	50	61	55	50	60	54	49	58	53	49	47								
7	71	59	51	45	69	58	50	45	56	50	45	55	49	44	54	48	44	42								
8	66	54	46	41	65	53	46	41	52	45	41	51	45	40	50	44	40	38								
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35								
10	59	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	27980	27980	27980
5°	28274	28016	27834
10°	28673	27928	27633
15°	29348	27753	27492
20°	29618	26929	27005
25°	28967	25574	26058
30°	27435	23757	24561
35°	24849	21710	22520
40°	21641	19630	20352
45°	18358	17374	18002
50°	16255	15181	15573
55°	14327	12979	12922
60°	12828	10931	10054
65°	11454	8769	7199
70°	10066	6331	4504
75°	8515	3834	2542
80°	6535	1673	1073
85°	3774	440	440



TEST NUMBER: P581649

CATALOG NUMBER: HCC6S10D010SL-HM60525930-61RWWH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	48.4	4.8
10°-20°	139.3	13.9
20°-30°	201.3	20.1
30°-40°	211.8	21.2
40°-50°	178.1	17.8
50°-60°	125.0	12.5
60°-70°	68.7	6.9
70°-80°	24.4	2.4
80°-90°	3.2	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	389.0	38.9
0°-40°	600.8	60.1
0°-60°	903.8	90.4
0°-90°	1000.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1000.2	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	510	510	510	510	510	
5°	514	512	509	507	506	49
15°	517	508	489	483	484	146
25°	479	455	423	424	431	219
35°	371	350	324	331	336	230
45°	237	230	224	230	232	186
55°	150	142	136	136	135	135
65°	88	79	68	56	56	88
75°	40	32	18	12	12	43
85°	6	3	1	1	1	8
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P581649

CATALOG NUMBER: HCC6S10D010SL-HM60525930-61RWWH

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	510.4	510.4	510.4	510.4	510.4	510.4	510.4	510.4	510.4
2.5°	510.4	510.4	509.7	509.7	508.4	508.4	507.7	507.7	507.7
5°	513.8	513.8	512.5	510.4	509.1	507.0	507.0	506.5	505.8
7.5°	515.7	515.1	513.1	510.4	507.0	503.7	502.4	503.1	502.4
10°	515.1	513.8	511.1	505.8	501.7	497.1	496.4	495.7	496.4
12.5°	516.4	514.4	509.1	502.4	495.7	490.4	489.7	489.7	490.4
15°	517.1	515.1	508.4	498.4	489.0	483.7	483.0	483.7	484.4
17.5°	515.1	512.5	502.4	489.0	478.3	472.9	472.9	474.3	475.7
20°	507.7	503.7	489.7	473.6	461.6	457.6	458.9	461.6	462.9
22.5°	494.3	489.7	473.6	455.5	442.8	439.6	442.8	446.2	447.5
25°	478.9	473.6	455.0	436.2	422.8	418.7	423.5	428.8	430.8
27.5°	458.2	452.2	434.8	413.4	400.0	398.0	403.3	409.4	410.7
30°	433.4	426.8	407.4	387.4	375.3	374.6	380.7	386.0	388.0
32.5°	403.3	397.3	380.7	360.5	349.9	349.9	355.9	360.5	362.6
35°	371.3	364.6	349.9	333.1	324.4	325.1	331.1	334.5	336.5
37.5°	333.1	331.1	319.8	305.8	299.6	301.0	305.8	308.4	310.4
40°	302.4	297.0	289.7	278.2	274.3	275.6	280.3	283.0	284.4
42.5°	269.0	265.6	259.6	251.5	248.8	250.9	254.9	256.9	256.2
45°	236.8	236.1	230.1	225.5	224.1	226.7	229.5	231.5	232.2
47.5°	213.4	210.8	205.3	202.1	200.7	203.4	206.0	207.4	207.4
50°	190.6	188.0	182.6	179.3	178.0	180.7	182.6	184.0	182.6
52.5°	167.9	165.3	160.5	156.6	155.9	157.2	157.9	158.6	159.8
55°	149.9	147.2	141.8	137.1	135.8	136.5	135.8	135.8	135.2
57.5°	132.4	129.7	124.4	119.1	117.0	116.4	114.4	113.8	113.1
60°	117.0	113.8	108.3	102.3	99.7	97.0	93.6	91.7	91.7
62.5°	102.3	99.0	92.9	87.6	83.7	78.9	73.6	70.9	70.9
65°	88.3	85.6	78.9	72.9	67.6	61.6	55.5	54.2	55.5
67.5°	74.9	72.2	65.5	59.5	52.9	45.5	40.2	40.2	41.4
70°	62.8	60.2	54.2	46.9	39.5	32.1	28.1	28.1	28.1
72.5°	51.5	48.8	42.1	35.4	28.1	20.7	18.7	19.4	18.7
75°	40.2	38.1	32.1	24.8	18.1	12.7	12.0	11.3	12.0
77.5°	30.1	28.1	22.8	16.1	10.1	7.4	6.7	6.7	6.7
80°	20.7	18.7	14.7	9.4	5.3	3.4	3.4	3.4	3.4
82.5°	12.7	10.8	8.0	4.6	2.0	2.0	2.0	2.0	2.0
85°	6.0	4.6	3.4	1.4	0.7	0.7	0.7	0.7	0.7
87.5°	1.4	1.4	0.7	0.7	0.0	0.7	0.7	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)