

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581728

Luminaire Tested: **HCC6S15D010SL-HM60525830-61WWW**

Issue Date: 9/16/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P581728  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-16)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/16/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC6S15D010SL-HM60525830-61WWW  
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, WHITE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1475.8 lumens  
Efficiency: N/A  
Efficacy: 105.4 lumens/watt  
Spacing Criteria (0/90/45): 1.1 / 1.06 / 1.14  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 14  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P581728  
CATALOG NUMBER: HCC6S15D010SL-HM60525830-61WWW

### Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P581728

CATALOG NUMBER: HCC6S15D010SL-HM60525830-61WWW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	93	91	89	87								
2	102	95	89	84	99	93	88	83	90	85	81	86	83	79	83	80	78	76								
3	94	85	78	72	92	83	77	71	80	75	70	78	73	69	75	71	68	66								
4	87	76	69	63	85	75	68	62	73	67	62	71	65	61	69	64	60	58								
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51								
6	75	63	55	49	73	62	55	49	61	54	49	59	53	48	57	52	48	46								
7	70	58	50	44	69	57	50	44	56	49	44	54	48	44	53	48	43	42								
8	66	53	46	40	64	53	45	40	51	45	40	50	44	40	49	44	39	38								
9	62	49	42	37	60	49	42	37	48	41	36	47	41	36	46	40	36	34								
10	58	46	39	34	57	45	38	34	44	38	33	44	38	33	43	37	33	32								

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	43429	43429	43429
5°	45355	43303	41311
10°	46598	42557	38816
15°	47747	41635	36368
20°	47960	39746	33405
25°	46950	37218	30631
30°	44545	34220	28080
35°	40462	30758	25190
40°	35252	27394	22664
45°	30507	23971	19925
50°	26652	20648	17466
55°	23540	18140	14977
60°	21161	15909	12981
65°	18951	13828	12582
70°	16926	11781	11781
75°	14678	9934	11056
80°	11775	8429	10102
85°	8051	7359	8680



TEST NUMBER: P581728  
 CATALOG NUMBER: HCC6S15D010SL-HM60525830-61WWW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	74.5	5.0
10°-20°	207.0	14.0
20°-30°	288.5	19.5
30°-40°	297.2	20.1
40°-50°	246.3	16.7
50°-60°	177.0	12.0
60°-70°	112.7	7.6
70°-80°	57.9	3.9
80°-90°	14.7	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	569.9	38.6
0°-40°	867.1	58.8
0°-60°	1290.4	87.4
0°-90°	1475.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1475.8	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	792	792	792	792	792	
5°	824	811	787	761	751	79
15°	841	809	734	666	641	237
25°	776	723	615	536	506	356
35°	605	556	460	399	376	376
45°	394	366	309	270	257	305
55°	246	226	190	168	157	222
65°	146	130	107	93	97	146
75°	69	60	47	49	52	74
85°	13	12	12	13	14	16
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P581728

CATALOG NUMBER: HCC6S15D010SL-HM60525830-61WWW

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	792.2	792.2	792.2	792.2	792.2	792.2	792.2	792.2	792.2
2.5°	807.2	804.0	799.7	795.4	789.1	781.6	775.2	773.0	769.9
5°	824.2	819.9	811.4	800.7	786.9	773.0	761.4	753.9	750.7
7.5°	834.9	829.6	817.9	799.7	779.4	759.2	742.2	731.5	727.2
10°	837.1	831.7	815.7	791.2	764.5	736.8	715.5	702.7	697.3
12.5°	840.2	832.7	812.5	783.7	749.6	717.7	691.0	675.0	669.6
15°	841.3	832.7	809.3	774.1	733.6	695.2	666.5	647.3	640.8
17.5°	837.1	827.4	799.7	757.0	711.2	670.7	636.6	616.3	607.8
20°	822.1	811.4	779.4	731.5	681.3	638.7	603.5	582.1	572.6
22.5°	802.9	789.1	752.8	701.7	649.3	604.6	569.4	548.1	538.4
25°	776.2	763.5	723.0	668.5	615.3	568.3	536.3	513.9	506.4
27.5°	745.4	730.4	688.8	634.5	580.1	533.1	502.2	481.9	472.4
30°	703.7	689.9	648.3	593.9	540.6	496.9	464.9	447.9	443.6
32.5°	654.7	643.0	602.5	551.3	500.1	459.6	432.9	414.7	410.5
35°	604.6	590.8	555.6	507.6	459.6	423.4	398.8	382.8	376.4
37.5°	550.2	537.4	507.6	464.9	422.2	388.2	366.8	353.0	346.5
40°	492.6	483.1	455.2	421.2	382.8	353.0	334.8	323.1	316.7
42.5°	439.4	429.7	410.5	378.5	346.5	319.8	303.8	293.3	287.9
45°	393.5	384.9	365.7	338.0	309.2	286.8	269.8	262.3	257.0
47.5°	347.7	343.3	326.3	300.7	274.0	254.8	243.1	234.6	230.3
50°	312.5	307.1	291.1	264.5	242.1	227.1	216.4	209.0	204.8
52.5°	276.1	270.8	255.9	233.5	215.4	201.6	190.9	184.4	180.2
55°	246.3	242.1	226.1	205.8	189.8	178.1	168.4	161.1	156.7
57.5°	218.6	214.3	199.4	180.2	166.4	155.7	147.1	140.7	135.4
60°	193.0	189.8	174.9	156.7	145.1	134.4	126.9	121.6	118.4
62.5°	170.6	164.2	151.4	135.4	124.7	116.2	108.7	105.6	107.7
65°	146.1	142.9	130.1	116.2	106.6	98.1	92.7	94.9	97.0
67.5°	125.9	121.6	110.9	98.1	89.6	83.2	80.0	84.2	85.4
70°	105.6	101.2	91.7	81.0	73.5	69.3	69.3	72.5	73.5
72.5°	86.4	83.2	74.7	66.1	60.7	57.5	59.7	61.9	62.9
75°	69.3	66.1	59.7	52.2	46.9	46.9	49.0	51.2	52.2
77.5°	53.3	51.2	44.8	39.5	37.3	37.3	39.5	40.5	41.5
80°	37.3	35.2	32.0	28.8	26.7	28.8	30.9	30.9	32.0
82.5°	24.5	23.5	21.3	19.2	19.2	20.2	21.3	22.4	22.4
85°	12.8	12.8	11.7	10.7	11.7	12.8	12.8	13.8	13.8
87.5°	4.3	4.3	4.3	4.3	5.3	5.3	5.3	5.3	5.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°    - - 45°-225°    - - - - 90°-270°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)