

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581746

Luminaire Tested: **HCC6S15D010BZ-HM60525835-61WWW**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P581746
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6S15D010BZ-HM60525835-61WWW
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1499.5 lumens
Efficiency: N/A
Efficacy: 107.1 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.06 / 1.14
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 14
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P581746
CATALOG NUMBER: HCC6S15D010BZ-HM60525835-61WWW

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P581746

CATALOG NUMBER: HCC6S15D010BZ-HM60525835-61WWW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	93	91	89	87								
2	102	95	89	84	99	93	88	83	90	85	81	86	83	79	83	80	78	76								
3	94	85	78	72	92	83	77	71	80	75	70	78	73	69	75	71	68	66								
4	87	76	69	63	85	75	68	62	73	67	62	71	65	61	69	64	60	58								
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51								
6	75	63	55	49	73	62	55	49	61	54	49	59	53	48	57	52	48	46								
7	70	58	50	44	69	57	50	44	56	49	44	54	48	44	53	48	43	42								
8	66	53	46	40	64	53	45	40	51	45	40	50	44	40	49	44	39	38								
9	62	49	42	37	60	49	42	37	48	41	36	47	41	36	46	40	36	34								
10	58	46	39	34	57	45	38	34	44	38	33	44	38	33	43	37	33	32								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	44125	44125	44125
5°	46087	44002	41971
10°	47344	43241	39445
15°	48513	42304	36953
20°	48736	40394	33941
25°	47706	37817	31127
30°	45260	34771	28530
35°	41111	31246	25598
40°	35817	27838	23029
45°	30988	24359	20235
50°	27078	20980	17739
55°	23923	18427	15216
60°	21500	16150	13190
65°	19263	14061	12790
70°	17198	11989	11989
75°	14911	10103	11247
80°	11965	8555	10260
85°	8240	7485	8869



TEST NUMBER: P581746
 CATALOG NUMBER: HCC6S15D010BZ-HM60525835-61WWW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	75.7	5.0
10°-20°	210.3	14.0
20°-30°	293.1	19.5
30°-40°	302.0	20.1
40°-50°	250.3	16.7
50°-60°	179.9	12.0
60°-70°	114.5	7.6
70°-80°	58.8	3.9
80°-90°	15.0	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	579.1	38.6
0°-40°	881.0	58.8
0°-60°	1311.2	87.4
0°-90°	1499.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1499.5	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	805	805	805	805	805	
5°	838	824	800	774	763	80
15°	855	822	745	677	651	241
25°	789	735	625	545	515	361
35°	614	564	467	405	382	382
45°	400	372	314	274	261	309
55°	250	230	193	171	159	225
65°	148	132	108	94	99	149
75°	70	61	48	50	53	75
85°	13	12	12	13	14	17
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P581746

CATALOG NUMBER: HCC6S15D010BZ-HM60525835-61WWW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	804.9	804.9	804.9	804.9	804.9	804.9	804.9	804.9	804.9
2.5°	820.2	816.9	812.5	808.2	801.8	794.2	787.7	785.4	782.2
5°	837.5	833.1	824.5	813.7	799.6	785.4	773.5	766.0	762.7
7.5°	848.3	842.9	830.9	812.5	792.0	771.3	754.1	743.2	738.9
10°	850.5	845.0	828.8	803.9	776.8	748.6	727.0	713.9	708.6
12.5°	853.7	846.1	825.6	796.3	761.6	729.1	702.0	685.8	680.4
15°	854.8	846.1	822.3	786.6	745.4	706.4	677.1	657.6	651.1
17.5°	850.5	840.7	812.5	769.2	722.7	681.5	646.8	626.2	617.6
20°	835.4	824.5	792.0	743.2	692.4	649.0	613.2	591.6	581.8
22.5°	815.8	801.8	764.9	712.9	659.8	614.3	578.5	556.8	547.1
25°	788.7	775.8	734.6	679.3	625.2	577.5	544.9	522.2	514.6
27.5°	757.3	742.2	699.8	644.7	589.4	541.7	510.3	489.8	480.0
30°	715.0	701.0	658.8	603.5	549.3	504.8	472.4	455.0	450.7
32.5°	665.2	653.3	612.1	560.1	508.1	466.9	439.8	421.4	417.1
35°	614.3	600.2	564.4	515.7	466.9	430.2	405.2	389.0	382.5
37.5°	559.0	546.0	515.7	472.4	429.0	394.4	372.7	358.7	352.1
40°	500.5	490.8	462.6	427.9	389.0	358.7	340.2	328.2	321.8
42.5°	446.4	436.6	417.1	384.7	352.1	325.1	308.7	297.9	292.5
45°	399.7	391.1	371.6	343.5	314.2	291.5	274.1	266.5	261.0
47.5°	353.2	348.9	331.5	305.5	278.4	258.9	247.0	238.4	234.0
50°	317.5	312.0	295.8	268.7	246.0	230.7	220.0	212.4	208.0
52.5°	280.6	275.2	260.0	237.2	218.8	204.8	194.0	187.4	183.1
55°	250.3	246.0	229.7	209.1	192.8	180.9	171.2	163.6	159.2
57.5°	222.1	217.8	202.6	183.1	169.0	158.2	149.5	143.0	137.6
60°	196.1	192.8	177.6	159.2	147.3	136.5	128.9	123.5	120.3
62.5°	173.3	166.8	153.8	137.6	126.8	118.0	110.5	107.3	109.4
65°	148.5	145.2	132.2	118.0	108.4	99.7	94.2	96.5	98.6
67.5°	127.8	123.5	112.7	99.7	91.0	84.6	81.3	85.6	86.7
70°	107.3	102.9	93.2	82.3	74.8	70.4	70.4	73.7	74.8
72.5°	87.7	84.6	75.8	67.2	61.7	58.5	60.7	62.9	63.9
75°	70.4	67.2	60.7	53.1	47.7	47.7	49.8	52.0	53.1
77.5°	54.1	52.0	45.5	40.1	37.9	37.9	40.1	41.2	42.2
80°	37.9	35.8	32.5	29.3	27.1	29.3	31.4	31.4	32.5
82.5°	25.0	23.8	21.7	19.5	19.5	20.5	21.7	22.7	22.7
85°	13.1	13.1	11.9	10.8	11.9	13.1	13.1	14.1	14.1
87.5°	4.3	4.3	4.3	4.3	5.4	5.4	5.4	5.4	5.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)