

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581781

Luminaire Tested: **HCC6W15D010BZ-HM60525927-61WWBB**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P581781
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-17)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6W15D010BZ-HM60525927-61WWBB
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, WHITE BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1060.9 lumens
Efficiency: N/A
Efficacy: 75.8 lumens/watt
Spacing Criteria (0/90/45): 1.15 / 1.06 / 1.14
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 14
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P581781
CATALOG NUMBER: HCC6W15D010BZ-HM60525927-61WWBB

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P581781

CATALOG NUMBER: HCC6W15D010BZ-HM60525927-61WWBB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20				
RC	80					70					50					30				
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	111	108	104	101	109	105	102	100	101	99	97	97	95	94	94	92	91	89		
2	103	97	91	87	101	95	90	86	91	87	84	88	85	82	85	83	80	78		
3	96	87	80	75	93	86	79	74	83	77	73	80	76	72	78	74	71	69		
4	89	79	71	66	87	78	71	65	75	69	64	73	68	64	71	66	63	61		
5	83	72	64	58	81	71	63	58	69	62	57	67	61	57	65	60	56	54		
6	77	65	58	52	75	65	57	52	63	56	51	61	55	51	60	55	51	49		
7	72	60	52	47	70	59	52	47	58	51	46	56	51	46	55	50	46	44		
8	67	55	48	43	66	55	47	42	53	47	42	52	46	42	51	46	42	40		
9	63	51	44	39	62	51	44	39	50	43	39	49	43	38	48	42	38	37		
10	60	48	40	36	58	47	40	36	46	40	36	45	40	35	45	39	35	34		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	32634	32634	32634
5°	33265	32578	31840
10°	34396	32158	30805
15°	35449	31601	29841
20°	36001	30283	28282
25°	35349	28211	26336
30°	33600	25706	24168
35°	30202	22975	21797
40°	26063	20138	19479
45°	22072	17335	16878
50°	18925	14635	14498
55°	16401	12320	11842
60°	14319	10010	8453
65°	12608	7718	4670
70°	10883	5097	2276
75°	9235	2478	890
80°	7135	1073	537
85°	4214	503	503



TEST NUMBER: P581781
 CATALOG NUMBER: HCC6W15D010BZ-HM60525927-61WWBB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	56.2	5.3
10°-20°	158.9	15.0
20°-30°	223.7	21.1
30°-40°	228.6	21.5
40°-50°	184.3	17.4
50°-60°	123.6	11.6
60°-70°	62.6	5.9
70°-80°	20.0	1.9
80°-90°	3.1	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	438.8	41.4
0°-40°	667.4	62.9
0°-60°	975.3	91.9
0°-90°	1060.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1060.9	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	595	595	595	595	595	
5°	604	600	592	583	579	58
15°	625	600	557	532	526	176
25°	584	538	466	438	435	268
35°	451	410	343	324	326	281
45°	285	262	224	216	218	221
55°	172	152	129	123	124	154
65°	97	80	60	39	36	97
75°	44	31	12	4	4	47
85°	7	3	1	1	1	9
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P581781

CATALOG NUMBER: HCC6W15D010BZ-HM60525927-61WWBB

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	595.3	595.3	595.3	595.3	595.3	595.3	595.3	595.3	595.3
2.5°	597.8	597.0	596.2	594.5	592.0	589.5	587.8	586.1	585.3
5°	604.5	602.9	600.3	597.0	592.0	586.1	582.7	579.4	578.6
7.5°	613.7	610.4	603.7	596.2	587.8	579.4	573.5	570.2	567.7
10°	617.9	612.1	602.9	590.3	577.7	567.7	560.1	555.1	553.4
12.5°	621.3	614.6	601.2	584.4	567.7	554.3	545.9	541.7	540.0
15°	624.6	617.9	599.5	577.7	556.8	540.9	531.6	527.5	525.8
17.5°	624.6	615.4	593.6	566.0	540.9	521.6	512.5	508.3	507.5
20°	617.1	607.0	580.2	547.6	519.1	497.4	489.0	486.5	484.8
22.5°	602.9	591.1	561.0	524.1	493.2	472.3	463.1	461.4	459.7
25°	584.4	572.7	538.4	499.1	466.4	445.5	437.9	436.2	435.4
27.5°	561.0	548.4	512.5	472.3	437.1	417.0	410.3	410.3	409.4
30°	530.8	516.7	481.5	441.3	406.1	387.7	382.6	382.6	381.8
32.5°	494.1	479.8	448.0	409.4	375.9	356.7	352.5	354.2	353.3
35°	451.3	439.6	410.3	372.6	343.3	325.7	324.0	325.7	325.7
37.5°	408.6	397.7	372.6	339.9	312.4	296.5	296.5	299.0	298.1
40°	364.2	355.8	332.4	304.0	281.4	270.5	268.8	271.3	272.2
42.5°	322.3	315.6	295.6	272.2	252.1	241.2	243.7	245.4	246.2
45°	284.7	278.0	262.1	237.8	223.6	216.0	216.0	218.5	217.7
47.5°	251.2	246.2	230.3	206.8	194.2	190.9	192.6	194.2	194.2
50°	221.9	214.4	199.3	180.8	171.6	167.4	169.1	170.0	170.0
52.5°	194.2	189.2	174.1	157.4	149.0	146.5	146.5	147.3	147.3
55°	171.6	165.8	152.4	135.6	128.9	125.6	123.0	122.2	123.9
57.5°	149.9	144.8	132.3	116.3	108.8	105.6	100.4	98.9	100.4
60°	130.6	126.4	113.8	98.9	91.3	84.6	78.7	75.4	77.1
62.5°	113.8	108.8	96.2	83.8	75.4	67.9	58.6	53.6	56.1
65°	97.2	93.0	80.4	67.9	59.5	50.3	39.4	36.0	36.0
67.5°	82.1	77.9	66.2	55.3	45.2	34.3	24.3	23.5	24.3
70°	67.9	63.7	53.6	42.7	31.8	20.9	14.2	14.2	14.2
72.5°	56.1	51.1	41.9	31.0	20.1	10.9	7.5	8.4	8.4
75°	43.6	39.4	31.0	20.9	11.7	5.0	4.2	4.2	4.2
77.5°	32.7	29.3	21.8	13.4	5.9	1.7	1.7	1.7	1.7
80°	22.6	19.3	14.2	8.4	3.4	1.7	1.7	1.7	1.7
82.5°	13.4	11.7	8.4	4.2	1.7	0.8	0.8	0.8	0.8
85°	6.7	5.9	3.4	1.7	0.8	0.8	0.8	0.8	0.8
87.5°	1.7	1.7	0.8	0.8	0.0	0.8	0.8	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)