

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581774

Luminaire Tested: **HCC6W15D010MB-HM60525927-61RWWC**

Issue Date: 9/16/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P581774  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-14)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/16/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC6W15D010MB-HM60525927-61RWWC  
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, SPECULAR TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1247.6 lumens  
Efficiency: N/A  
Efficacy: 89.1 lumens/watt  
Spacing Criteria (0/90/45): 1.22 / 1.15 / 1.2  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 14  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P581774  
CATALOG NUMBER: HCC6W15D010MB-HM60525927-61RWWC

### Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P581774

CATALOG NUMBER: HCC6W15D010MB-HM60525927-61RWWC

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	88								
2	103	96	90	86	100	94	89	85	91	86	83	88	84	81	85	82	79	77								
3	95	86	79	74	93	85	78	73	82	76	72	79	75	71	77	73	69	68								
4	88	78	70	64	86	76	69	64	74	68	63	72	67	62	70	65	61	60								
5	82	70	62	57	80	69	62	56	67	61	56	65	60	55	64	59	55	53								
6	76	64	56	50	74	63	56	50	62	55	50	60	54	49	58	53	49	47								
7	71	59	51	45	69	58	50	45	56	50	45	55	49	45	54	48	44	42								
8	66	54	46	41	65	53	46	41	52	45	41	51	45	40	50	44	40	38								
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35								
10	59	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32								

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	33879	33879	33879
5°	34052	34239	34239
10°	35008	34402	34262
15°	36118	34597	34597
20°	36537	33801	34583
25°	35809	32107	33631
30°	33866	29846	31593
35°	30657	27291	28636
40°	26664	24689	25648
45°	22793	22010	22793
50°	19999	19283	20068
55°	17443	16248	16888
60°	15415	13497	13310
65°	13698	10650	9132
70°	12085	7517	5498
75°	10294	4257	2669
80°	7671	1326	789
85°	4214	503	503



TEST NUMBER: P581774  
 CATALOG NUMBER: HCC6W15D010MB-HM60525927-61RWWC

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	59.3	4.8
10°-20°	173.4	13.9
20°-30°	253.3	20.3
30°-40°	265.7	21.3
40°-50°	223.8	17.9
50°-60°	156.8	12.6
60°-70°	84.1	6.7
70°-80°	28.2	2.3
80°-90°	3.1	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	486.0	39.0
0°-40°	751.7	60.2
0°-60°	1132.3	90.8
0°-90°	1247.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1247.6	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	618	618	618	618	618	
5°	619	621	622	622	622	59
15°	636	628	610	606	610	180
25°	592	567	531	540	556	271
35°	458	435	408	420	428	284
45°	294	289	284	291	294	229
55°	182	177	170	173	177	164
65°	106	96	82	68	70	105
75°	49	38	20	13	13	52
85°	7	3	1	1	1	9
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P581774

CATALOG NUMBER: HCC6W15D010MB-HM60525927-61RWWC

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	618.0	618.0	618.0	618.0	618.0	618.0	618.0	618.0	618.0
2.5°	613.8	613.8	615.5	617.1	618.8	618.8	619.6	620.5	619.6
5°	618.8	618.8	621.3	622.2	622.2	621.3	622.2	622.2	622.2
7.5°	626.3	624.7	625.5	623.8	622.2	621.3	620.5	620.5	620.5
10°	628.9	627.2	625.5	622.2	618.0	615.5	614.6	615.5	615.5
12.5°	632.2	630.5	626.3	619.6	614.6	610.4	609.6	611.3	611.3
15°	636.4	634.7	628.0	617.1	609.6	605.4	606.2	607.9	609.6
17.5°	636.4	633.0	622.2	607.9	598.7	594.5	597.9	602.1	604.6
20°	626.3	623.0	607.9	590.3	579.4	576.9	582.8	590.3	592.8
22.5°	612.9	606.2	588.6	567.7	556.0	556.0	564.4	573.6	576.9
25°	592.0	587.0	566.9	542.6	530.8	530.0	540.1	552.6	556.0
27.5°	568.5	561.8	540.1	514.9	502.5	503.3	514.2	526.8	530.0
30°	535.0	526.8	507.5	483.2	471.5	474.8	485.7	494.9	499.1
32.5°	497.4	489.9	472.3	449.7	439.6	443.0	452.2	460.6	463.9
35°	458.1	449.7	434.6	414.5	407.8	411.1	419.5	426.2	427.9
37.5°	413.7	407.8	396.9	381.0	376.0	380.1	386.8	391.0	392.7
40°	372.6	367.6	358.4	346.6	345.0	348.3	355.0	357.5	358.4
42.5°	332.4	328.2	322.3	314.1	314.1	317.3	323.2	325.0	325.7
45°	294.0	291.4	288.9	282.2	283.9	288.1	291.4	294.0	294.0
47.5°	260.4	261.3	257.9	252.9	254.6	258.8	261.3	263.8	263.8
50°	234.5	232.0	228.6	223.6	226.1	229.4	232.8	234.5	235.3
52.5°	204.3	203.5	201.0	195.1	196.8	198.4	201.8	204.3	205.2
55°	182.5	180.0	176.7	170.0	170.0	171.6	173.3	175.0	176.7
57.5°	161.6	159.1	154.0	146.5	145.7	145.7	144.8	146.5	149.0
60°	140.6	139.8	132.3	125.6	123.1	120.5	117.2	118.0	121.4
62.5°	122.2	120.5	113.8	105.6	100.4	96.2	92.2	91.3	94.7
65°	105.6	103.9	96.2	88.0	82.1	74.6	67.9	67.9	70.4
67.5°	90.5	87.1	80.4	71.2	63.7	54.5	47.8	49.4	50.3
70°	75.4	72.9	65.3	56.1	46.9	37.7	33.5	34.3	34.3
72.5°	62.0	58.6	51.1	41.9	32.7	24.3	22.6	21.8	21.8
75°	48.6	45.2	37.7	28.5	20.1	14.2	12.6	12.6	12.6
77.5°	35.2	32.7	26.0	17.6	10.9	6.7	5.9	5.0	5.0
80°	24.3	21.8	15.9	9.2	4.2	2.5	2.5	2.5	2.5
82.5°	14.2	11.7	7.5	4.2	1.7	0.8	0.8	0.8	0.8
85°	6.7	5.0	3.4	1.7	0.8	0.8	0.8	0.8	0.8
87.5°	0.8	0.8	0.8	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°    - - 45°-225°    - - - - 90°-270°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)