

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581810

Luminaire Tested: **HCC6S15D010SL-HM60525935-61RWWC**

Issue Date: 9/16/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P581810  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-14)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/16/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC6S15D010SL-HM60525935-61RWWC  
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, SPECULAR TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1433.8 lumens  
Efficiency: N/A  
Efficacy: 102.4 lumens/watt  
Spacing Criteria (0/90/45): 1.22 / 1.15 / 1.2  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 14  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P581810  
CATALOG NUMBER: HCC6S15D010SL-HM60525935-61RWWC

### Luminous Intensity Polar Plot





TEST NUMBER: P581810

CATALOG NUMBER: HCC6S15D010SL-HM60525935-61RWWC

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	88								
2	103	96	90	86	100	94	89	85	91	86	83	88	84	81	85	82	79	77								
3	95	86	79	74	93	85	78	73	82	76	72	79	75	71	77	73	69	68								
4	88	78	70	64	86	76	69	64	74	68	63	72	67	62	70	65	61	60								
5	82	70	62	57	80	69	62	56	67	61	56	65	60	55	64	59	55	53								
6	76	64	56	50	74	63	56	50	62	55	50	60	54	49	58	53	49	47								
7	71	59	51	45	69	58	50	45	56	50	45	55	49	45	54	48	44	42								
8	66	54	46	41	65	53	46	41	52	45	41	51	45	40	50	44	40	38								
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35								
10	59	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32								

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	38933	38933	38933
5°	39137	39346	39346
10°	40230	39534	39372
15°	41510	39756	39756
20°	41992	38848	39746
25°	41150	36903	38651
30°	38924	34290	36303
35°	35228	31360	32913
40°	30643	28375	29477
45°	26189	25289	26189
50°	22976	22157	23070
55°	20042	18666	19411
60°	17718	15503	15295
65°	15722	12232	10481
70°	13881	8639	6331
75°	11819	4872	3050
80°	8808	1515	884
85°	4843	566	566



TEST NUMBER: P581810

CATALOG NUMBER: HCC6S15D010SL-HM60525935-61RWWC

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	68.1	4.8
10°-20°	199.3	13.9
20°-30°	291.1	20.3
30°-40°	305.3	21.3
40°-50°	257.2	17.9
50°-60°	180.2	12.6
60°-70°	96.6	6.7
70°-80°	32.4	2.3
80°-90°	3.5	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	558.6	39.0
0°-40°	863.9	60.3
0°-60°	1301.3	90.8
0°-90°	1433.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1433.8	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	710	710	710	710	710	
5°	711	714	715	715	715	68
15°	731	722	700	697	700	206
25°	680	652	610	621	639	312
35°	526	499	469	482	492	327
45°	338	332	326	335	338	263
55°	210	203	195	199	203	189
65°	121	111	94	78	81	121
75°	56	43	23	14	14	59
85°	8	4	1	1	1	11
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P581810

CATALOG NUMBER: HCC6S15D010SL-HM60525935-61RWWC

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	710.2	710.2	710.2	710.2	710.2	710.2	710.2	710.2	710.2
2.5°	705.4	705.4	707.3	709.3	711.2	711.2	712.1	713.1	712.1
5°	711.2	711.2	714.0	715.0	715.0	714.0	715.0	715.0	715.0
7.5°	719.8	717.9	718.9	717.0	715.0	714.0	713.1	713.1	713.1
10°	722.7	720.8	718.9	715.0	710.2	707.3	706.3	707.3	707.3
12.5°	726.5	724.6	719.8	712.1	706.3	701.5	700.5	702.5	702.5
15°	731.4	729.5	721.7	709.3	700.5	695.8	696.8	698.7	700.5
17.5°	731.4	727.5	715.0	698.7	688.0	683.3	687.1	691.9	694.8
20°	719.8	716.0	698.7	678.4	665.9	663.1	669.8	678.4	681.3
22.5°	704.4	696.8	676.6	652.5	639.0	639.0	648.7	659.2	663.1
25°	680.3	674.6	651.5	623.6	610.1	609.2	620.7	635.1	639.0
27.5°	653.4	645.7	620.7	591.8	577.4	578.4	590.9	605.3	609.2
30°	614.9	605.3	583.2	555.2	541.7	545.6	558.2	568.7	573.5
32.5°	571.6	563.0	542.8	516.8	505.2	509.0	519.6	529.3	533.1
35°	526.4	516.8	499.4	476.4	468.6	472.5	482.1	489.9	491.8
37.5°	475.3	468.6	456.2	437.9	432.1	436.9	444.6	449.5	451.4
40°	428.2	422.4	411.9	398.4	396.5	400.3	408.0	410.9	411.9
42.5°	382.0	377.3	370.5	360.9	360.9	364.7	371.5	373.4	374.3
45°	337.8	334.9	332.0	324.3	326.2	331.1	334.9	337.8	337.8
47.5°	299.3	300.2	296.3	290.7	292.6	297.4	300.2	303.2	303.2
50°	269.4	266.6	262.8	257.0	259.8	263.7	267.5	269.4	270.5
52.5°	234.8	233.8	231.0	224.3	226.1	228.0	231.9	234.8	235.7
55°	209.7	206.9	203.1	195.3	195.3	197.3	199.2	201.1	203.1
57.5°	185.7	182.8	177.1	168.4	167.4	167.4	166.5	168.4	171.3
60°	161.6	160.7	152.1	144.4	141.4	138.6	134.7	135.6	139.5
62.5°	140.5	138.6	130.9	121.2	115.4	110.7	105.9	104.9	108.7
65°	121.2	119.3	110.7	101.0	94.3	85.7	78.0	78.0	80.8
67.5°	104.0	100.1	92.4	81.8	73.1	62.5	54.8	56.8	57.8
70°	86.6	83.8	75.0	64.5	53.9	43.4	38.5	39.5	39.5
72.5°	71.2	67.4	58.7	48.1	37.6	27.9	26.0	25.0	25.0
75°	55.8	52.0	43.4	32.7	23.0	16.3	14.4	14.4	14.4
77.5°	40.4	37.6	29.9	20.2	12.5	7.7	6.7	5.8	5.8
80°	27.9	25.0	18.3	10.6	4.8	2.8	2.8	2.8	2.8
82.5°	16.3	13.5	8.6	4.8	1.9	0.9	0.9	0.9	0.9
85°	7.7	5.8	3.9	1.9	0.9	0.9	0.9	0.9	0.9
87.5°	0.9	0.9	0.9	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°    - - 45°-225°    - - - - 90°-270°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)