

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581817

Luminaire Tested: **HCC6W15D010BZ-HM60525935-61WWBB**

Issue Date: 9/16/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P581817  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-17)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/16/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC6W15D010BZ-HM60525935-61WWBB  
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, WHITE BAFFLE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1219.2 lumens  
Efficiency: N/A  
Efficacy: 87.1 lumens/watt  
Spacing Criteria (0/90/45): 1.15 / 1.06 / 1.14  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 14  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P581817  
CATALOG NUMBER: HCC6W15D010BZ-HM60525935-61WWBB

### Luminous Intensity Polar Plot





TEST NUMBER: P581817

CATALOG NUMBER: HCC6W15D010BZ-HM60525935-61WWBB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20										
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	108	104	101	109	105	102	100	101	99	97	97	95	94	94	92	91	89								
2	103	97	91	87	101	95	90	86	91	87	84	88	85	82	85	83	80	78								
3	96	87	80	75	93	86	79	74	83	77	73	80	76	72	78	74	71	69								
4	89	79	71	66	87	78	71	65	75	69	64	73	68	64	71	67	63	61								
5	83	72	64	58	81	71	63	58	69	62	57	67	61	57	65	60	56	54								
6	77	65	58	52	75	65	57	52	63	56	51	61	55	51	60	55	51	49								
7	72	60	52	47	70	59	52	47	58	51	46	56	51	46	55	50	46	44								
8	67	55	48	43	66	55	47	42	53	47	42	52	46	42	51	46	42	40								
9	63	51	44	39	62	51	44	39	50	43	39	49	43	38	48	42	38	37								
10	60	48	40	36	58	47	40	36	46	40	36	45	40	35	45	39	35	34								

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	37508	37508	37508
5°	38229	37437	36589
10°	39534	36962	35409
15°	40744	36317	34296
20°	41368	34805	32506
25°	40629	32415	30268
30°	38620	29543	27776
35°	34713	26401	25049
40°	29956	23143	22378
45°	25367	19925	19397
50°	21748	16827	16656
55°	18857	14164	13610
60°	16468	11501	9703
65°	14476	8860	5370
70°	12502	5850	2613
75°	10612	2859	1017
80°	8208	1231	600
85°	4843	566	566



TEST NUMBER: P581817  
 CATALOG NUMBER: HCC6W15D010BZ-HM60525935-61WWBB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	64.6	5.3
10°-20°	182.6	15.0
20°-30°	257.1	21.1
30°-40°	262.7	21.5
40°-50°	211.8	17.4
50°-60°	142.1	11.7
60°-70°	71.9	5.9
70°-80°	23.0	1.9
80°-90°	3.5	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	504.3	41.4
0°-40°	766.9	62.9
0°-60°	1120.8	91.9
0°-90°	1219.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1219.2	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	684	684	684	684	684	
5°	695	690	680	670	665	67
15°	718	689	640	611	604	203
25°	672	619	536	503	500	307
35°	519	472	394	372	374	323
45°	327	301	257	248	250	254
55°	197	175	148	141	142	178
65°	112	92	68	45	41	111
75°	50	36	14	5	5	54
85°	8	4	1	1	1	10
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P581817

CATALOG NUMBER: HCC6W15D010BZ-HM60525935-61WWBB

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	684.2	684.2	684.2	684.2	684.2	684.2	684.2	684.2	684.2
2.5°	687.0	686.1	685.1	683.2	680.3	677.5	675.6	673.6	672.6
5°	694.7	692.8	690.0	686.1	680.3	673.6	669.8	665.9	664.9
7.5°	705.3	701.5	693.8	685.1	675.6	665.9	659.2	655.3	652.4
10°	710.2	703.5	692.8	678.4	664.0	652.4	643.8	638.0	636.1
12.5°	714.0	706.3	690.9	671.7	652.4	637.1	627.4	622.5	620.6
15°	717.9	710.2	688.9	664.0	639.9	621.6	611.1	606.2	604.3
17.5°	717.9	707.2	682.2	650.5	621.6	599.5	589.0	584.1	583.2
20°	709.1	697.7	666.8	629.4	596.6	571.6	561.9	559.1	557.2
22.5°	692.8	679.4	644.7	602.3	566.8	542.8	532.1	530.2	528.2
25°	671.7	658.2	618.7	573.5	535.9	511.9	503.3	501.3	500.4
27.5°	644.7	630.3	589.0	542.8	502.4	479.2	471.5	471.5	470.6
30°	610.1	593.7	553.3	507.1	466.7	445.5	439.8	439.8	438.8
32.5°	567.7	551.4	514.8	470.6	432.1	410.0	405.1	407.0	406.1
35°	518.7	505.2	471.5	428.2	394.5	374.3	372.4	374.3	374.3
37.5°	469.5	457.1	428.2	390.7	358.9	340.6	340.6	343.6	342.5
40°	418.6	408.9	382.0	349.4	323.4	310.8	308.8	311.8	312.7
42.5°	370.5	362.7	339.7	312.7	289.7	277.2	280.0	281.9	283.0
45°	327.2	319.5	301.2	273.3	257.0	248.2	248.2	251.2	250.2
47.5°	288.6	283.0	264.6	237.7	223.3	219.4	221.3	223.3	223.3
50°	255.0	246.3	229.0	207.8	197.3	192.5	194.4	195.3	195.3
52.5°	223.3	217.5	200.1	180.9	171.3	168.4	168.4	169.3	169.3
55°	197.3	190.6	175.1	155.8	148.2	144.4	141.4	140.5	142.4
57.5°	172.3	166.5	152.1	133.7	125.1	121.2	115.4	113.5	115.4
60°	150.2	145.3	130.9	113.5	104.9	97.2	90.5	86.6	88.5
62.5°	130.9	125.1	110.7	96.2	86.6	78.0	67.3	61.6	64.5
65°	111.6	106.8	92.4	78.0	68.3	57.8	45.2	41.4	41.4
67.5°	94.3	89.4	76.0	63.6	52.0	39.5	27.9	26.9	27.9
70°	78.0	73.1	61.6	49.0	36.5	24.1	16.3	16.3	16.3
72.5°	64.5	58.7	48.1	35.6	23.0	12.5	8.6	9.6	9.6
75°	50.1	45.2	35.6	24.1	13.5	5.8	4.8	4.8	4.8
77.5°	37.6	33.7	25.0	15.4	6.7	1.9	1.9	1.9	1.9
80°	26.0	22.1	16.3	9.6	3.9	1.9	1.9	1.9	1.9
82.5°	15.4	13.5	9.6	4.8	1.9	0.9	0.9	0.9	0.9
85°	7.7	6.7	3.9	1.9	0.9	0.9	0.9	0.9	0.9
87.5°	1.9	1.9	0.9	0.9	0.0	0.9	0.9	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°    - - 45°-225°    - - - - 90°-270°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)