

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581835

Luminaire Tested: **HCC6S15D010SL-HM60525940-61WWBB**

Issue Date: 9/16/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P581835  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-17)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/16/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC6S15D010SL-HM60525940-61WWBB  
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, WHITE BAFFLE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1234.5 lumens  
Efficiency: N/A  
Efficacy: 88.2 lumens/watt  
Spacing Criteria (0/90/45): 1.15 / 1.06 / 1.14  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 14  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P581835  
CATALOG NUMBER: HCC6S15D010SL-HM60525940-61WWBB

### Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P581835

CATALOG NUMBER: HCC6S15D010SL-HM60525940-61WWBB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	111	108	104	101	109	105	102	100	101	99	97	97	95	94	94	92	91	89					89			
2	103	97	91	87	101	95	90	86	91	87	84	88	85	82	85	83	80	78					78			
3	96	87	80	75	93	86	79	74	83	77	73	80	76	72	78	74	71	69					69			
4	89	79	71	66	87	78	71	65	75	69	64	73	68	64	71	66	63	61					61			
5	83	72	64	58	81	71	63	58	69	62	57	67	61	57	65	60	56	54					54			
6	77	65	58	52	75	65	57	52	63	56	51	61	55	51	60	55	51	49					49			
7	72	60	52	47	70	59	52	47	58	51	46	56	51	46	55	50	46	44					44			
8	67	55	48	43	66	55	47	42	53	47	42	52	46	42	51	46	42	40					40			
9	63	51	44	39	62	51	44	39	50	43	39	49	43	38	48	42	38	37					37			
10	60	48	40	36	58	47	40	36	46	40	36	45	40	35	45	39	35	34					34			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	37974	37974	37974
5°	38713	37904	37051
10°	40024	37424	35849
15°	41254	36777	34728
20°	41893	35236	32909
25°	41137	32820	30649
30°	39101	29910	28118
35°	35148	26736	25364
40°	30328	23422	22664
45°	25685	20165	19638
50°	22021	17040	16869
55°	19096	14336	13773
60°	16665	11644	9835
65°	14658	8963	5435
70°	12646	5930	2661
75°	10718	2881	1038
80°	8303	1231	600
85°	4906	629	629



TEST NUMBER: P581835  
 CATALOG NUMBER: HCC6S15D010SL-HM60525940-61WWBB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	65.4	5.3
10°-20°	184.9	15.0
20°-30°	260.3	21.1
30°-40°	266.0	21.5
40°-50°	214.5	17.4
50°-60°	143.8	11.7
60°-70°	72.8	5.9
70°-80°	23.3	1.9
80°-90°	3.6	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	510.6	41.4
0°-40°	776.6	62.9
0°-60°	1134.9	91.9
0°-90°	1234.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1234.5	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	693	693	693	693	693	
5°	704	699	689	678	673	68
15°	727	698	648	619	612	205
25°	680	626	543	510	507	311
35°	525	477	400	377	379	327
45°	331	305	260	251	253	258
55°	200	177	150	143	144	180
65°	113	94	69	46	42	113
75°	51	36	14	5	5	54
85°	8	4	1	1	1	10
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P581835

CATALOG NUMBER: HCC6S15D010SL-HM60525940-61WWBB

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	692.7	692.7	692.7	692.7	692.7	692.7	692.7	692.7	692.7
2.5°	695.6	694.7	693.7	691.8	688.8	685.9	684.0	682.0	681.0
5°	703.5	701.5	698.6	694.7	688.8	682.0	678.2	674.2	673.3
7.5°	714.1	710.3	702.5	693.7	684.0	674.2	667.4	663.5	660.6
10°	719.0	712.2	701.5	686.9	672.3	660.6	651.8	645.9	644.0
12.5°	723.0	715.2	699.6	680.1	660.6	645.0	635.3	630.4	628.4
15°	726.9	719.0	697.6	672.3	648.0	629.4	618.7	613.8	611.9
17.5°	726.9	716.1	690.8	658.6	629.4	607.0	596.3	591.4	590.4
20°	718.1	706.4	675.2	637.2	604.0	578.7	569.0	566.0	564.1
22.5°	701.5	687.9	652.7	609.9	573.9	549.6	538.8	536.9	534.9
25°	680.1	666.5	626.5	580.7	542.6	518.4	509.6	507.6	506.7
27.5°	652.7	638.2	596.3	549.6	508.6	485.2	477.4	477.4	476.5
30°	617.7	601.2	560.2	513.5	472.5	451.2	445.3	445.3	444.2
32.5°	574.9	558.3	521.3	476.5	437.4	415.1	410.2	412.1	411.2
35°	525.2	511.5	477.4	433.6	399.5	379.0	377.0	379.0	379.0
37.5°	475.5	462.9	433.6	395.5	363.4	344.9	344.9	347.9	346.9
40°	423.8	414.0	386.8	353.7	327.3	314.7	312.8	315.6	316.7
42.5°	375.1	367.3	343.9	316.7	293.3	280.6	283.5	285.5	286.5
45°	331.3	323.5	305.0	276.7	260.1	251.4	251.4	254.4	253.3
47.5°	292.3	286.5	268.0	240.6	226.1	222.1	224.0	226.1	226.1
50°	258.2	249.5	231.9	210.4	199.8	194.9	196.8	197.8	197.8
52.5°	226.1	220.2	202.7	183.2	173.4	170.5	170.5	171.5	171.5
55°	199.8	193.0	177.3	157.9	150.0	146.2	143.2	142.2	144.1
57.5°	174.4	168.5	153.9	135.4	126.7	122.8	116.9	115.0	116.9
60°	152.0	147.1	132.5	115.0	106.2	98.4	91.6	87.7	89.7
62.5°	132.5	126.7	112.0	97.4	87.7	78.9	68.2	62.3	65.3
65°	113.0	108.2	93.5	78.9	69.1	58.5	45.7	41.9	41.9
67.5°	95.5	90.6	77.0	64.4	52.7	40.0	28.3	27.2	28.3
70°	78.9	74.0	62.3	49.7	37.0	24.4	16.6	16.6	16.6
72.5°	65.3	59.5	48.7	36.1	23.4	12.7	8.7	9.8	9.8
75°	50.6	45.7	36.1	24.4	13.6	5.9	4.9	4.9	4.9
77.5°	38.0	34.0	25.3	15.5	6.8	1.9	1.9	1.9	1.9
80°	26.3	22.4	16.6	9.8	3.9	1.9	1.9	1.9	1.9
82.5°	15.5	13.6	9.8	4.9	1.9	1.0	1.0	1.0	1.0
85°	7.8	6.8	3.9	1.9	1.0	1.0	1.0	1.0	1.0
87.5°	1.9	1.9	1.0	1.0	0.0	1.0	1.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°    - - 45°-225°    - - - - 90°-270°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)