

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581846

Luminaire Tested: **HCC6S20D010BZ-HM60525827-61RWWC**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P581846
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-14)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6S20D010BZ-HM60525827-61RWWC
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1994.4 lumens
Efficiency: N/A
Efficacy: 99.7 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.15 / 1.2
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 20
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P581846
CATALOG NUMBER: HCC6S20D010BZ-HM60525827-61RWWC

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P581846

CATALOG NUMBER: HCC6S20D010BZ-HM60525827-61RWWC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	88								
2	103	96	90	86	100	94	89	85	91	86	83	88	84	81	85	82	79	77								
3	95	86	79	74	93	85	78	73	82	76	72	79	75	71	77	73	69	68								
4	88	78	70	64	86	76	69	64	74	68	63	72	67	62	70	65	61	59								
5	82	70	62	57	80	69	62	56	67	61	56	65	60	55	64	59	55	53								
6	76	64	56	50	74	63	56	50	62	55	50	60	54	49	58	53	49	47								
7	71	59	51	45	69	58	50	45	56	50	45	55	49	45	54	48	44	42								
8	66	54	46	41	65	53	46	41	52	45	41	51	45	40	50	44	40	38								
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35								
10	59	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	54157	54157	54157
5°	54435	54727	54727
10°	55961	54992	54770
15°	57736	55307	55307
20°	58408	54039	55293
25°	57245	51330	53761
30°	54148	47710	50495
35°	49008	43627	45775
40°	42623	39467	41005
45°	36430	35182	36430
50°	31965	30822	32084
55°	27899	25968	27000
60°	24658	21577	21281
65°	21883	17019	14580
70°	19298	12021	8784
75°	16436	6820	4257
80°	12281	2115	1263
85°	6793	881	881



TEST NUMBER: P581846
 CATALOG NUMBER: HCC6S20D010BZ-HM60525827-61RWWC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	94.8	4.8
10°-20°	277.2	13.9
20°-30°	404.9	20.3
30°-40°	424.7	21.3
40°-50°	357.8	17.9
50°-60°	250.7	12.6
60°-70°	134.4	6.7
70°-80°	45.1	2.3
80°-90°	4.9	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	776.9	39.0
0°-40°	1201.6	60.2
0°-60°	1810.0	90.8
0°-90°	1994.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1994.4	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	988	988	988	988	988	
5°	989	993	994	994	994	95
15°	1017	1004	974	969	974	287
25°	946	906	849	863	889	434
35°	732	695	652	671	684	454
45°	470	462	454	466	470	366
55°	292	282	272	277	282	263
65°	169	154	131	108	112	168
75°	78	60	32	20	20	82
85°	11	5	1	1	1	15
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P581846

CATALOG NUMBER: HCC6S20D010BZ-HM60525827-61RWWC

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	987.9	987.9	987.9	987.9	987.9	987.9	987.9	987.9	987.9
2.5°	981.2	981.2	983.9	986.5	989.2	989.2	990.6	991.9	990.6
5°	989.2	989.2	993.2	994.5	994.5	993.2	994.5	994.5	994.5
7.5°	1001.2	998.6	999.9	997.3	994.5	993.2	991.9	991.9	991.9
10°	1005.3	1002.6	999.9	994.5	987.9	983.9	982.5	983.9	983.9
12.5°	1010.6	1007.9	1001.2	990.6	982.5	975.9	974.5	977.2	977.2
15°	1017.3	1014.6	1004.0	986.5	974.5	967.8	969.2	971.8	974.5
17.5°	1017.3	1012.0	994.5	971.8	957.0	950.4	955.8	962.5	966.4
20°	1001.2	995.9	971.8	943.7	926.3	922.3	931.7	943.7	947.8
22.5°	979.8	969.2	941.1	907.5	888.8	888.8	902.2	916.9	922.3
25°	946.4	938.4	906.2	867.4	848.6	847.4	863.3	883.5	888.8
27.5°	908.9	898.2	863.3	823.2	803.2	804.5	821.9	841.9	847.4
30°	855.4	841.9	811.2	772.4	753.7	759.0	776.3	791.1	797.7
32.5°	795.1	783.1	754.9	718.8	702.8	708.1	722.9	736.2	741.5
35°	732.3	718.8	694.8	662.6	651.9	657.3	670.6	681.4	684.0
37.5°	661.2	651.9	634.5	609.1	601.1	607.7	618.4	625.1	627.8
40°	595.6	587.7	573.0	554.2	551.5	556.9	567.5	571.6	573.0
42.5°	531.4	524.7	515.4	501.9	501.9	507.4	516.6	519.4	520.7
45°	469.9	465.8	461.8	451.2	453.8	460.5	465.8	469.9	469.9
47.5°	416.3	417.6	412.3	404.3	407.0	413.7	417.6	421.7	421.7
50°	374.8	370.8	365.4	357.3	361.4	366.8	372.1	374.8	376.2
52.5°	326.6	325.3	321.2	311.9	314.5	317.2	322.6	326.6	328.0
55°	291.9	287.8	282.5	271.7	271.7	274.4	277.1	279.7	282.5
57.5°	258.3	254.4	246.3	234.3	232.9	232.9	231.6	234.3	238.3
60°	224.9	223.5	211.5	200.8	196.8	192.7	187.4	188.8	194.1
62.5°	195.4	192.7	182.1	168.7	160.7	154.0	147.3	145.9	151.3
65°	168.7	166.0	154.0	140.6	131.2	119.1	108.4	108.4	112.4
67.5°	144.6	139.2	128.5	113.8	101.7	87.0	76.3	79.0	80.3
70°	120.4	116.5	104.5	89.7	75.0	60.3	53.6	54.8	54.8
72.5°	99.0	93.7	81.7	67.0	52.2	38.9	36.1	34.8	34.8
75°	77.6	72.3	60.3	45.5	32.2	22.8	20.1	20.1	20.1
77.5°	56.2	52.2	41.5	28.1	17.4	10.8	9.4	8.0	8.0
80°	38.9	34.8	25.4	14.7	6.7	4.0	4.0	4.0	4.0
82.5°	22.8	18.7	12.0	6.7	2.7	1.4	1.4	1.4	1.4
85°	10.8	8.0	5.3	2.7	1.4	1.4	1.4	1.4	1.4
87.5°	1.4	1.4	1.4	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)