

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581844

Luminaire Tested: **HCC6S20D010MB-HM60525827-61NDW**

Issue Date: 9/16/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P581844  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-3)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/16/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC6S20D010MB-HM60525827-61NDW  
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" NARROW DISTRIBUTION, WHITE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1821.8 lumens  
Efficiency: N/A  
Efficacy: 91.1 lumens/watt  
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.03  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 20  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P581844  
CATALOG NUMBER: HCC6S20D010MB-HM60525827-61NDW

### Luminous Intensity Polar Plot





TEST NUMBER: P581844  
 CATALOG NUMBER: HCC6S20D010MB-HM60525827-61NDW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	108	104	101	109	105	102	100	101	99	96	97	95	94	94	92	91	89			
2	104	97	92	87	101	95	90	86	92	88	84	89	85	83	86	83	81	79			
3	97	88	82	77	94	87	81	76	84	79	75	81	77	73	79	75	72	70			
4	90	81	73	68	88	79	73	68	77	71	67	75	70	66	73	69	65	63			
5	84	74	67	61	83	73	66	61	71	65	60	69	64	60	67	63	59	57			
6	79	68	61	55	77	67	60	55	66	59	55	64	59	54	63	58	54	52			
7	74	63	56	50	73	62	55	50	61	55	50	60	54	50	58	53	49	48			
8	70	59	51	46	69	58	51	46	57	50	46	56	50	46	54	49	46	44			
9	66	55	48	43	65	54	47	43	53	47	42	52	46	42	51	46	42	41			
10	62	51	44	40	61	51	44	40	50	44	39	49	43	39	48	43	39	38			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	68997
5°	68677
10°	67155
15°	65579
20°	63116
25°	59689
30°	54249
35°	43908
40°	29613
45°	20343
50°	16665
55°	14585
60°	13804
65°	13023
70°	12246
75°	11649
80°	10544
85°	9246



TEST NUMBER: P581844  
 CATALOG NUMBER: HCC6S20D010MB-HM60525827-61NDW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	117.8	6.5
10°-20°	324.5	17.8
20°-30°	450.8	24.7
30°-40°	401.4	22.0
40°-50°	213.1	11.7
50°-60°	139.3	7.6
60°-70°	99.9	5.5
70°-80°	57.9	3.2
80°-90°	16.9	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	893.2	49.0
0°-40°	1294.6	71.1
0°-60°	1647.0	90.4
0°-90°	1821.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1821.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1259	
5°	1248	118
15°	1156	325
25°	987	451
35°	656	401
45°	262	213
55°	153	139
65°	100	100
75°	55	58
85°	15	17
90°	0	



TEST NUMBER: P581844  
CATALOG NUMBER: HCC6S20D010MB-HM60525827-61NDW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1258.6
2.5°	1252.0
5°	1248.0
7.5°	1233.3
10°	1206.4
12.5°	1182.3
15°	1155.5
17.5°	1122.1
20°	1081.9
22.5°	1036.4
25°	986.8
27.5°	929.3
30°	857.0
32.5°	769.9
35°	656.1
37.5°	530.2
40°	413.8
42.5°	321.3
45°	262.4
47.5°	223.7
50°	195.4
52.5°	172.8
55°	152.6
57.5°	137.9
60°	125.9
62.5°	113.9
65°	100.4
67.5°	88.4
70°	76.4
72.5°	65.6
75°	55.0
77.5°	44.2
80°	33.4
82.5°	24.1
85°	14.7
87.5°	6.7
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)