

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581871

Luminaire Tested: **HCC6S20D010BZ-HM60525830-61WWBB**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P581871
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-17)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6S20D010BZ-HM60525830-61WWBB
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, WHITE BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1824.0 lumens
Efficiency: N/A
Efficacy: 91.2 lumens/watt
Spacing Criteria (0/90/45): 1.15 / 1.06 / 1.14
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 20
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P581871
CATALOG NUMBER: HCC6S20D010BZ-HM60525830-61WWBB

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P581871

CATALOG NUMBER: HCC6S20D010BZ-HM60525830-61WWBB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20										
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	108	104	101	109	105	102	100	101	99	97	97	95	94	94	92	91	89								
2	103	97	91	87	101	95	90	86	91	87	84	88	85	82	85	83	80	78								
3	96	87	80	75	93	86	79	74	83	77	73	80	76	72	78	74	71	69								
4	89	79	71	66	87	78	71	65	75	69	64	73	68	64	71	66	63	61								
5	83	72	64	58	81	71	63	58	69	62	57	67	61	57	65	60	56	54								
6	77	65	58	52	75	65	57	52	63	56	51	61	55	51	60	55	51	49								
7	72	60	52	47	70	59	52	47	58	51	46	56	51	46	55	50	46	44								
8	67	55	48	43	66	55	47	42	53	47	42	52	46	42	51	46	42	40								
9	63	51	44	39	62	51	44	39	50	43	39	49	43	38	48	42	38	37								
10	60	48	40	36	58	47	40	36	46	40	36	45	40	35	45	39	35	34								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	56114	56114	56114
5°	57192	56009	54743
10°	59139	55293	52966
15°	60948	54331	51306
20°	61891	52073	48625
25°	60784	48499	45281
30°	57768	44197	41557
35°	51926	39498	37477
40°	44813	34615	33477
45°	37950	29794	29011
50°	32536	25168	24920
55°	28204	21189	20358
60°	24625	17203	14516
65°	21663	13257	8029
70°	18689	8768	3927
75°	15864	4279	1546
80°	12281	1831	884
85°	7296	943	943



TEST NUMBER: P581871

CATALOG NUMBER: HCC6S20D010BZ-HM60525830-61WWBB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	96.6	5.3
10°-20°	273.1	15.0
20°-30°	384.6	21.1
30°-40°	393.0	21.5
40°-50°	316.9	17.4
50°-60°	212.5	11.7
60°-70°	107.5	5.9
70°-80°	34.4	1.9
80°-90°	5.3	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	754.4	41.4
0°-40°	1147.3	62.9
0°-60°	1676.7	91.9
0°-90°	1824.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1824.0	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1024	1024	1024	1024	1024	
5°	1039	1032	1018	1002	995	100
15°	1074	1031	957	914	904	303
25°	1005	926	802	753	749	460
35°	776	705	590	557	560	483
45°	490	451	384	371	374	381
55°	295	262	222	212	213	266
65°	167	138	102	68	62	167
75°	75	53	20	7	7	80
85°	12	6	2	2	2	15
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P581871

CATALOG NUMBER: HCC6S20D010BZ-HM60525830-61WWBB

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	1023.6	1023.6	1023.6	1023.6	1023.6	1023.6	1023.6	1023.6	1023.6
2.5°	1027.9	1026.4	1024.9	1022.1	1017.8	1013.5	1010.5	1007.7	1006.2
5°	1039.3	1036.5	1032.2	1026.4	1017.8	1007.7	1001.9	996.1	994.8
7.5°	1055.2	1049.4	1037.9	1024.9	1010.5	996.1	986.0	980.4	976.0
10°	1062.4	1052.3	1036.5	1014.9	993.3	976.0	963.0	954.4	951.5
12.5°	1068.2	1056.6	1033.6	1004.9	976.0	953.0	938.6	931.4	928.5
15°	1073.9	1062.4	1030.7	993.3	957.3	930.0	914.1	907.0	904.0
17.5°	1073.9	1058.1	1020.6	973.1	930.0	896.9	881.0	873.8	872.4
20°	1060.9	1043.7	997.6	941.5	892.6	855.1	840.7	836.4	833.5
22.5°	1036.5	1016.3	964.5	901.2	847.9	811.9	796.0	793.2	790.3
25°	1004.9	984.7	925.7	858.0	801.8	765.8	752.9	750.0	748.6
27.5°	964.5	942.9	881.0	811.9	751.4	716.8	705.4	705.4	703.9
30°	912.6	888.2	827.8	758.7	698.2	666.5	657.8	657.8	656.5
32.5°	849.3	824.8	770.2	703.9	646.4	613.3	606.0	609.0	607.5
35°	775.9	755.7	705.4	640.6	590.2	560.0	557.1	560.0	560.0
37.5°	702.5	683.8	640.6	584.5	536.9	509.6	509.6	513.9	512.5
40°	626.2	611.8	571.5	522.5	483.7	465.0	462.2	466.5	467.8
42.5°	554.3	542.7	508.2	467.8	433.3	414.6	418.9	421.8	423.2
45°	489.5	477.9	450.6	408.8	384.3	371.4	371.4	375.7	374.2
47.5°	431.9	423.2	395.9	355.5	334.0	328.2	331.1	334.0	334.0
50°	381.5	368.6	342.6	310.9	295.1	287.9	290.8	292.2	292.2
52.5°	334.0	325.3	299.5	270.7	256.3	251.9	251.9	253.3	253.3
55°	295.1	285.1	261.9	233.2	221.7	215.9	211.6	210.2	213.0
57.5°	257.6	249.0	227.4	200.1	187.2	181.4	172.8	169.8	172.8
60°	224.6	217.4	195.8	169.8	156.9	145.4	135.3	129.6	132.4
62.5°	195.8	187.2	165.5	144.0	129.6	116.6	100.7	92.1	96.4
65°	167.0	159.8	138.2	116.6	102.2	86.3	67.6	61.9	61.9
67.5°	141.1	133.9	113.8	95.1	77.7	59.0	41.7	40.3	41.7
70°	116.6	109.4	92.1	73.4	54.7	36.0	24.5	24.5	24.5
72.5°	96.4	87.8	71.9	53.3	34.6	18.7	12.9	14.4	14.4
75°	74.9	67.6	53.3	36.0	20.2	8.6	7.3	7.3	7.3
77.5°	56.2	50.4	37.4	23.0	10.1	2.8	2.8	2.8	2.8
80°	38.9	33.1	24.5	14.4	5.8	2.8	2.8	2.8	2.8
82.5°	23.0	20.2	14.4	7.3	2.8	1.5	1.5	1.5	1.5
85°	11.6	10.1	5.8	2.8	1.5	1.5	1.5	1.5	1.5
87.5°	2.8	2.8	1.5	1.5	0.0	1.5	1.5	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)