

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581908

Luminaire Tested: **HCC6W20D010MW-HM60525840-61WWW**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P581908
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6W20D010MW-HM60525840-61WWW
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 4000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2089.6 lumens
Efficiency: N/A
Efficacy: 104.5 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.06 / 1.14
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 20
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P581908
CATALOG NUMBER: HCC6W20D010MW-HM60525840-61WWW

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P581908

CATALOG NUMBER: HCC6W20D010MW-HM60525840-61WWW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	93	91	89	87					87			
2	102	95	89	84	99	93	88	83	90	85	81	86	83	79	83	80	78	76					76			
3	94	85	78	72	92	83	77	71	80	75	70	78	73	69	75	71	68	66					66			
4	87	76	69	63	85	75	68	62	73	67	62	71	65	61	69	64	60	58					58			
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51					51			
6	75	63	55	49	73	62	55	49	61	54	49	59	53	48	57	52	48	46					46			
7	70	58	50	44	69	57	50	44	56	49	44	54	48	44	53	48	43	42					42			
8	66	53	46	40	64	53	45	40	51	45	40	50	44	40	49	44	39	38					38			
9	62	49	42	37	60	49	42	37	48	41	36	47	41	36	46	40	36	34					34			
10	58	46	39	34	57	45	38	34	44	38	33	44	38	33	43	37	33	32					32			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	61497	61497	61497
5°	64220	61314	58491
10°	65970	60258	54964
15°	67605	58950	51499
20°	67906	56279	47301
25°	66482	52697	43382
30°	63079	48457	39753
35°	57286	43547	35670
40°	49915	38787	32089
45°	43191	33942	28204
50°	37722	29227	24716
55°	33327	25681	21218
60°	29965	22509	18376
65°	26838	19587	17823
70°	23946	16686	16686
75°	20778	14064	15674
80°	16669	11902	14301
85°	11385	10504	12328



TEST NUMBER: P581908
 CATALOG NUMBER: HCC6W20D010MW-HM60525840-61WWW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	105.4	5.0
10°-20°	293.1	14.0
20°-30°	408.4	19.5
30°-40°	420.8	20.1
40°-50°	348.8	16.7
50°-60°	250.6	12.0
60°-70°	159.6	7.6
70°-80°	82.0	3.9
80°-90°	20.9	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	806.9	38.6
0°-40°	1227.7	58.8
0°-60°	1827.1	87.4
0°-90°	2089.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2089.6	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1122	1122	1122	1122	1122	
5°	1167	1149	1114	1078	1063	112
15°	1191	1146	1039	944	907	336
25°	1099	1024	871	759	717	504
35°	856	786	651	565	533	532
45°	557	518	438	382	364	431
55°	349	320	269	238	222	314
65°	207	184	151	131	137	207
75°	98	84	66	70	74	105
85°	18	17	17	18	20	23
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P581908

CATALOG NUMBER: HCC6W20D010MW-HM60525840-61WWW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	1121.8	1121.8	1121.8	1121.8	1121.8	1121.8	1121.8	1121.8	1121.8
2.5°	1142.9	1138.3	1132.3	1126.3	1117.3	1106.6	1097.7	1094.6	1090.1
5°	1167.0	1161.0	1149.0	1133.8	1114.2	1094.6	1077.9	1067.4	1062.9
7.5°	1182.2	1174.6	1158.0	1132.3	1103.7	1075.0	1050.7	1035.7	1029.7
10°	1185.1	1177.6	1155.0	1120.2	1082.5	1043.3	1013.0	994.9	987.4
12.5°	1189.6	1179.1	1150.4	1109.7	1061.4	1016.1	978.3	955.7	948.1
15°	1191.2	1179.1	1145.9	1096.1	1038.7	984.4	943.6	916.4	907.4
17.5°	1185.1	1171.5	1132.3	1071.9	1007.0	949.7	901.3	872.6	860.5
20°	1164.0	1149.0	1103.7	1035.7	964.7	904.4	854.5	824.4	810.8
22.5°	1136.9	1117.3	1065.9	993.4	919.4	856.0	806.2	776.0	762.4
25°	1099.1	1081.0	1023.7	946.6	871.2	804.7	759.4	727.7	717.2
27.5°	1055.3	1034.2	975.3	898.4	821.3	754.9	711.1	682.4	668.8
30°	996.5	976.8	918.0	840.9	765.5	703.6	658.3	634.1	628.0
32.5°	927.0	910.4	853.0	780.5	708.1	650.7	613.0	587.3	581.2
35°	856.0	836.4	786.5	718.7	650.7	599.4	564.7	542.0	533.0
37.5°	779.1	760.9	718.7	658.3	597.9	549.5	519.4	499.8	490.7
40°	697.5	683.9	644.7	596.3	542.0	499.8	474.0	457.5	448.4
42.5°	622.0	608.4	581.2	535.9	490.7	453.0	430.3	415.1	407.7
45°	557.1	545.0	517.9	478.6	437.8	406.2	381.9	371.4	363.8
47.5°	492.2	486.2	462.0	425.8	388.1	360.9	344.2	332.2	326.1
50°	442.3	434.8	412.2	374.5	342.7	321.5	306.5	295.9	289.8
52.5°	391.0	383.5	362.3	330.6	305.0	285.3	270.2	261.2	255.2
55°	348.7	342.7	320.1	291.4	268.7	252.1	238.5	228.0	222.0
57.5°	309.5	303.4	282.3	255.2	235.6	220.4	208.4	199.3	191.7
60°	273.3	268.7	247.6	222.0	205.3	190.2	179.7	172.1	167.6
62.5°	241.6	232.5	214.4	191.7	176.6	164.5	154.0	149.4	152.5
65°	206.9	202.4	184.2	164.5	151.0	138.9	131.3	134.4	137.4
67.5°	178.1	172.1	157.0	138.9	126.8	117.7	113.2	119.3	120.8
70°	149.4	143.4	129.8	114.8	104.1	98.1	98.1	102.6	104.1
72.5°	122.3	117.7	105.7	93.6	86.1	81.6	84.5	87.6	89.1
75°	98.1	93.6	84.5	74.0	66.4	66.4	69.5	72.5	74.0
77.5°	75.5	72.5	63.4	55.9	52.8	52.8	55.9	57.3	58.9
80°	52.8	49.9	45.3	40.8	37.7	40.8	43.7	43.7	45.3
82.5°	34.7	33.2	30.3	27.2	27.2	28.7	30.3	31.7	31.7
85°	18.1	18.1	16.7	15.1	16.7	18.1	18.1	19.6	19.6
87.5°	6.0	6.0	6.0	6.0	7.6	7.6	7.6	7.6	7.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)