

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581926

Luminaire Tested: **HCC6S20D010SL-HM60525927-61WWW**

Issue Date: 9/16/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P581926  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-16)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/16/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC6S20D010SL-HM60525927-61WWW  
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, WHITE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1564.5 lumens  
Efficiency: N/A  
Efficacy: 78.2 lumens/watt  
Spacing Criteria (0/90/45): 1.1 / 1.06 / 1.14  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 20  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P581926  
CATALOG NUMBER: HCC6S20D010SL-HM60525927-61WWW

### Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P581926

CATALOG NUMBER: HCC6S20D010SL-HM60525927-61WWW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	93	91	89	87					87			
2	102	95	89	84	99	93	88	83	90	85	81	86	83	79	83	80	78	76					76			
3	94	85	78	72	92	83	77	71	80	75	70	78	73	69	75	71	68	66					66			
4	87	76	69	63	85	75	68	62	73	67	62	71	65	61	69	64	60	58					58			
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51					51			
6	75	63	55	49	73	62	55	49	61	54	49	59	53	48	57	52	48	46					46			
7	70	58	50	44	69	57	50	44	56	49	44	54	48	44	53	48	43	42					42			
8	66	53	46	40	64	53	45	40	51	45	40	50	44	40	49	44	39	38					38			
9	62	49	42	37	60	49	42	37	48	41	36	47	41	36	46	40	36	34					34			
10	58	46	39	34	57	45	38	34	44	38	33	44	38	33	43	37	33	32					32			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	46043	46043	46043
5°	48085	45906	43793
10°	49398	45112	41154
15°	50619	44138	38553
20°	50842	42138	35417
25°	49775	39456	32476
30°	47229	36278	29764
35°	42891	32605	26702
40°	37370	29040	24024
45°	32344	25413	21118
50°	28246	21884	18515
55°	24964	19230	15885
60°	22432	16852	13749
65°	20093	14671	13348
70°	17936	12502	12502
75°	15568	10527	11734
80°	12470	8903	10702
85°	8554	7862	9246



TEST NUMBER: P581926

CATALOG NUMBER: HCC6S20D010SL-HM60525927-61WWW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	78.9	5.0
10°-20°	219.4	14.0
20°-30°	305.8	19.5
30°-40°	315.1	20.1
40°-50°	261.1	16.7
50°-60°	187.7	12.0
60°-70°	119.5	7.6
70°-80°	61.4	3.9
80°-90°	15.6	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	604.1	38.6
0°-40°	919.2	58.8
0°-60°	1368.0	87.4
0°-90°	1564.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1564.5	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	840	840	840	840	840	
5°	874	860	834	807	796	84
15°	892	858	778	706	679	251
25°	823	766	652	568	537	377
35°	641	589	487	423	399	398
45°	417	388	328	286	272	323
55°	261	240	201	179	166	235
65°	155	138	113	98	103	155
75°	74	63	50	52	55	78
85°	14	12	12	14	15	17
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P581926

CATALOG NUMBER: HCC6S20D010SL-HM60525927-61WWW

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	839.9	839.9	839.9	839.9	839.9	839.9	839.9	839.9	839.9
2.5°	855.8	852.4	847.8	843.3	836.5	828.6	821.8	819.5	816.1
5°	873.8	869.2	860.2	849.0	834.2	819.5	807.1	799.2	795.8
7.5°	885.1	879.4	867.0	847.8	826.3	804.9	786.8	775.4	770.9
10°	887.4	881.7	864.7	838.8	810.4	781.1	758.5	744.9	739.3
12.5°	890.8	882.8	861.3	830.8	794.7	760.8	732.5	715.5	709.9
15°	891.9	882.8	858.0	820.6	777.7	737.0	706.5	686.1	679.3
17.5°	887.4	877.2	847.8	802.6	754.0	711.1	674.8	653.4	644.3
20°	871.5	860.2	826.3	775.4	722.3	677.1	639.8	617.1	607.1
22.5°	851.2	836.5	798.1	743.8	688.4	640.9	603.7	581.0	570.8
25°	822.9	809.4	766.4	708.8	652.3	602.5	568.5	544.9	536.9
27.5°	790.2	774.3	730.2	672.5	614.9	565.1	532.4	511.0	500.8
30°	746.1	731.4	687.3	629.6	573.1	526.7	492.9	474.7	470.2
32.5°	694.1	681.6	638.7	584.4	530.1	487.2	459.0	439.7	435.2
35°	640.9	626.2	588.9	538.1	487.2	448.8	422.7	405.8	399.0
37.5°	583.3	569.7	538.1	492.9	447.6	411.5	388.8	374.1	367.4
40°	522.2	512.1	482.7	446.5	405.8	374.1	355.0	342.5	335.7
42.5°	465.8	455.6	435.2	401.3	367.4	339.1	322.1	310.9	305.2
45°	417.2	408.1	387.7	358.4	327.8	304.1	286.0	278.0	272.4
47.5°	368.5	364.0	345.9	318.8	290.5	270.1	257.8	248.7	244.2
50°	331.2	325.5	308.6	280.3	256.6	240.8	229.4	221.5	217.1
52.5°	292.8	287.1	271.2	247.6	228.3	213.7	202.4	195.6	191.0
55°	261.2	256.6	239.6	218.2	201.2	188.8	178.6	170.7	166.2
57.5°	231.7	227.2	211.4	191.0	176.3	165.1	156.0	149.2	143.6
60°	204.6	201.2	185.4	166.2	153.7	142.4	134.5	128.8	125.4
62.5°	180.8	174.0	160.5	143.6	132.2	123.2	115.3	111.9	114.2
65°	154.9	151.5	137.9	123.2	113.1	104.0	98.3	100.6	102.9
67.5°	133.4	128.8	117.6	104.0	94.9	88.1	84.7	89.3	90.4
70°	111.9	107.4	97.2	85.9	78.0	73.5	73.5	76.8	78.0
72.5°	91.5	88.1	79.1	70.1	64.5	61.1	63.3	65.6	66.7
75°	73.5	70.1	63.3	55.4	49.7	49.7	52.0	54.3	55.4
77.5°	56.5	54.3	47.5	41.8	39.5	39.5	41.8	42.9	44.1
80°	39.5	37.3	33.9	30.5	28.2	30.5	32.7	32.7	33.9
82.5°	25.9	24.8	22.7	20.4	20.4	21.5	22.7	23.8	23.8
85°	13.6	13.6	12.5	11.3	12.5	13.6	13.6	14.7	14.7
87.5°	4.5	4.5	4.5	4.5	5.7	5.7	5.7	5.7	5.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°    - - 45°-225°    - - - - 90°-270°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)