

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581943

Luminaire Tested: **HCC6S20D010MW-HM60525930-61WWBB**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P581943
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-17)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6S20D010MW-HM60525930-61WWBB
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, WHITE BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1563.5 lumens
Efficiency: N/A
Efficacy: 78.2 lumens/watt
Spacing Criteria (0/90/45): 1.15 / 1.06 / 1.14
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 20
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P581943
CATALOG NUMBER: HCC6S20D010MW-HM60525930-61WWBB

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P581943

CATALOG NUMBER: HCC6S20D010MW-HM60525930-61WWBB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	108	104	101	109	105	102	100	101	99	97	97	95	94	94	92	91	89								
2	103	97	91	87	101	95	90	86	91	87	84	88	85	82	85	83	80	78								
3	96	87	80	75	93	86	79	74	83	77	73	80	76	72	78	74	71	69								
4	89	79	71	66	87	78	71	65	75	69	64	73	68	64	71	67	63	61								
5	83	72	64	58	81	71	63	58	69	62	57	67	61	57	65	60	56	54								
6	77	65	58	52	75	65	57	52	63	56	51	61	55	51	60	55	51	49								
7	72	60	52	47	70	59	52	47	58	51	46	56	51	46	55	50	46	44								
8	67	55	48	43	66	55	47	42	53	47	42	52	46	42	51	46	42	40								
9	63	51	44	39	62	51	44	39	50	43	39	49	43	38	48	42	38	37								
10	60	48	40	36	58	47	40	36	46	40	36	45	40	35	45	39	35	34								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	48099	48099	48099
5°	49031	48008	46924
10°	50695	47394	45401
15°	52248	46572	43984
20°	53059	44635	41683
25°	52098	41579	38815
30°	49520	37886	35626
35°	44517	33863	32130
40°	38415	29677	28704
45°	32523	25545	24879
50°	27888	21577	21364
55°	24181	18159	17452
60°	21106	14747	12444
65°	18562	11363	6875
70°	16012	7517	3366
75°	13577	3643	1292
80°	10513	1578	789
85°	6227	755	755



TEST NUMBER: P581943
 CATALOG NUMBER: HCC6S20D010MW-HM60525930-61WWBB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	82.8	5.3
10°-20°	234.1	15.0
20°-30°	329.7	21.1
30°-40°	336.9	21.5
40°-50°	271.6	17.4
50°-60°	182.2	11.7
60°-70°	92.2	5.9
70°-80°	29.5	1.9
80°-90°	4.5	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	646.7	41.4
0°-40°	983.5	62.9
0°-60°	1437.3	91.9
0°-90°	1563.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1563.5	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	877	877	877	877	877	
5°	891	885	872	859	853	86
15°	921	884	821	784	775	260
25°	861	793	687	645	642	394
35°	665	605	506	478	480	414
45°	420	386	330	318	321	326
55°	253	225	190	181	183	228
65°	143	118	88	58	53	143
75°	64	46	17	6	6	69
85°	10	5	1	1	1	13
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P581943

CATALOG NUMBER: HCC6S20D010MW-HM60525930-61WWBB

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	877.4	877.4	877.4	877.4	877.4	877.4	877.4	877.4	877.4
2.5°	881.1	879.9	878.6	876.1	872.4	868.8	866.3	863.8	862.6
5°	891.0	888.5	884.8	879.9	872.4	863.8	858.9	853.9	852.7
7.5°	904.6	899.6	889.7	878.6	866.3	853.9	845.3	840.3	836.7
10°	910.7	902.1	888.5	870.0	851.4	836.7	825.6	818.1	815.6
12.5°	915.7	905.7	886.0	861.3	836.7	816.9	804.5	798.4	795.9
15°	920.6	910.7	883.5	851.4	820.6	797.2	783.6	777.5	775.0
17.5°	920.6	907.0	874.9	834.2	797.2	768.9	755.3	749.0	747.8
20°	909.5	894.6	855.2	807.0	765.1	733.1	720.7	717.0	714.5
22.5°	888.5	871.3	826.8	772.5	726.8	696.0	682.4	679.9	677.5
25°	861.3	844.1	793.4	735.4	687.4	656.5	645.4	643.0	641.7
27.5°	826.8	808.3	755.3	696.0	644.1	614.5	604.7	604.7	603.4
30°	782.3	761.4	709.6	650.3	598.5	571.4	563.9	563.9	562.8
32.5°	728.1	707.1	660.2	603.4	554.0	525.7	519.5	522.0	520.7
35°	665.2	647.8	604.7	549.2	506.0	480.1	477.6	480.1	480.1
37.5°	602.2	586.2	549.2	501.0	460.3	436.9	436.9	440.5	439.3
40°	536.8	524.5	489.9	448.0	414.7	398.6	396.1	399.8	401.1
42.5°	475.1	465.2	435.6	401.1	371.4	355.4	359.0	361.5	362.8
45°	419.5	409.7	386.2	350.4	329.5	318.4	318.4	322.1	320.9
47.5°	370.2	362.8	339.3	304.8	286.3	281.3	283.8	286.3	286.3
50°	327.0	315.9	293.7	266.6	253.0	246.8	249.3	250.5	250.5
52.5°	286.3	278.9	256.6	232.0	219.7	215.9	215.9	217.2	217.2
55°	253.0	244.4	224.6	199.9	190.0	185.1	181.4	180.1	182.6
57.5°	220.9	213.5	195.0	171.5	160.4	155.4	148.1	145.6	148.1
60°	192.5	186.4	167.8	145.6	134.5	124.6	116.0	111.0	113.5
62.5°	167.8	160.4	142.0	123.4	111.0	99.9	86.3	79.0	82.7
65°	143.1	137.0	118.5	99.9	87.6	74.0	58.0	53.0	53.0
67.5°	120.9	114.8	97.4	81.5	66.6	50.6	35.8	34.6	35.8
70°	99.9	93.8	79.0	62.9	46.9	30.8	21.0	21.0	21.0
72.5°	82.7	75.2	61.7	45.7	29.6	16.1	11.1	12.3	12.3
75°	64.1	58.0	45.7	30.8	17.2	7.4	6.1	6.1	6.1
77.5°	48.2	43.2	32.1	19.7	8.6	2.5	2.5	2.5	2.5
80°	33.3	28.4	21.0	12.3	5.0	2.5	2.5	2.5	2.5
82.5°	19.7	17.2	12.3	6.1	2.5	1.2	1.2	1.2	1.2
85°	9.9	8.6	5.0	2.5	1.2	1.2	1.2	1.2	1.2
87.5°	2.5	2.5	1.2	1.2	0.0	1.2	1.2	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)