

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581937

Luminaire Tested: **HCC6W20D010MW-HM60525930-61RWWH**

Issue Date: 9/16/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P581937  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-15)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/16/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC6W20D010MW-HM60525930-61RWWH  
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, HAZE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1844.8 lumens  
Efficiency: N/A  
Efficacy: 92.2 lumens/watt  
Spacing Criteria (0/90/45): 1.19 / 1.12 / 1.19  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 20  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P581937  
CATALOG NUMBER: HCC6W20D010MW-HM60525930-61RWWH

### Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P581937

CATALOG NUMBER: HCC6W20D010MW-HM60525930-61RWWH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	103	96	90	85	100	94	89	84	91	86	83	87	84	81	85	82	79	77			
3	95	86	79	74	93	84	78	73	82	76	72	79	74	70	77	73	69	67			
4	88	78	70	64	86	76	69	64	74	68	63	72	66	62	70	65	61	59			
5	82	70	62	57	80	69	62	56	67	61	56	65	60	55	64	59	55	53			
6	76	64	56	50	74	63	56	50	61	55	50	60	54	49	58	53	49	47			
7	71	59	51	45	69	58	50	45	56	50	45	55	49	44	54	48	44	42			
8	66	54	46	41	65	53	46	41	52	45	41	51	45	40	50	44	40	38			
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35			
10	59	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	51613	51613	51613
5°	52146	51673	51337
10°	52888	51513	50968
15°	54138	51198	50704
20°	54634	49669	49815
25°	53441	47168	48069
30°	50622	43823	45304
35°	45836	40053	41539
40°	39918	36204	37535
45°	33872	32050	33197
50°	29995	27991	28724
55°	26427	23942	23827
60°	23671	20163	18529
65°	21131	16163	13283
70°	18593	11685	8303
75°	15674	7053	4702
80°	12091	3125	1926
85°	6982	755	755



TEST NUMBER: P581937  
 CATALOG NUMBER: HCC6W20D010MW-HM60525930-61RWWH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	89.4	4.8
10°-20°	256.9	13.9
20°-30°	371.3	20.1
30°-40°	390.7	21.2
40°-50°	328.4	17.8
50°-60°	230.5	12.5
60°-70°	126.8	6.9
70°-80°	45.0	2.4
80°-90°	5.9	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	717.5	38.9
0°-40°	1108.2	60.1
0°-60°	1667.2	90.4
0°-90°	1844.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1844.8	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	942	942	942	942	942	
5°	948	945	939	935	933	91
15°	954	938	902	891	893	269
25°	884	839	780	781	795	404
35°	685	645	598	611	621	424
45°	437	424	413	423	428	343
55°	276	262	250	250	249	249
65°	163	146	125	102	102	162
75°	74	59	33	22	22	80
85°	11	6	1	1	1	15
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P581937

CATALOG NUMBER: HCC6W20D010MW-HM60525930-61RWWH

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	941.5	941.5	941.5	941.5	941.5	941.5	941.5	941.5	941.5
2.5°	941.5	941.5	940.3	940.3	937.8	937.8	936.5	936.5	936.5
5°	947.6	947.6	945.3	941.5	939.0	935.4	935.4	934.2	932.9
7.5°	951.4	950.1	946.5	941.5	935.4	929.2	926.7	927.9	926.7
10°	950.1	947.6	942.8	932.9	925.4	916.8	915.6	914.3	915.6
12.5°	952.6	948.9	939.0	926.7	914.3	904.5	903.2	903.2	904.5
15°	953.9	950.1	937.8	919.3	902.1	892.1	890.9	892.1	893.4
17.5°	950.1	945.3	926.7	902.1	882.3	872.4	872.4	874.9	877.4
20°	936.5	929.2	903.2	873.7	851.4	844.1	846.5	851.4	853.9
22.5°	912.0	903.2	873.7	840.3	816.9	810.8	816.9	823.0	825.5
25°	883.5	873.7	839.1	804.5	779.8	772.5	781.1	790.9	794.7
27.5°	845.3	834.1	802.1	762.6	737.9	734.2	744.0	755.1	757.6
30°	799.7	787.3	751.5	714.5	692.3	691.0	702.1	712.0	715.7
32.5°	744.0	732.9	702.1	665.1	645.4	645.4	656.5	665.1	668.8
35°	684.9	672.5	645.4	614.5	598.5	599.7	610.8	617.0	620.7
37.5°	614.5	610.8	589.8	563.9	552.8	555.3	563.9	568.9	572.6
40°	557.8	547.9	534.3	513.4	505.9	508.4	517.0	522.0	524.5
42.5°	496.0	489.9	478.8	464.0	459.1	462.7	470.2	473.8	472.6
45°	436.9	435.6	424.5	415.8	413.4	418.3	423.3	426.9	428.2
47.5°	393.6	388.7	378.9	372.6	370.2	375.1	380.1	382.5	382.5
50°	351.7	346.7	336.8	330.7	328.2	333.2	336.8	339.3	336.8
52.5°	309.8	304.8	296.2	288.8	287.6	289.9	291.2	292.4	294.9
55°	276.5	271.5	261.6	253.0	250.5	251.8	250.5	250.5	249.3
57.5°	244.3	239.4	229.5	219.7	215.9	214.7	211.0	209.8	208.6
60°	215.9	209.8	199.9	188.8	183.9	178.9	172.8	169.0	169.0
62.5°	188.8	182.6	171.5	161.7	154.2	145.6	135.7	130.7	130.7
65°	162.9	157.9	145.6	134.5	124.6	113.5	102.4	99.9	102.4
67.5°	138.2	133.2	120.9	109.8	97.4	84.0	74.0	74.0	76.5
70°	116.0	111.0	99.9	86.3	72.9	59.3	51.8	51.8	51.8
72.5°	95.1	90.1	77.7	65.4	51.8	38.3	34.6	35.8	34.6
75°	74.0	70.4	59.3	45.7	33.3	23.5	22.2	21.0	22.2
77.5°	55.5	51.8	41.9	29.6	18.5	13.6	12.3	12.3	12.3
80°	38.3	34.6	27.2	17.2	9.9	6.1	6.1	6.1	6.1
82.5°	23.5	19.7	14.8	8.6	3.7	3.7	3.7	3.7	3.7
85°	11.1	8.6	6.1	2.5	1.2	1.2	1.2	1.2	1.2
87.5°	2.5	2.5	1.2	1.2	0.0	1.2	1.2	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°    - - 45°-225°    - - - - 90°-270°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)