

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581961

Luminaire Tested: **HCC6S20D010MW-HM60525935-61WWW**

Issue Date: 9/16/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P581961  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-16)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/16/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC6S20D010MW-HM60525935-61WWW  
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, WHITE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1798.0 lumens  
Efficiency: N/A  
Efficacy: 89.9 lumens/watt  
Spacing Criteria (0/90/45): 1.1 / 1.06 / 1.14  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 20  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P581961  
CATALOG NUMBER: HCC6S20D010MW-HM60525935-61WWW

### Luminous Intensity Polar Plot





TEST NUMBER: P581961

CATALOG NUMBER: HCC6S20D010MW-HM60525935-61WWW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	93	91	89	87								
2	102	95	89	84	99	93	88	83	90	85	81	86	83	79	83	80	78	76								
3	94	85	78	72	92	83	77	71	80	75	70	78	73	69	75	71	68	66								
4	87	76	69	63	85	75	68	62	73	67	62	71	65	61	69	64	60	58								
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51								
6	75	63	55	49	73	62	55	49	61	54	49	59	53	48	57	52	48	46								
7	70	58	50	44	69	57	50	44	56	49	44	54	48	44	53	48	43	42								
8	66	53	46	40	64	53	45	40	51	45	40	50	44	40	49	44	39	38								
9	62	49	42	37	60	49	42	37	48	41	36	47	41	36	46	40	36	34								
10	58	46	39	34	57	45	38	34	44	38	33	44	38	33	43	37	33	32								

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	52912	52912	52912
5°	55261	52757	50330
10°	56768	51847	47294
15°	58173	50727	44314
20°	58432	48427	40697
25°	57203	45341	37321
30°	54281	41690	34208
35°	49296	37470	30684
40°	42952	33370	27609
45°	37167	29205	24266
50°	32468	25151	21270
55°	28682	22097	18245
60°	25776	19362	15810
65°	23089	16863	15332
70°	20612	14361	14361
75°	17877	12115	13492
80°	14333	10260	12312
85°	9812	8995	10630



TEST NUMBER: P581961  
 CATALOG NUMBER: HCC6S20D010MW-HM60525935-61WWW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	90.7	5.0
10°-20°	252.2	14.0
20°-30°	351.4	19.5
30°-40°	362.1	20.1
40°-50°	300.1	16.7
50°-60°	215.7	12.0
60°-70°	137.3	7.6
70°-80°	70.5	3.9
80°-90°	17.9	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	694.3	38.6
0°-40°	1056.4	58.8
0°-60°	1572.2	87.4
0°-90°	1798.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1798.0	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	965	965	965	965	965	
5°	1004	989	959	928	915	96
15°	1025	986	894	812	781	289
25°	946	881	750	653	617	433
35°	737	677	560	486	458	458
45°	479	446	377	329	313	371
55°	300	275	231	205	191	270
65°	178	158	130	113	118	178
75°	84	73	57	60	64	90
85°	16	14	14	16	17	20
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P581961

CATALOG NUMBER: HCC6S20D010MW-HM60525935-61WWW

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	965.2	965.2	965.2	965.2	965.2	965.2	965.2	965.2	965.2
2.5°	983.4	979.5	974.3	969.2	961.4	952.3	944.5	941.9	937.9
5°	1004.2	999.0	988.7	975.6	958.7	941.9	927.6	918.4	914.6
7.5°	1017.2	1010.7	996.4	974.3	949.7	925.0	904.1	891.2	886.0
10°	1019.8	1013.2	993.8	964.0	931.4	897.7	871.7	856.1	849.6
12.5°	1023.7	1014.6	989.9	954.8	913.3	874.3	841.8	822.3	815.9
15°	1025.0	1014.6	986.0	943.1	893.8	847.0	811.9	788.6	780.8
17.5°	1019.8	1008.1	974.3	922.4	866.5	817.1	775.5	750.8	740.5
20°	1001.6	988.7	949.7	891.2	830.1	778.1	735.3	709.3	697.6
22.5°	978.2	961.4	917.2	854.8	791.2	736.6	693.7	667.8	656.0
25°	945.7	930.2	880.8	814.5	749.6	692.4	653.4	626.2	617.0
27.5°	908.1	889.9	839.2	772.9	706.7	649.5	611.8	587.2	575.5
30°	857.5	840.5	789.8	723.6	658.6	605.4	566.4	545.7	540.4
32.5°	797.6	783.4	734.0	671.6	609.3	559.9	527.4	505.3	500.1
35°	736.6	719.7	676.9	618.4	559.9	515.7	485.8	466.3	458.5
37.5°	670.3	654.8	618.4	566.4	514.5	472.9	446.9	430.0	422.2
40°	600.2	588.5	554.7	513.1	466.3	430.0	407.9	393.6	385.8
42.5°	535.2	523.6	500.1	461.1	422.2	389.8	370.3	357.2	350.8
45°	479.4	468.9	445.6	411.8	376.7	349.4	328.7	319.6	313.0
47.5°	423.5	418.3	397.6	366.3	333.9	310.4	296.2	285.9	280.6
50°	380.7	374.1	354.6	322.2	294.9	276.7	263.8	254.6	249.4
52.5°	336.5	329.9	311.8	284.5	262.4	245.5	232.5	224.8	219.6
55°	300.1	294.9	275.4	250.7	231.2	217.0	205.3	196.1	190.9
57.5°	266.4	261.2	242.9	219.6	202.7	189.7	179.2	171.5	165.0
60°	235.1	231.2	213.0	190.9	176.6	163.7	154.5	148.1	144.2
62.5°	207.9	200.1	184.5	165.0	152.0	141.6	132.6	128.6	131.2
65°	178.0	174.0	158.5	141.6	130.0	119.5	113.1	115.6	118.2
67.5°	153.3	148.1	135.1	119.5	109.1	101.3	97.4	102.6	103.9
70°	128.6	123.4	111.7	98.7	89.6	84.4	84.4	88.4	89.6
72.5°	105.3	101.3	91.0	80.6	74.1	70.1	72.7	75.3	76.6
75°	84.4	80.6	72.7	63.7	57.2	57.2	59.7	62.3	63.7
77.5°	64.9	62.3	54.6	48.0	45.4	45.4	48.0	49.4	50.6
80°	45.4	42.8	39.0	35.1	32.5	35.1	37.7	37.7	39.0
82.5°	29.9	28.6	25.9	23.3	23.3	24.7	25.9	27.3	27.3
85°	15.6	15.6	14.3	13.0	14.3	15.6	15.6	16.9	16.9
87.5°	5.2	5.2	5.2	5.2	6.5	6.5	6.5	6.5	6.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°    - - 45°-225°    - - - - 90°-270°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)