

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581978

Luminaire Tested: **HCC6W20D010MW-HM60525940-61WWBB**

Issue Date: 9/16/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P581978  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-17)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/16/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC6W20D010MW-HM60525940-61WWBB  
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, WHITE BAFFLE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1666.6 lumens  
Efficiency: N/A  
Efficacy: 83.3 lumens/watt  
Spacing Criteria (0/90/45): 1.15 / 1.06 / 1.14  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 20  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P581978  
CATALOG NUMBER: HCC6W20D010MW-HM60525940-61WWBB

### Luminous Intensity Polar Plot





TEST NUMBER: P581978  
 CATALOG NUMBER: HCC6W20D010MW-HM60525940-61WWBB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20										
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	108	104	101	109	105	102	100	101	99	97	97	95	94	94	92	91	89								
2	103	97	91	87	101	95	90	86	91	87	84	88	85	82	85	83	80	78								
3	96	87	80	75	93	86	79	74	83	77	73	80	76	72	78	74	71	69								
4	89	79	71	66	87	78	71	65	75	69	64	73	68	64	71	66	63	61								
5	83	72	64	58	81	71	63	58	69	62	57	67	61	57	65	60	56	54								
6	77	65	58	52	75	65	57	52	63	56	51	61	55	51	60	55	51	49								
7	72	60	52	47	70	59	52	47	58	51	46	56	51	46	55	50	46	44								
8	67	55	48	43	66	55	47	42	53	47	42	52	46	42	51	46	42	40								
9	63	51	44	39	62	51	44	39	50	43	39	49	43	38	48	42	38	37								
10	60	48	40	36	58	47	40	36	46	40	36	45	40	35	45	39	35	34								

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	51273	51273	51273
5°	52262	51178	50016
10°	54040	50522	48401
15°	55693	49643	46884
20°	56553	47575	44431
25°	55539	44319	41373
30°	52793	40386	37968
35°	47448	36092	34245
40°	40948	31631	30593
45°	34670	27228	26522
50°	29730	23001	22771
55°	25777	19364	18599
60°	22498	15711	13266
65°	19795	12115	7329
70°	17070	8014	3574
75°	14488	3918	1398
80°	11207	1642	821
85°	6604	881	881



TEST NUMBER: P581978

CATALOG NUMBER: HCC6W20D010MW-HM60525940-61WWBB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	88.3	5.3
10°-20°	249.6	15.0
20°-30°	351.5	21.1
30°-40°	359.1	21.5
40°-50°	289.5	17.4
50°-60°	194.2	11.7
60°-70°	98.3	5.9
70°-80°	31.4	1.9
80°-90°	4.9	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	689.3	41.4
0°-40°	1048.4	62.9
0°-60°	1532.1	91.9
0°-90°	1666.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1666.6	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	935	935	935	935	935	
5°	950	943	930	916	909	91
15°	981	942	875	835	826	277
25°	918	846	733	688	684	420
35°	709	645	539	509	512	441
45°	447	412	351	339	342	348
55°	270	239	203	193	195	243
65°	153	126	93	62	56	152
75°	68	49	18	7	7	73
85°	10	5	1	1	1	14
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P581978

CATALOG NUMBER: HCC6W20D010MW-HM60525940-61WWBB

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3
2.5°	939.1	937.9	936.5	933.9	930.0	926.0	923.4	920.8	919.4
5°	949.7	947.1	943.1	937.9	930.0	920.8	915.5	910.3	908.9
7.5°	964.2	958.9	948.4	936.5	923.4	910.3	901.1	895.7	891.8
10°	970.8	961.6	947.1	927.4	907.6	891.8	880.0	872.1	869.5
12.5°	976.0	965.5	944.5	918.2	891.8	870.8	857.7	851.0	848.4
15°	981.3	970.8	941.9	907.6	874.7	849.8	835.2	828.7	826.1
17.5°	981.3	966.8	932.6	889.2	849.8	819.5	805.0	798.4	797.1
20°	969.4	953.6	911.6	860.3	815.5	781.3	768.2	764.2	761.6
22.5°	947.1	928.6	881.4	823.5	774.7	741.9	727.4	724.8	722.2
25°	918.2	899.7	845.8	783.9	732.7	699.7	688.0	685.4	684.0
27.5°	881.4	861.5	805.0	741.9	686.6	655.1	644.6	644.6	643.2
30°	834.0	811.6	756.4	693.2	638.0	609.0	601.2	601.2	599.8
32.5°	776.1	753.7	703.7	643.2	590.6	560.4	553.8	556.4	555.1
35°	709.0	690.6	644.6	585.3	539.3	511.7	509.1	511.7	511.7
37.5°	642.0	624.8	585.3	534.1	490.6	465.7	465.7	469.6	468.3
40°	572.2	559.0	522.2	477.4	442.0	424.9	422.3	426.2	427.5
42.5°	506.5	495.9	464.3	427.5	396.0	378.9	382.7	385.4	386.7
45°	447.2	436.7	411.7	373.6	351.2	339.3	339.3	343.3	342.1
47.5°	394.6	386.7	361.8	324.9	305.1	299.9	302.5	305.1	305.1
50°	348.6	336.7	313.0	284.2	269.7	263.1	265.7	267.0	267.0
52.5°	305.1	297.3	273.6	247.3	234.2	230.2	230.2	231.5	231.5
55°	269.7	260.5	239.4	213.1	202.6	197.3	193.4	192.0	194.6
57.5°	235.4	227.5	207.8	182.9	171.0	165.8	157.8	155.2	157.8
60°	205.2	198.6	178.9	155.2	143.3	132.9	123.6	118.4	121.0
62.5°	178.9	171.0	151.3	131.5	118.4	106.5	92.1	84.2	88.1
65°	152.6	146.0	126.3	106.5	93.4	79.0	61.9	56.5	56.5
67.5°	128.9	122.4	103.9	86.8	71.0	53.9	38.2	36.8	38.2
70°	106.5	99.9	84.2	67.1	50.0	32.9	22.3	22.3	22.3
72.5°	88.1	80.2	65.7	48.7	31.6	17.1	11.8	13.1	13.1
75°	68.4	61.9	48.7	32.9	18.5	7.9	6.6	6.6	6.6
77.5°	51.3	46.0	34.2	21.1	9.2	2.6	2.6	2.6	2.6
80°	35.5	30.3	22.3	13.1	5.2	2.6	2.6	2.6	2.6
82.5°	21.1	18.5	13.1	6.6	2.6	1.4	1.4	1.4	1.4
85°	10.5	9.2	5.2	2.6	1.4	1.4	1.4	1.4	1.4
87.5°	2.6	2.6	1.4	1.4	0.0	1.4	1.4	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°    - - 45°-225°    - - - - 90°-270°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)