

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581997

Luminaire Tested: **HCC6S25D010SL-HM60525827-61WWBB**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P581997
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-17)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6S25D010SL-HM60525827-61WWBB
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, WHITE BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2103.0 lumens
Efficiency: N/A
Efficacy: 78.5 lumens/watt
Spacing Criteria (0/90/45): 1.15 / 1.06 / 1.14
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 26.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P581997
CATALOG NUMBER: HCC6S25D010SL-HM60525827-61WWBB

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P581997

CATALOG NUMBER: HCC6S25D010SL-HM60525827-61WWBB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	108	104	101	109	105	102	100	101	99	97	97	95	94	94	92	91	89								
2	103	97	91	87	101	95	90	86	91	87	84	88	85	82	85	83	80	78								
3	96	87	80	75	93	86	79	74	83	77	73	80	76	72	78	74	71	69								
4	89	79	71	66	87	78	71	65	75	69	64	73	68	64	71	67	63	61								
5	83	72	64	58	81	71	63	58	69	62	57	67	61	57	65	60	56	54								
6	77	65	58	52	75	65	57	52	63	56	51	61	55	51	60	55	51	49								
7	72	60	52	47	70	59	52	47	58	51	46	56	51	46	55	50	46	44								
8	67	55	48	43	66	55	47	42	53	47	42	52	46	42	51	46	42	40								
9	63	51	44	39	62	51	44	39	50	43	39	49	43	38	48	42	38	37								
10	60	48	40	36	58	47	40	36	46	40	36	45	40	35	45	39	35	34								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	64693	64693	64693
5°	65947	64572	63113
10°	68185	63749	61071
15°	70273	62645	59160
20°	71365	60036	56069
25°	70075	55921	52207
30°	66612	50964	47906
35°	59869	45541	43212
40°	51668	39910	38601
45°	43756	34360	33453
50°	37508	29023	28733
55°	32525	24429	23473
60°	28386	19834	16742
65°	24983	15293	9262
70°	21542	10098	4520
75°	18279	4914	1758
80°	14175	2084	1042
85°	8366	1006	1006



TEST NUMBER: P581997
 CATALOG NUMBER: HCC6S25D010SL-HM60525827-61WWBB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	111.4	5.3
10°-20°	314.9	15.0
20°-30°	443.5	21.1
30°-40°	453.1	21.5
40°-50°	365.3	17.4
50°-60°	245.0	11.7
60°-70°	124.0	5.9
70°-80°	39.6	1.9
80°-90°	6.1	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	869.8	41.4
0°-40°	1322.9	62.9
0°-60°	1933.3	91.9
0°-90°	2103.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2103.0	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1180	1180	1180	1180	1180	
5°	1198	1190	1173	1155	1147	115
15°	1238	1188	1104	1054	1042	350
25°	1158	1067	924	868	863	530
35°	895	813	680	642	646	557
45°	564	520	443	428	432	439
55°	340	302	256	244	246	306
65°	193	159	118	78	71	192
75°	86	61	23	8	8	93
85°	13	7	2	2	2	18
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P581997

CATALOG NUMBER: HCC6S25D010SL-HM60525827-61WWBB

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	1180.1	1180.1	1180.1	1180.1	1180.1	1180.1	1180.1	1180.1	1180.1
2.5°	1185.1	1183.5	1181.8	1178.4	1173.4	1168.5	1165.2	1161.9	1160.2
5°	1198.4	1195.1	1190.1	1183.5	1173.4	1161.9	1155.3	1148.6	1146.9
7.5°	1216.7	1210.0	1196.7	1181.8	1165.2	1148.6	1137.0	1130.3	1125.3
10°	1224.9	1213.3	1195.1	1170.2	1145.2	1125.3	1110.4	1100.4	1097.1
12.5°	1231.6	1218.3	1191.7	1158.5	1125.3	1098.8	1082.2	1073.9	1070.6
15°	1238.2	1224.9	1188.5	1145.2	1103.8	1072.2	1054.0	1045.6	1042.4
17.5°	1238.2	1219.9	1176.8	1122.1	1072.2	1034.1	1015.8	1007.5	1005.8
20°	1223.3	1203.4	1150.3	1085.5	1029.1	985.9	969.3	964.3	961.1
22.5°	1195.1	1171.8	1112.0	1039.0	977.6	936.1	917.8	914.6	911.2
25°	1158.5	1135.3	1067.3	989.2	924.5	883.0	868.1	864.7	863.1
27.5°	1112.0	1087.2	1015.8	936.1	866.4	826.6	813.3	813.3	811.7
30°	1052.3	1024.1	954.4	874.7	805.1	768.5	758.6	758.6	756.8
32.5°	979.2	951.0	888.0	811.7	745.3	707.1	698.8	702.1	700.4
35°	894.6	871.3	813.3	738.6	680.5	645.7	642.3	645.7	645.7
37.5°	809.9	788.4	738.6	673.9	619.1	587.5	587.5	592.5	590.9
40°	722.0	705.4	659.0	602.6	557.7	536.2	532.8	537.8	539.4
42.5°	639.0	625.7	585.9	539.4	499.6	478.0	483.0	486.3	488.0
45°	564.4	551.1	519.5	471.4	443.2	428.3	428.3	433.2	431.5
47.5°	497.9	488.0	456.5	410.0	385.0	378.4	381.8	385.0	385.0
50°	439.8	424.9	395.1	358.5	340.3	331.9	335.3	336.9	336.9
52.5°	385.0	375.1	345.2	312.0	295.5	290.4	290.4	292.1	292.1
55°	340.3	328.7	302.1	268.9	255.6	249.0	244.0	242.3	245.6
57.5°	297.1	287.2	262.3	230.7	215.8	209.1	199.2	195.8	199.2
60°	258.9	250.6	225.8	195.8	180.9	167.7	156.0	149.4	152.7
62.5°	225.8	215.8	190.8	166.0	149.4	134.4	116.2	106.3	111.3
65°	192.6	184.2	159.4	134.4	117.9	99.6	78.1	71.4	71.4
67.5°	162.6	154.4	131.1	109.5	89.6	68.0	48.1	46.5	48.1
70°	134.4	126.2	106.3	84.7	63.0	41.5	28.2	28.2	28.2
72.5°	111.3	101.2	82.9	61.4	39.8	21.6	14.9	16.5	16.5
75°	86.3	78.1	61.4	41.5	23.2	9.9	8.3	8.3	8.3
77.5°	64.8	58.1	43.1	26.6	11.7	3.3	3.3	3.3	3.3
80°	44.9	38.2	28.2	16.5	6.6	3.3	3.3	3.3	3.3
82.5°	26.6	23.2	16.5	8.3	3.3	1.6	1.6	1.6	1.6
85°	13.3	11.7	6.6	3.3	1.6	1.6	1.6	1.6	1.6
87.5°	3.3	3.3	1.6	1.6	0.0	1.6	1.6	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)