

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581991

Luminaire Tested: **HCC6W25D010MW-HM60525827-61RWWH**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P581991
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-15)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6W25D010MW-HM60525827-61RWWH
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2481.4 lumens
Efficiency: N/A
Efficacy: 92.6 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.12 / 1.19
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 26.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P581991
CATALOG NUMBER: HCC6W25D010MW-HM60525827-61RWWH

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P581991

CATALOG NUMBER: HCC6W25D010MW-HM60525827-61RWWH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88								
2	103	96	90	85	100	94	89	84	91	86	83	87	84	81	85	82	79	77								
3	95	86	79	74	93	84	78	73	82	76	72	79	74	70	77	73	69	67								
4	88	78	70	64	86	76	69	64	74	68	63	72	66	62	70	65	61	59								
5	82	70	62	57	80	69	62	56	67	61	56	65	60	55	64	59	55	53								
6	76	64	56	50	74	63	56	50	61	55	50	60	54	49	58	53	49	47								
7	71	59	51	45	69	58	50	45	56	50	45	55	49	44	54	48	44	42								
8	66	54	46	41	65	53	46	41	52	45	41	51	45	40	50	44	40	38								
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35								
10	59	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	69424	69424	69424
5°	70146	69502	69051
10°	71147	69298	68558
15°	72810	68860	68196
20°	73495	66809	67002
25°	71877	63451	64655
30°	68074	58939	60940
35°	61650	53866	55874
40°	53686	48698	50480
45°	45547	43105	44648
50°	40340	37645	38643
55°	35535	32200	32047
60°	31840	27114	24932
65°	28408	21753	17862
70°	25004	15708	11172
75°	21096	9510	6312
80°	16258	4199	2620
85°	9372	1006	1006



TEST NUMBER: P581991
 CATALOG NUMBER: HCC6W25D010MW-HM60525827-61RWWH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	120.2	4.8
10°-20°	345.5	13.9
20°-30°	499.4	20.1
30°-40°	525.5	21.2
40°-50°	441.8	17.8
50°-60°	310.1	12.5
60°-70°	170.6	6.9
70°-80°	60.6	2.4
80°-90°	7.9	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	965.1	38.9
0°-40°	1490.6	60.1
0°-60°	2242.4	90.4
0°-90°	2481.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2481.4	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1266	1266	1266	1266	1266	
5°	1275	1271	1263	1258	1255	122
15°	1283	1261	1213	1198	1202	362
25°	1188	1129	1049	1051	1069	544
35°	921	868	805	822	835	571
45°	588	571	556	569	576	461
55°	372	352	337	337	335	335
65°	219	196	168	138	138	218
75°	100	80	45	30	30	107
85°	15	8	2	2	2	21
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P581991

CATALOG NUMBER: HCC6W25D010MW-HM60525827-61RWWH

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	1266.4	1266.4	1266.4	1266.4	1266.4	1266.4	1266.4	1266.4	1266.4
2.5°	1266.4	1266.4	1264.8	1264.8	1261.4	1261.4	1259.8	1259.8	1259.8
5°	1274.7	1274.7	1271.4	1266.4	1263.0	1258.1	1258.1	1256.4	1254.8
7.5°	1279.7	1278.1	1273.0	1266.4	1258.1	1249.7	1246.5	1248.1	1246.5
10°	1278.1	1274.7	1268.0	1254.8	1244.9	1233.2	1231.6	1229.8	1231.6
12.5°	1281.3	1276.3	1263.0	1246.5	1229.8	1216.5	1214.9	1214.9	1216.5
15°	1282.9	1278.1	1261.4	1236.5	1213.3	1200.0	1198.4	1200.0	1201.6
17.5°	1278.1	1271.4	1246.5	1213.3	1186.7	1173.4	1173.4	1176.7	1180.1
20°	1259.8	1249.7	1214.9	1175.1	1145.2	1135.2	1138.6	1145.2	1148.5
22.5°	1226.6	1214.9	1175.1	1130.3	1098.8	1090.5	1098.8	1107.0	1110.4
25°	1188.3	1175.1	1128.6	1082.1	1049.0	1039.0	1050.6	1063.9	1068.9
27.5°	1137.0	1121.9	1078.8	1025.7	992.5	987.5	1000.8	1015.8	1019.1
30°	1075.4	1058.9	1010.8	961.1	931.1	929.5	944.4	957.7	962.7
32.5°	1000.8	985.9	944.4	894.6	868.1	868.1	883.0	894.6	899.5
35°	921.2	904.5	868.1	826.6	804.9	806.7	821.6	829.9	834.9
37.5°	826.6	821.6	793.4	758.4	743.5	746.9	758.4	765.1	770.1
40°	750.2	736.9	718.7	690.4	680.5	683.8	695.4	702.1	705.4
42.5°	667.2	659.0	643.9	624.1	617.5	622.4	632.4	637.4	635.6
45°	587.5	585.9	571.0	559.3	556.0	562.6	569.2	574.2	575.9
47.5°	529.5	522.9	509.6	501.2	497.9	504.6	511.2	514.5	514.5
50°	473.0	466.4	453.1	444.8	441.4	448.1	453.1	456.5	453.1
52.5°	416.6	410.0	398.3	388.4	386.7	390.1	391.7	393.3	396.7
55°	371.8	365.1	351.8	340.2	336.9	338.6	336.9	336.9	335.3
57.5°	328.7	322.0	308.7	295.5	290.4	288.8	283.8	282.2	280.5
60°	290.4	282.2	268.9	254.0	247.3	240.7	232.3	227.4	227.4
62.5°	254.0	245.6	230.7	217.4	207.5	195.8	182.6	175.9	175.9
65°	219.0	212.5	195.8	180.9	167.7	152.7	137.7	134.4	137.7
67.5°	185.9	179.3	162.6	147.7	131.1	112.9	99.6	99.6	102.9
70°	156.0	149.4	134.4	116.2	98.0	79.7	69.7	69.7	69.7
72.5°	127.8	121.2	104.6	88.0	69.7	51.5	46.5	48.1	46.5
75°	99.6	94.6	79.7	61.4	44.9	31.6	29.8	28.2	29.8
77.5°	74.7	69.7	56.4	39.8	24.9	18.3	16.5	16.5	16.5
80°	51.5	46.5	36.5	23.2	13.3	8.3	8.3	8.3	8.3
82.5°	31.6	26.6	19.9	11.7	5.0	5.0	5.0	5.0	5.0
85°	14.9	11.7	8.3	3.3	1.6	1.6	1.6	1.6	1.6
87.5°	3.3	3.3	1.6	1.6	0.0	1.6	1.6	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)