

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581998

Luminaire Tested: **HCC6W25D010SL-HM60525827-61WWW**

Issue Date: 9/16/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P581998  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-16)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/16/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC6W25D010SL-HM60525827-61WWW  
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, WHITE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2297.2 lumens  
Efficiency: N/A  
Efficacy: 85.7 lumens/watt  
Spacing Criteria (0/90/45): 1.1 / 1.06 / 1.14  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 26.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P581998  
CATALOG NUMBER: HCC6W25D010SL-HM60525827-61WWW

### Luminous Intensity Polar Plot





TEST NUMBER: P581998

CATALOG NUMBER: HCC6W25D010SL-HM60525827-61WWW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	93	91	89	87					87			
2	102	95	89	84	99	93	88	83	90	85	81	86	83	79	83	80	78	76					76			
3	94	85	78	72	92	83	77	71	80	75	70	78	73	69	75	71	68	66					66			
4	87	76	69	63	85	75	68	62	73	67	62	71	65	61	69	64	60	58					58			
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51					51			
6	75	63	55	49	73	62	55	49	61	54	49	59	53	48	57	52	48	46					46			
7	70	58	50	44	69	57	50	44	56	49	44	54	48	44	53	48	43	42					42			
8	66	53	46	40	64	53	45	40	51	45	40	50	44	40	49	44	39	38					38			
9	62	49	42	37	60	49	42	37	48	41	36	47	41	36	46	40	36	34					34			
10	58	46	39	34	57	45	38	34	44	38	33	44	38	33	43	37	33	32					32			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	67604	67604	67604
5°	70608	67406	64302
10°	72527	66248	60425
15°	74319	64813	56612
20°	74656	61868	51997
25°	73087	57929	47688
30°	69346	53268	43709
35°	62981	47870	39210
40°	54874	42637	35273
45°	47486	37314	31011
50°	41474	32135	27172
55°	36644	28243	23321
60°	32947	24757	20196
65°	29497	21533	19587
70°	26335	18352	18352
75°	22854	15462	17220
80°	18342	13101	15690
85°	12517	11511	13586



TEST NUMBER: P581998  
 CATALOG NUMBER: HCC6W25D010SL-HM60525827-61WWW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	115.9	5.0
10°-20°	322.2	14.0
20°-30°	449.0	19.5
30°-40°	462.6	20.1
40°-50°	383.4	16.7
50°-60°	275.6	12.0
60°-70°	175.5	7.6
70°-80°	90.1	3.9
80°-90°	22.9	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	887.1	38.6
0°-40°	1349.7	58.8
0°-60°	2008.7	87.4
0°-90°	2297.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2297.2	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	1233	1233	1233	1233	1233	
5°	1283	1263	1225	1185	1168	123
15°	1310	1260	1142	1037	998	369
25°	1208	1125	958	835	788	554
35°	941	865	715	621	586	585
45°	612	569	481	420	400	474
55°	383	352	296	262	244	345
65°	227	202	166	144	151	228
75°	108	93	73	76	81	115
85°	20	18	18	20	22	25
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P581998

CATALOG NUMBER: HCC6W25D010SL-HM60525827-61WWW

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	1233.2	1233.2	1233.2	1233.2	1233.2	1233.2	1233.2	1233.2	1233.2
2.5°	1256.5	1251.5	1244.9	1238.2	1228.2	1216.7	1206.6	1203.4	1198.4
5°	1283.1	1276.4	1263.1	1246.5	1224.9	1203.4	1185.1	1173.4	1168.5
7.5°	1299.6	1291.3	1273.0	1244.9	1213.3	1181.7	1155.3	1138.6	1132.0
10°	1302.9	1294.6	1269.8	1231.6	1190.1	1146.9	1113.7	1093.7	1085.5
12.5°	1307.9	1296.2	1264.8	1219.9	1166.8	1117.0	1075.6	1050.6	1042.4
15°	1309.5	1296.2	1259.8	1205.0	1142.0	1082.2	1037.4	1007.5	997.5
17.5°	1302.9	1288.0	1244.9	1178.4	1107.0	1044.0	990.9	959.3	946.0
20°	1279.7	1263.1	1213.3	1138.6	1060.5	994.3	939.4	906.3	891.3
22.5°	1249.9	1228.2	1171.8	1092.1	1010.8	941.1	886.4	853.2	838.1
25°	1208.3	1188.3	1125.3	1040.7	957.7	884.6	834.9	800.0	788.4
27.5°	1160.2	1137.0	1072.2	987.6	902.9	829.9	781.7	750.2	735.3
30°	1095.5	1073.8	1009.2	924.5	841.5	773.5	723.6	697.2	690.5
32.5°	1019.1	1000.9	937.7	858.1	778.5	715.3	673.9	645.7	639.0
35°	941.1	919.6	864.7	790.0	715.3	659.0	620.7	595.8	585.9
37.5°	856.4	836.5	790.0	723.6	657.3	604.2	571.0	549.4	539.4
40°	766.8	751.9	708.7	655.6	595.8	549.4	521.1	503.0	492.9
42.5°	683.9	668.9	639.0	589.2	539.4	497.9	473.0	456.5	448.2
45°	612.5	599.2	569.4	526.1	481.3	446.4	419.9	408.4	400.0
47.5°	541.0	534.4	507.8	468.1	426.5	396.7	378.4	365.1	358.5
50°	486.3	478.0	453.1	411.6	376.8	353.5	336.9	325.3	318.6
52.5°	429.9	421.6	398.3	363.5	335.3	313.8	297.1	287.2	280.5
55°	383.4	376.8	351.8	320.4	295.5	277.2	262.3	250.6	244.0
57.5°	340.3	333.7	310.4	280.5	258.9	242.3	229.0	219.1	210.8
60°	300.5	295.5	272.2	244.0	225.8	209.1	197.5	189.2	184.2
62.5°	265.5	255.6	235.7	210.8	194.2	180.9	169.3	164.3	167.7
65°	227.4	222.4	202.5	180.9	166.0	152.7	144.3	147.7	151.0
67.5°	195.8	189.2	172.7	152.7	139.5	129.4	124.4	131.1	132.8
70°	164.3	157.6	142.7	126.2	114.5	107.9	107.9	112.9	114.5
72.5°	134.4	129.4	116.2	102.9	94.6	89.6	93.0	96.2	98.0
75°	107.9	102.9	93.0	81.3	73.0	73.0	76.3	79.7	81.3
77.5°	82.9	79.7	69.7	61.4	58.1	58.1	61.4	63.0	64.8
80°	58.1	54.8	49.7	44.9	41.5	44.9	48.1	48.1	49.7
82.5°	38.2	36.5	33.2	29.8	29.8	31.6	33.2	34.8	34.8
85°	19.9	19.9	18.3	16.5	18.3	19.9	19.9	21.6	21.6
87.5°	6.6	6.6	6.6	6.6	8.3	8.3	8.3	8.3	8.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°    - - 45°-225°    - - - - 90°-270°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)