

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582035

Luminaire Tested: **HCC6W25D010MW-HM60525835-61WWWB**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582035
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-18)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6W25D010MW-HM60525835-61WWWB
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2599.2 lumens
Efficiency: N/A
Efficacy: 97.0 lumens/watt
Spacing Criteria (0/90/45): 1.17 / 1.09 / 1.17
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 26.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582035
CATALOG NUMBER: HCC6W25D010MW-HM60525835-61WWWB

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P582035

CATALOG NUMBER: HCC6W25D010MW-HM60525835-61WWWB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	111	107	103	100	108	104	101	98	100	97	95	96	94	92	93	91	89	87					87			
2	102	95	89	84	100	93	88	83	90	85	81	87	83	80	84	81	78	76					76			
3	94	85	78	72	92	84	77	72	81	75	71	78	73	69	76	72	68	66					66			
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58					58			
5	81	70	61	56	79	68	61	55	66	60	55	65	59	54	63	58	54	52					52			
6	75	63	55	49	74	62	55	49	61	54	49	59	53	48	58	52	48	46					46			
7	70	58	50	44	69	57	50	44	56	49	44	54	48	44	53	48	43	42					42			
8	66	53	46	40	64	53	45	40	51	45	40	50	44	40	49	44	39	38					38			
9	62	49	42	37	60	49	42	37	48	41	36	47	41	36	46	40	36	34					34			
10	58	46	38	34	57	45	38	33	44	38	33	43	37	33	43	37	33	31					31			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	72757	72757	72757
5°	74339	72738	71439
10°	76607	72065	69644
15°	79030	71107	67918
20°	80285	68437	65158
25°	78966	64377	61413
30°	75176	59686	57382
35°	68563	53880	53030
40°	59941	48405	48140
45°	51595	42594	43578
50°	44843	37116	37884
55°	39158	32572	32916
60°	34789	28232	25842
65°	31041	23764	19769
70°	27312	19474	16573
75°	23426	15356	15737
80°	18910	13165	15469
85°	12517	11448	13712



TEST NUMBER: P582035

CATALOG NUMBER: HCC6W25D010MW-HM60525835-61WWWB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	125.7	4.8
10°-20°	357.7	13.8
20°-30°	510.7	19.6
30°-40°	534.9	20.6
40°-50°	450.4	17.3
50°-60°	320.6	12.3
60°-70°	187.6	7.2
70°-80°	88.8	3.4
80°-90°	22.8	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	994.1	38.2
0°-40°	1529.0	58.8
0°-60°	2300.0	88.5
0°-90°	2599.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2599.2	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1327	1327	1327	1327	1327	
5°	1351	1340	1322	1304	1298	130
15°	1392	1342	1253	1202	1197	393
25°	1306	1213	1064	1014	1015	598
35°	1024	939	805	778	792	636
45°	666	616	549	551	562	517
55°	410	375	341	341	344	369
65°	239	212	183	154	152	239
75°	111	92	72	71	74	119
85°	20	16	18	22	22	26
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P582035

CATALOG NUMBER: HCC6W25D010MW-HM60525835-61WWWB

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	1327.2	1327.2	1327.2	1327.2	1327.2	1327.2	1327.2	1327.2	1327.2
2.5°	1329.1	1329.1	1327.2	1325.4	1321.8	1316.4	1312.8	1309.1	1309.1
5°	1350.9	1347.2	1340.0	1330.8	1321.8	1310.9	1303.6	1298.2	1298.2
7.5°	1368.9	1361.6	1347.2	1330.8	1314.5	1300.0	1287.3	1280.1	1278.3
10°	1376.2	1367.1	1345.3	1320.0	1294.6	1274.7	1260.1	1251.1	1251.1
12.5°	1383.4	1372.5	1343.6	1307.3	1274.7	1247.5	1233.0	1225.7	1223.9
15°	1392.5	1378.0	1341.7	1296.4	1252.9	1222.1	1202.1	1196.7	1196.7
17.5°	1392.5	1374.4	1329.1	1272.8	1218.4	1184.0	1165.9	1160.4	1162.3
20°	1376.2	1356.2	1301.9	1233.0	1173.1	1136.8	1118.7	1115.0	1116.9
22.5°	1345.3	1321.8	1260.1	1185.8	1120.6	1082.5	1066.2	1066.2	1064.3
25°	1305.5	1280.1	1213.0	1135.1	1064.3	1026.2	1013.6	1015.3	1015.3
27.5°	1252.9	1227.6	1160.4	1077.0	1006.3	968.2	959.2	962.8	964.6
30°	1187.6	1160.4	1089.7	1008.2	942.9	904.8	899.3	904.8	906.5
32.5°	1107.8	1087.9	1018.9	935.6	874.0	841.3	839.5	844.9	852.2
35°	1024.5	1002.7	939.2	863.1	805.1	777.9	777.9	786.9	792.4
37.5°	933.7	912.1	854.0	790.5	741.5	716.2	719.8	728.9	730.7
40°	837.6	821.3	772.3	718.0	676.4	656.3	661.8	670.9	672.7
42.5°	747.0	732.5	692.7	643.7	612.8	598.3	605.6	616.5	620.1
45°	665.5	649.1	616.5	574.8	549.4	542.2	551.2	558.5	562.1
47.5°	591.0	576.6	549.4	511.3	493.2	489.5	498.6	502.2	505.8
50°	525.8	511.3	484.2	449.7	435.2	435.2	442.4	446.1	444.2
52.5°	462.4	449.7	424.3	395.3	386.2	386.2	391.7	393.4	397.1
55°	409.7	397.1	375.3	348.1	340.8	337.3	340.8	340.8	344.4
57.5°	360.9	350.0	330.0	304.6	295.6	291.9	290.1	288.3	291.9
60°	317.3	308.2	286.4	264.8	257.5	248.3	241.2	233.9	235.7
62.5°	277.4	268.4	248.3	226.7	219.4	206.7	197.6	188.6	192.2
65°	239.3	230.3	212.1	194.0	183.2	168.7	154.1	148.7	152.4
67.5°	204.9	197.6	179.6	161.4	152.4	136.0	121.5	121.5	123.3
70°	170.4	163.1	148.7	132.3	121.5	107.0	101.5	103.4	103.4
72.5°	139.6	134.2	119.7	105.1	94.2	85.2	85.2	87.1	88.8
75°	110.6	107.0	92.5	79.8	72.5	67.0	70.7	72.5	74.3
77.5°	85.2	79.8	68.9	59.9	54.4	56.3	59.9	61.6	63.4
80°	59.9	58.0	49.0	43.5	41.7	43.5	47.1	49.0	49.0
82.5°	38.1	36.2	30.8	29.1	29.1	30.8	34.5	34.5	34.5
85°	19.9	18.2	16.3	16.3	18.2	19.9	21.8	21.8	21.8
87.5°	7.3	5.4	7.3	7.3	9.0	9.0	9.0	9.0	9.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)